



PHILIPS

Greenspace Accent Gridlight

GD301B
GD302B



GD301B



GD302B



220 V
240 V

50 Hz
60 Hz

Max. 40 °C
Min. 10 °C






IK02

GLOW
WIRE
650 °C

IP20

Lum. Pack		CCT	Driver				Pnom.[W]	Pmax.[W]	BEAM ANGLE					Cable
									NB	MB	WB	CW	CW-L	
GD301B	1XLED17S	830	PSU-E	1,2	*		16,4	18		*	*	*		
	1XLED27S				*		26,5	29	*	*	*	*		
	1XLED39S		PSE-E	1,25	*		41	45		*	*	*		
GD302B	2XLED17S	827/830/840	PSE-E	2,1		*	31	34		*	*	*	*	
			PSD-E	2,2	*		32,5	36		*	*	*	*	
		CRW	PSE-E	2,1		*	45,5	50		*	*	*	*	
			PSD-E	2,2	*		46	51		*	*	*	*	
		PW9	PSE-E	2,1		*	34,5	37,5		*	*	*	*	
			PSD-E	2,2	*		35,5	39,5		*	*	*	*	
	2XLED27S	827/830/840	PSE-E	2,1	*		51	57	*	*	*	*	*	
			PSD-E	2,2	*		52	57	*	*	*	*	*	
		CRW	PSE-E	2,1	*		70	77	*	*	*	*	*	
			PSD-E	2,2	*		71	78	*	*	*	*	*	
		PW9	PSE-E	2,1	*		55	61	*	*	*	*	*	
			PSD-E	2,2	*		56	61	*	*	*	*	*	
	2XLED35S	827/830	PSE-E	2,1	*		64	71		*	*	*	*	
		840	PSE-E	2,1	*		65	71		*	*	*	*	
		827/830/840	PSD-E	2,2	*		65	72		*	*	*	*	
		PW9	PSE-E	2,1	*		72	79		*	*	*	*	
			PSD-E	2,2	*		73	80		*	*	*	*	

Main dimensions



	A[mm]	B[mm]	C[mm]	D[mm]	E[mm]
GD301B	194	194	96	141	133
GD302B	366	194	96	141	133

Min: 5mm
Max: 25mm

1
2
3

F
G
H

! (Warning icon)

K
L
M

	F[mm]*	G[mm]*	H[mm]*	I[mm]*	J[mm]*	K[mm]*	L[mm]*	M[mm]*
GD301B	177	177	900	400	100	75	100	20
GD302B	348	177	900	400	100	75	100	20


* Min

Mounted out of arms reach


Don't touch until it cooled down

Driver dimensions

GD301B	LED17S
	LED27S








GD302B	LED17S
	LED27S
	LED35S




	Lum. Pack	Driver	L[mm]	W[mm]	H[mm]
GD301	17S	Fix	126	68	32
	27S				
	39S				
GD302	17S	Fix	220	83	35
	27S				
	35S				
GD302	17S	Dali	190	46	32
	27S				
	35S				

GD301B	LED39S
	LED17S
	LED27S
	LED35S








PSU-E




PSE-E




~ 220-240V




PSED-E




a. ~220-240V cable




b. DALI cable






CW connector




CW-L connector



Optical unit changing, and cleaning instructions



Only with soft cloths!



GD301B	Fix driver	GD301B	Fix driver	GD302B	Fix driver	GD302B	Dali driver
LED17S & LED27S		LED39S		LED17S & LED27S & LED35S		LED17S & LED27S & LED35S	
LED Driver 36W 929000892506		Xitanium 50W 929000934706		Xitanium 75W Fix 929000853803		Xitanium 36W 929000870806	
Inom[A]	0.2	Inom[A]	0.27	Inom[A]	0.37	Inom[A]	0.2
Ipeak[A]	6	Ipeak[A]	23.5	Ipeak[A]	32	Ipeak[A]	5.3
Tref[us]	55	Tref[us]	272	Tref[us]	300	Tref[us]	700
MCB	Max products [pcs]*	MCB	Max products [pcs]*	MCB	Max products [pcs]*	MCB	Max products [pcs]*
B-16A	40	B-16A	24	B-16A	12	B-16A	24

*According to: IEC60555 test conditions