

CITYSPIRIT BRACKET - ZRP450 MBP/MBW

Mounting instructions

Instructions de montage

Montageanleitung

Montage instructie

Istruzioni di montaggio

Instrucciones de montaje

Instruções de montagem

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet

Montaj yönergəsi

Οδηγίες τήξεσσηθηθX

Instrukcja montazu

Szerelési utasítások

Návod k montázi

bychnerwbz gj vjynf:e

Návod k montázi



EN 40




Weight max for luminaire : 15 kg

SCx max for luminaire : 0,093 m²


SINGLE

Type	Weight kg	W mm	H1 mm	H2 mm	H3 mm	D mm	SCx m ²
Top 60 ZRP450 MBP-S	5,6	590	315	182		81,6	0,11
ZRP450 MBP-S DECO	6,2	590	315		430	81,6	0,12
Top 76 ZRP450 MBP-S D76	6,6	595	315	182		95	0,12
ZRP450 MBP-S DECO D76	7,2	595	315		430	95	0,13





DOUBLE

Type	Weight kg	W mm	H1 mm	H2 mm	H3 mm	D mm	SCx m ²
Top 60 ZRP450 MBP-T	7	590	315	182		81,6	0,216
ZRP450 MBP-T DECO	8,1	590	315		430	81,6	0,23
Top 76 ZRP450 MBP-T D76	8	595	315	182		95	0,22
ZRP450 MBP-T DECO D76	9,2	595	315		430	95	0,23




WALL MOUNTING

Type	Weight kg	W mm	H1 mm	H2 mm	H3 mm	SCx m ²
With connection compartment ZRP450 MBW JB	7,1	660	320	162		0,12
ZRP450 MBW JB DECO	7,5	660	320		430	0,13
Without connection compartment ZRP450 MBW	6,1	585	190	162		0,108
ZRP450 MBW DECO	6,4	585	190		430	0,11




13 Nm

TOP
Ø 60 mm - L 95 mm
OR
Ø 76 mm - L 95 mm



MBW
MBW DECO



MBW JB
MBW JB DECO