



# PHILIPS

## LuxSpace Accent Performance

RS750B, RS751B  
RS752B















| P (W) / Color temperature            |        |      |      |      |     |  |  |  |  |  | Beam angle |    |    |     |
|--------------------------------------|--------|------|------|------|-----|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------------|----|----|-----|
| CRW                                  | CH     | FMT  | ROSE |      |     | Ø mm                                                                              |                                                                                   |                                                                                   |                                                                                     |                                                                                     | NB         | MB | WB | VWB |
| RS750 B<br>Performance,<br>Fixed     | LED19S |      |      | 31   | 1,4 | 155                                                                               | x                                                                                 |                                                                                   | x                                                                                   |                                                                                     | x          | x  | x  |     |
|                                      | LED26S |      |      | 37,5 | 48  | 1,4                                                                               | 155                                                                               | x                                                                                 | x                                                                                   |                                                                                     | x          | x  | x  |     |
|                                      | LED26S | 47   |      |      |     | 1,4                                                                               | 155                                                                               | x                                                                                 | x                                                                                   | x                                                                                   |            |    |    |     |
|                                      | LED27S | 30,5 | 42   |      |     | 1,4                                                                               | 155                                                                               | x                                                                                 | x                                                                                   |                                                                                     | x          | x  | x  |     |
|                                      | LED39S | 49,5 |      |      |     | 1,4                                                                               | 155                                                                               | x                                                                                 | x                                                                                   |                                                                                     | x          | x  | x  |     |
| RS751B<br>Performance,<br>Adjustable | LED19S |      |      | 31   | 1,4 | 155                                                                               |                                                                                   | x                                                                                 | x                                                                                   |                                                                                     | x          | x  | x  |     |
|                                      | LED26S |      |      | 37,5 | 48  | 1,4                                                                               | 155                                                                               | x                                                                                 | x                                                                                   |                                                                                     | x          | x  | x  |     |
|                                      | LED26S | 47   |      |      |     | 1,4                                                                               | 155                                                                               | x                                                                                 | x                                                                                   | x                                                                                   |            |    |    |     |
|                                      | LED27S | 30,5 | 42   |      |     | 1,4                                                                               | 155                                                                               | x                                                                                 | x                                                                                   |                                                                                     | x          | x  | x  |     |
|                                      | LED39S | 49,5 |      |      |     | 1,4                                                                               | 155                                                                               | x                                                                                 | x                                                                                   |                                                                                     | x          | x  | x  |     |
| RS752B<br>Performance,<br>Elbow      | LED19S |      |      | 31   | 1,3 | 155                                                                               |                                                                                   | x                                                                                 | x                                                                                   |                                                                                     | x          | x  | x  |     |
|                                      | LED26S |      |      | 48   |     | 1,3                                                                               | 155                                                                               |                                                                                   | x                                                                                   | x                                                                                   |            | x  | x  | x   |
|                                      | LED26S | 47   |      |      |     | 1,3                                                                               | 155                                                                               |                                                                                   | x                                                                                   | x                                                                                   | x          | x  | x  |     |
|                                      | LED27S | 30,5 |      |      |     | 1,3                                                                               | 155                                                                               |                                                                                   | x                                                                                   | x                                                                                   |            | x  | x  | x   |
|                                      | LED39S | 49,5 |      |      |     | 1,2                                                                               | 155                                                                               |                                                                                   | x                                                                                   | x                                                                                   |            | x  | x  | x   |



RS750B  
RS751B  
RS752B


# Minimal built-in dimensions






| Xitanium 36W LH 0.3-1A 48V I 230V<br>(PSE-E) |                      |           | Xitanium 36W WH 0.3-1A 54V TD/I 230V<br>(PSED-E) |                      |           | Xitanium 50W LH 0.7-1.5A 48V 230V<br>(PSE-E) |                      |           | Xitanium 50W LH 0.7-1.5A 48V TD/I 230V<br>(PSED-E) |                      |           |
|----------------------------------------------|----------------------|-----------|--------------------------------------------------|----------------------|-----------|----------------------------------------------|----------------------|-----------|----------------------------------------------------|----------------------|-----------|
| Lum. Pack                                    | CCT                  | Inom. (A) | Lum. Pack                                        | CCT                  | Inom. (A) | Lum. Pack                                    | CCT                  | Inom. (A) | Lum. Pack                                          | CCT                  | Inom. (A) |
| LED27S                                       | CRW                  | 0.14      | LED27S                                           | CRW                  | 0.14      | LED26S                                       | CRW                  | 0.218     | LED26S                                             | CRW                  | 0.218     |
|                                              | CH                   | 0.187     |                                                  | CH                   | 0.187     | LED26S                                       | FMT                  | 0.166     | LED26S                                             | FMT                  | 0.166     |
|                                              |                      |           |                                                  |                      |           | LED39S                                       | CRW                  | 0.229     | LED39S                                             | CRW                  | 0.229     |
| Imax. (A)                                    | 14.5                 |           | Imax. (A)                                        | 5.3                  |           | Imax. (A)                                    | 23.5                 |           | Imax. (A)                                          | 5.3                  |           |
| Tref. (ms)                                   | 0.22                 |           | Tref. (ms)                                       | 0.7                  |           | Tref. (ms)                                   | 0.272                |           | Tref. (ms)                                         | 0.7                  |           |
| MCB                                          | Max. Products (pcs)* |           | MCB                                              | Max. Products (pcs)* |           | MCB                                          | Max. Products (pcs)* |           | MCB                                                | Max. Products (pcs)* |           |
| B-10A                                        | 20                   |           | B-10A                                            | 15                   |           | B-10A                                        | 15                   |           | B-10A                                              | 18                   |           |
| B-16A                                        | 32                   |           | B-16A                                            | 24                   |           | B-16A                                        | 24                   |           | B-16A                                              | 30                   |           |
| C-10A                                        | 33                   |           | C-10A                                            | 24                   |           | C-10A                                        | 24                   |           | C-10A                                              | 31                   |           |
| C-16A                                        | 54                   |           | C-16A                                            | 40                   |           | C-16A                                        | 40                   |           | C-16A                                              | 51                   |           |


| Xitanium 75W SH 0.3- 1A 110 V I 230 V<br>(PSE-E) |                      |           | Xitanium 75W SH 0.3- 1A 110 V TD/I 230 V<br>(PSED-E) |                      |           |
|--------------------------------------------------|----------------------|-----------|------------------------------------------------------|----------------------|-----------|
| Lum. Pack                                        | CCT                  | Inom. (A) | Lum. Pack                                            | CCT                  | Inom. (A) |
| LED19S                                           | ROSE                 | 0,13      | LED19S                                               | ROSE                 | 0,13      |
| LED26S                                           | ROSE                 | 0,2       | LED26S                                               | ROSE                 | 0,2       |
| Imax. (A)                                        | 32                   |           | Imax. (A)                                            | 7,4                  |           |
| Tref. (ms)                                       | 0,25                 |           | Tref. (ms)                                           | 0,53                 |           |
| MCB                                              | Max. Products (pcs)* |           | MCB                                                  | Max. Products (pcs)* |           |
| B- 10A                                           | 7                    |           | B- 10A                                               | 10                   |           |
| B- 16A                                           | 12                   |           | B- 16A                                               | 16                   |           |
| C- 10A                                           | 13                   |           | C- 10A                                               | 17                   |           |
| C- 16A                                           | 22                   |           | C- 16A                                               | 23                   |           |



Luminaire not suitable for being covered with thermally insulating material.



## Reflector accessory changing instructions



Only with soft clothes!  
Do not push hard!



© 2016 Philips Lighting Holding B.V.  
All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.  
The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use.  
Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V.  
The Netherlands