



DyNet-STP-CABLE-LSZH

100 MHz 100 Ω STP 4 pair Cat5e

DyNet data cable is specifically designed for high reliability RS-485 network wiring. In addition to a twisted pair for RS-485 data, conductors are provided to supply DC power to network powered devices.

DyNet-STP-CABLE-LSZH

100 MHz 100 Ω STP 4 pair Cat5e

- Overall shield for maximum data integrity The data cable is flexible and all conductors are stranded.
- Fast termination Designed for robust termination into pressure-plate style terminals.
- Extra thick outer jacket Mains rated for use in distribution boards.
- Supplied in 305 meter roll

SpecificationsDue to continuous improvements and innovations, specifications may change without notice.

Electrical

Characteristic Impedance	100 Ω ± 5 Ω @ 100 MHz
Conductor DC Loop Resistance	190 Ω/km (max)
DC Resistance Imbalance	2.5% (max)
Dielectric Strength Between Pairs	1 KV RMS / minute
Dielectric Strength Conductors to Screen	2.5 KV RMS / min
Capacitance	56 pF/m
Capacitance Imbalance	3.3 pF/M (max)
Maximum Delay	620 ns/100 m @ 100 MHz
Outer Jacket Voltage Rating	600 V RMS

Conductors

Wires	4 x twisted pairs and shield
Construction	Stranded Bare Copper 0.2 mm² (#24 AWG) 7-strand
Insulation	Polyethylene HDPE Ø 1.08 mm ± 0.05 mm
Colors	blue/white-blue orange/white-orange green/white-green brown/white-brown
Shielding	Aluminium/Mylar tape, 100% coverage
Drain Wire	Tinned copper

Physical

Dimensions (Cross-Section)	Ø 6.8 mm ± 0.30 mm
Shipping Carton (H x W x D)	425 x 212 x 425 mm (16.7 x 8.3 x 16.7 in)
Packed Weight	15 kg / 305 m roll (33 lb / 1000.6 ft roll)
Outer Jacket Construction	LSZH (Low Smoke Zero Halogen)
Outer Jacket Color	Orange
Outer Jacket Thickness	0.54 mm ± 0.05 mm
Minimum Bending Radius (Installed	d) 55 mm
Maximum Tensile Load (Installation	n) 100 N
Maximum Tensile Load (Installed)	0 N

Environment*

Operating Temperature	-20° to 70°C ambient (-4° to 158°F)
Storage/Transport Temperature	-20° to 70°C ambient (-4° to 158°F)
Humidity	0 to 90% non-condensing

Compliance

Certification CE, UKCA, RoHS ISO/IEC 11801 ACA Approval (N1756) TIA/EIA-568B.2 Category 5E

For indoor installation only



Ordering Code

Product Philips 12NC DyNet-STP-CABLE-LSZH (305 m roll) 913703898809

0.2 mm2 (#24 AWG) 7-strand



^{© 2022} Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Revision 07 2021-12-21 www.dynalite.com