

Velocity

SGP338

Mounting instruction 安装说明

4441 000 65391



IEC
60598

GB
7000

ta
35°



Gear
IP44
电器腔

Optics
IP66
光源腔

IK05



Type Number 型号	Lamp 光源	Voltage/Frequency 电压/频率	Glass 玻璃	Weight 重量(kg)	Dimming 调光
SGP338	SON-T 150W	220V/50Hz 230V/50Hz	GB (曲面)	12.5	
	SON-T 250W	220V/50Hz 230V/50Hz 240V/50Hz	GB (曲面) FG (平面)	13.5	
		220V/50Hz 230V/50Hz		14.35	SD
	SON-T 400W	220V/50Hz 230V/50Hz 240V/50Hz	GB (曲面)	15.8	



Philips Lighting Luminaires (Shanghai) Co., Ltd.
Address: No. 2688, Huiyi Road, Jiading, Shanghai, China
Postalcode: 201801
飞利浦灯具（上海）有限公司
地址：中国上海市嘉定区马陆镇沪宜公路
邮编：201801

PHILIPS

