







220V 240V 50Hz 60Hz



















		Driver PSU/PSD		А	В		kg
Dosessed	RC	40W	L120	1135	1150	65 x 1140	2.8
Recessed	KC	50W	L150	1415	1430	65 x 1420	3.3



- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.











	characteristics
Imax (A)	22
Tref (µs)	275
MCB	Luminaire max.
B-10 A	15
B-13 A	19
B-16 A	24
C-10 A	25
C-13 A	32
C-16 A	40


Electrical













© 2017 Philips Lighting Holding B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V. The Netherlands