




PHILIPS

TrueLine

SM530C



							Sensor/ Blind sensor holder.	
Surface Mounted		A	B	C	D	E		
Standalone	L1130	1130	759	200	171	930		3.2
	L1170	1170			211	970	•	3.4
	L1410	1409	1031		178	1209		3.8
	L1450	1449			219	1250	•	4.1
Line End	L1130	1128	759	200	170	929		3.2
	L1170	1168			210	969	•	3.4
	L1410	1408	1031		177	1208		3.8
	L1450	1448			217	1248	•	4.1
Line Feature	L1130	1127	957		170	1127		3.2
	L1170	1167			210	1167	•	3.4
	L1410	1406	1229		177	1406		3.8
	L1450	1446			217	1446	•	4.1



ACL / MDU versions only

ATTENTION
OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
SENSITIVE
DEVICES

DALI
Standalone /
Line End

1

Black **L**

Yellow-Green **⏏**

Blue **N**

+ DA / LS

Orange

- DA

Purple

2a

2b

2c





DALI

PoE

3

4a

4b





© 2017 Philips Lighting Holding B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V.
The Netherlands