

CitySoul Standard (CGP43I) and suspended (CSP43I)

Mounting instructions

Instructions de montage

Montageanleitung

Montage-instruktie

Istruzioni di montaggio

Instrucciones de montaje

Instruções de montagem

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet

Montaj yönergeleri

Οδηγίες τροφοδομηθθX


Instrukcja montazu

Szerelési utasítások

Návod k montázi


bycnerwbz gj vjynf.e

Návod k montázi



SON-T 50W	12	25	-20	66	●	●	7
SON-T 70W	12,5	25	-20	66	●	●	7
SON-T 100W	12,7	25	-20	66	●	●	7
SON-T 150W	13,3	25	-20	66	●	●	7
SON-T 250W	13,5	25	-20	66	●	●	3
CDO-TT 70W	12,5	25	-20	66	●	●	7
CDO-TT 100W	12,5	25	-20	66	●	●	7
CDO-TT 150W	13,3	25	-20	66	●	●	7
CDO-TT 250W	14	25	-20	66	●	●	3
CDM-T 70W	12,5	25	-20	66	●	●	7
CDM-T 150W	13	25	-20	66	●	●	7
CDM-T 250W	13,5	25	-20	66	●	●	1
CPO-T 45W	11	25	-20	66	●	●	5
CPO-T 60W	11	25	-20	66	●	●	5
CPO-T 90W	11	25	-20	66	●	●	5
CPO-T 140W	11	25	-20	66	●	●	5
PL-T 32W	11,2	25	-20	66	●	●	3
PL-T 42W	11,2	25	-20	66	●	●	3
PL-T 57W	10,4	25	-20	66	●	●	3
QL 55W	11	25	-20	66	●	●	8
QL 85W	11	25	-20	66	●	●	8


Standard Post Top



SCx 0.053 m² max.

SCx 0.073 m² max.

Standard Side Entry




SCx 0.053 m² max.

SCx 0.073 m² max.




Standard Post Top Tilttable



SCx 0.053 m² max.

SCx 0.073 m² max.

Suspended



SCx 0.063 m² max.




SCx 0.063 m² max.

Use Philips lamps for optimum performance


- Fonctionnement optimal avec lampes Philips
- Optimale Bestriebsleistung mit Philips-Lampen
- Toimii parhaiten Philips-lamppujen kanssa
- Fungerar bäst med lampor från Philips

- Funzionamento ottimale garantito con lampade Philips
- Funciona melhor com lâmpadas Philips no interior
- Fungerer bedst med Philips-lamper


- Werkt het best met Philips-lampen
- Resultados óptimos con lámparas Philips
- Fungerer mest optimalt med Philips-lamper




STANDARD




SUSPENDED








SIDE ENTRY




POST TOP






	P3 Electromagnetic		P3 Electronic	

Functional ground
 Security ground
 C : Control line N : Neutral line L : Phase



CHRONOSENSE



1 2 3 4 5 6 7 8									
T1			T2			TEST MODE			
1	2	3	4	5	6	7	8		
3H30	☐	☐	☐	5H30	☐	OFF	☐		
3H00	☐	☐	☐	5H00	☐	1	☐		
2H30	☐	☐	☐	4H30	☐	2	☐		
2H00	☐	☐	☐	4H00	☐			TEST MODE 1	
1H30	☐	☐	☐					1 H = 1 mn	
1H00	☐	☐	☐					TEST MODE 2	
0H30	☐	☐	☐					60 sec. 100%	
0H00	☐	☐	☐					5 sec. 50%	

