



TTX400



PHILIPS

TTX400	P 3-4
TTX400 CM-CU-CL	P 5
TTX400 CM-CU	P 6-9
ZTX400 CPX	P 10-13
TTX400 2C	P14
TTX410	P15
ZTX410 CPX	P16-17
TTX400 CU M	P 18
ZTX400 ECP	P 18
TMX400 - TMX407	P19
TMX400 EL	P 20
TMX400 M+S	P 21
GMX 430/450 + GGX	P 22
GMX 460-465-466-467-470	P 23
GMX 562-564-565-566-567-570	P 23
GGX555 C-BD +C-A	P24-25
GMX555 + OPTICS	P26
ZTX400 NE-E27	P 27
ZTX400 MDU HFP / HFD	P 28-29
TMX 400 C-2R	P 30
SERVICE	P 31



TTX400 / TTX410




WARNING :

For applications subject to vibration , additional trunking fixings and reflector fixings are required . Details of these extra fixings are available on request



TTX400




TTX400 CM-CU-CL







TTX400 CM-CU








TTX400 CM-CU + ZTX400 CP




ZTX400 CPX









TTX400 2C





TTX410



TTX410 LB / WB





WARNING : For applications subject to vibration , additional trunking fixings and reflector fixings are required . Details of these extra fixings are available on request




TTX400 CU M


ZTX400 CPE




TMX400




TMX407




TMX400 EL



TMX400 M+S





GMX 430/450 + GGX





GMX 460-465-466-467-470

GMX 562-564-565-566-567-570







GMX555/GGX555 C-BD-20	GMX555/GGX555 C-BD-40	GMX555/GGX555 C-A-20	GMX555/GGX555 C-A 40
 PHILIPS 20°	 PHILIPS 40°	 PHILIPS 20°	 PHILIPS 40°
 PHILIPS 20°	 PHILIPS 40°	 PHILIPS 20°	 PHILIPS 40°



GMX555 + OPTICS



ZTX400 NE E27



AWG 26 RJ-12 (6p/6c)

4a 4b

Pin/core	Colour wire	Function
1	White	+12V supply
2	Black	GND
3	Red	-
4	Green	Light sensor / Luxsense
5	Yellow	-
6	Blue	Movement detector

5a 5b

7,5 - 8,5

1,5 - 2,5 mm²

Distance between movement detectors for optimal coverage

ZTX400 MDU HFD	max. 4x LRM 8117
ZTX400 MDU HFP	max. 3x LRM 8117, LED OFF max. 2x LRM 8117, LED ON

Position door !


Coverage as function of mounting height LRM 8117

Height [m]

Coverage [m]

2 x LRM 8117
3 x LRM 8117
4 x LRM 8117

ZTX400 MDU HFD




DEFAULT SETTING:
DIP SWITCH 3 AND 4: OFF

See Datasheet LLC1650
www.controls4lighting.com

Un-occupied light level	DIP switch	
	1	2
0% [OFF]	OFF	OFF
10%	ON	OFF
20%	OFF	ON
30%	ON	ON

TMX400 C-2R



SERVICE

