

StyliD Mini / Compact

Installation instructions

Instructions de montage

Montageanleitung

Montage instruktio

Instruzioni di montaggio

Instrucciones de montaje

Instrues de montage

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet

Montaj yönergesi

Οδηγίες εγκατάστασης

Instrukcja montazu

Szerelési utasítások


Návod k montáži

инструкция по монтажу

Návod k montáži



Housing	Lum. Pack	CCT							BEAM ANGLE		
									NB	MB	WB
ST730T StyliD Mini track mounted	LED11S	827	0.8	17.6	•	•	•	•	•		
		830/840	0.8	15.6	•	•	•	•	•		
		930	0.8	18.8	•	•	•	•	•		
ST730C StyliD Mini Surface mounted	LED12S	827/830/840	0.8	13.4	•	•	•	•		•	•
		930	0.8	16	•	•	•	•		•	•
ST740T StyliD Compact track mounted	LED17S	827/830/840	1.1	17.2	•	•	•	•		•	•
		930	1.1	22	•	•	•	•		•	•
	LED20S	827/840	1.2	28.5	•	•	•	•	•		
		830/930	1.2	29	•	•	•	•	•		
	LED27S	827/830/840/930	1.2	27	•	•	•	•		•	•
		930	1.2	34.5	•	•	•	•		•	•
	LED39S	827/830/840	1.2	42	•	•	•	•		•	•
		930	1.2	41.5	•	•	•	•		•	•



4443 160 07912



Version date : 07/05/2015

Data Subject to change without notice



Printed in EU

www.philips.com/lighting


ST730C / ST740C INSTALLATION



MAIN CABLE FOR PSE and PSD (DALI) DRIVER




DALI CABLE FOR PSD (DALI) DRIVER





ST730T / ST740T INSTALLATION

ST730T PSE/ ST740T PSE


Installation



Uninstallation




GLOBAL Trac Pro





ST730T PSED/ ST740T PSED

Installation





Uninstallation



GAC
600 dali
1A 50V FELV




GLOBAL Trac Control PULSE








Rotation maintenance

PLEASE TAKE CARE OF MARKED AREA,
AVOID FINGERPRINTS!





Installation of accessories



Xitanium 25W LH 0.3-1A 36V I 230V (PSE)			Xitanium 20W LH 0.15-0.5A 48V TD/Is 230V (PSED)			Xitanium 25W LH 0.3-1A 36V TD Is 230V (PSED)			Xitanium 36W LH 0.3-1A 48V I 230V (PSE)		
Lum. Pack	CCT	Inom. (A)	Lum. Pack	CCT	Inom. (A)	Lum. Pack	CCT	Inom. (A)	Lum. Pack	CCT	Inom. (A)
LED11S	827	0.073	LED12S	827/830/840	0.054	LED11S	827	0.073	LED20S	827/830/840	0.115
	830/840	0.065		930	0.064		830/840	0.065		930	0.117
	930	0.078	LED17S	827/830/840	0.069		930	0.078	LED27S	930	0.136
LED12S	830/840/840	0.053				LED17S	930	0.089	LED39S	827/930	0.167
	930	0.064					827/830/840	0.108		830/840	0.169
LED17S	830/840/840	0.069									
	930	0.089									
LED27S	830/840/840	0.108									
I _{max} (A)	8		I _{max} (A)	16		I _{max} (A)	20		I _{max} (A)	20	
T _{ref} (us)	0.18		T _{ref} (us)	0.22		T _{ref} (us)	0.15		T _{ref} (us)	0.25	
MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*	
B-10A	15		B-10A	15		B-10A	18		B-10A	20	
B-16A	24		B-16A	24		B-16A	30		B-16A	32	
C-10A	24		C-10A	24		C-10A	31		C-10A	33	
C-16A	40		C-16A	40		C-16A	51		C-16A	54	

Xitanium 36W 0.3- 1A 48V		
Lum. Pack	CCT	Inom. (A)
LED20S	827/830/840	0.115
	930	0.117
LED27S	930	0.136
LED39S	827/930	0.167
	830/840	0.169
I _{max} (A)	5.3	
T _{ref} (us)	0.7	
MCB	Max. Products (pcs)*	
B-10A	15	
B-16A	24	
C-10A	24	
C-16A	40	



*According to: IEC60555 test conditions

StyliD PERFORMANCE

Installation instructions

Instructions de montage

Instrucciones de montaje

Kokoonpano- ja kiinnitysohjeet

Szerelési utasítások

Montageanleitung

Instrues de montage

Montaj yönergesi

Návod k montáži

Montage instructie

Monteringsinstruktioner

Οδηγίες εγκατάστασης

инструкция по монтажу

Istruzioni di montaggio

Monteringsvejledning





Instrukcja montażu

Návod k montáži




kg P max 10°C min max 40°C 650°C IK02 BEAM ANGLE NB MB WB VWB LIN													
Housing	Lum. Pack	CCT											
ST750T StyliD Performance track mounted	LED39S	827/830/840	1.5	37	•	•	•	•		•	•	•	•
		930	1.5	49	•	•	•	•		•	•	•	•
	LED40S	827/830/840	1.5	58	•	•	•	•	•				
		930	1.5	59	•	•	•	•	•				
	LED49S	827/830/840	1.5	50	•	•	•	•		•	•	•	•
		930	1.5	59.5	•	•	•	•		•	•	•	•
ST750C StyliD Performance surface mounted	LED39S	827/830/840	1.6	37	•	•	•	•		•	•	•	•
		930	1.6	49	•	•	•	•		•	•	•	•
	LED40S	827/830/840	1.6	58	•	•	•	•	•				
		930	1.6	59	•	•	•	•	•				
	LED49S	827/830/840	1.6	50	•	•	•	•		•	•	•	•
		930	1.6	59.5	•	•	•	•		•	•	•	•

ST750C INSTALLATION




Wirings for PSE and PSED drivers

PSE – Power supply unit DC-compatible for central emergency lightning.




Mains cable
~220-240V




A: 0.5-1.5mm²



PSED – Power supply unit with DALI interface DC-compatible for central emergency lightning.




DALI cable




A: 0.5-1.5mm²

CABLE FOR POWER SUPPLY
~220-240V




A: 0.5-1.5mm²

ST750T INSTALLATION




ST750T PSE




Installation



Uninstallation




GLOBAL Trac Pro





ST750T PSED

Installation





Uninstallation



GAC
600 dali
1A 50V FELV




GLOBAL Trac Control PULSE




Rotation maintenance

PLEASE TAKE CARE OF MARKED AREA,
AVOID FINGERPRINTS!




Installation of accessories

ST550Z GS




Glare Shield GS


a.



c.




ST550Z HC




Honeycomb HC


b.



d.



Xitanium 50W LH 0.7-1.5A 48V TD/I 230V (PSE,PSED)			Xitanium 36W 0.3-1A 48V TD/I 230V (PSE,PSED)		
Lum. Pack	CCT	I _{nom.} (A)	Lum. Pack	CCT	I _{nom.} (A)
LED39S	930	0.154	LED39S	827/830/840	0.154
LED40S	827/830/930	0.183			
	840	0.181			
LED49S	827/830/840	0.156			
	930	0.183			
I _{max.} (A)	5.3		I _{max.} (A)	5.3	
T _{ref.} (us)	0.7		T _{ref.} (us)	0.7	
MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*	
B-10A	18		B-10A	15	
B-16A	30		B-16A	24	
C-10A	31		C-10A	24	
C-16A	51		C-16A	40	



*According to: IEC60555 test conditions