





PHILIPS

Philips Lighting Electronics (Shanghai) Co., Ltd.
All rights reserved. No part is
permitted without the written consent of the copyright owner.



GB/T 1804-2000m (Unit: mm)									
SIZE RANGE	0.5-3	>3-6	>6-30	>30-120	>120-400	>400-1000	ITEM	ASSEMBLY NO.	QUANT.
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8			
GENERAL ROUGHNESS	<div>UNIT: mm</div> <div>MATERIAL:</div>						MODEL NAME		
<div>✓</div>									
SCALE	<div>PROJECT TYPE:</div> <div>TREATMENT:</div>						ORDER NO.	QUANT.	
<div></div>									
TITLE: <div>Actilume Sensor Assembly</div>						PART NUMBER:		1	2010/7/22 A
REV. CHANGE NO. DATE									
DESIGNED BY Yugui Xu		CHECKED BY		1	SH.	SH. 110 of 1		FORM NO.	A3
DRAWN BY		APPROVED BY		REVISED BY		PHILIPS LIGHTING ELECTRONICS (SHANGHAI) CO., LTD			