

**PHILIPS
LUMEC**

Urban

L40U Lantern

L40U/L40U-STM



Distinguished touch of yesteryear

The Philips Lumec L40U LED post top and pendant luminaires create a warm and friendly ambiance with its design while at the same time offering high-end technology and photometric performance. Evoking a distinguished touch of yesteryear, the L40 LED lanterns deliver an encompassing light that is warm and safe.



L40U Lantern

LED luminaires

The Philips Lumec L40U LED post top and pendant luminaires offer a blend of form and function that make them an excellent choice for any environment.

Prior to ordering, consult spec sheets for the most current info, notes, and exclusions.



Benefits

- Post top and pendant versions available to suit a wide range of applications.
- Multiple lumen packages with output of up to 9,457 lumens.
- Type 2, 3, 4, & 5 optics available.
- Highly efficient IP66 optics are protected from the elements and ensure optimal photometric performance.
- Color temperatures 4000K and 3000K are available.
- Dimming driver is standard.
- Maximizes energy savings with multiple driver options and programmed dimming options.



Lumen range: 2,813-9,457

Wattage range: 37-106

Efficacy range: 76-95

Post top




L40U

Pendant




L40U-STM

Dimensions



L40U

EPA: 0.47 sq. ft.
Weight: 30 lbs (13.6 kg)



L40U-STM

EPA: 0.83 sq. ft.
Weight: 55 lbs (25 kg)

© 2017 Philips Lighting Holding B.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008