

Philips ClearWay BGP303

Mounting instruction

Instructions de montage
Montageanleitung
Montage instruktio
Instruzioni di montaggio

Instrucciones de montaje
Instruções de montagem
Monteringsinstruktioner
Monteringsvejledning


Kokoonpano- ja kiinnitysohjeet
Montaj yönergəsi
Návod k montáži
Instrukcja montażu

Szerelési utasítások



~220V...240V

50/60Hz



IEC
EN60598

4-6 m

IP66

IK08




max
35°C
-30°C
min

		W +/-11%	 740 MCB B 16A	Inrush current	W +/-11%	 830 MCB B 16A	Inrush current
LED18-3S	6,5	16	18	27A/290µs	-	-	-
LED23-3S	6,5	20	18	27A/290µs	-	-	-
LED35-3S	6,5	29	18	27A/290µs	-	-	-
LED49-3S	7,2	44	11	46A/250µs	-	-	-
LED73-3S	7,2	58	11	46A/250µs	-	-	-
LED98-3S	7,2	80	8	53A/300µs	-	-	-
LED122-3S	7,2	110	8	53A/300µs	-	-	-
LED18-4S	6,5	14	18	27A/290µs	17	18	27A/290µs
LED25-4S	6,5	18	18	27A/290µs	22	18	27A/290µs
LED30-4S	6,5	21	18	27A/290µs	26	18	27A/290µs


		W +/-11%	 740 MCB B 16A	Inrush current	W +/-11%	 830 MCB B 16A	Inrush current
LED35-4S	7,2	24	11	46A/250µs	29	11	46A/250µs
LED40-4S	7,2	27	11	46A/250µs	33	11	46A/250µs
LED45-4S	7,2	30	11	46A/250µs	38	11	46A/250µs
LED54-4S	7,2	40	18	27A/290µs	46	11	46A/250µs
LED69-4S	7,2	48	11	46A/250µs	62	11	46A/250µs
LED84-4S	7,2	61	11	46A/250µs	73	8	53A/300µs
LED99-4S	7,2	69	8	53A/300µs	-	-	-
LED109-4S	7,2	77	8	53A/300µs	-	-	-
LED120-4S	7,2	87	8	53A/300µs	-	-	-



Disconnect before servicing
Mettre hors tension avant intervention
Öffnen nur spannungsfrei
Demonteren voor onderhoud
Togliere tensione prima di fare manutenzione
Desconectar antes de manipular
Bryt strömmen före lampbyte




330




481


97



5




PH2



4






Scx 0,016 m²
max.


Scx 0,029 m²
max.






536

98






Version without cable:




Version with cable:


13



14




...DDFx... - DYNADIMMER




15

...LS-x... - LUMISTEP



16

SRG10
10kV protection



17

