

# BSP 390


## Mounting instructions

Instructions de montage  
Montageanleitung  
Montage instrukcie  
Istruzioni di montaggio

Instrucciones de montaje  
Instruções de montagem  
Monteringsinstruktioner  
Monteringsvejledning


Kokoonpano- ja kiinnitysohjeet  
Montaj yönergeleri  
Οδηγίες συναρμολόγησης  
Instrukcja montażu

Szerelési utasítások  
Návod k montáži  
Монтажная инструкция






BSP 390		830	W +/- 10%	LED	740	W +/- 10%	LED	kg	max 35°C	m <sup>2</sup>	max Ta
ECO35	32	16	-	-	-	-	-	16	●	0.07m <sup>2</sup>	● 35°C
ECO46	42	24	ECO42	30	24	16	●	0.07m <sup>2</sup>	● 35°C		
ECO58	51	32	ECO57	43	24	16	●	0.07m <sup>2</sup>	● 35°C		
ECO70	64	32	ECO71	54	28	16	●	0.07m <sup>2</sup>	● 35°C		
ECO81	72	48	ECO85	64	36	16	●	0.07m <sup>2</sup>	● 35°C		
ECO93	84	48	ECO99	76	40	16	●	0.07m <sup>2</sup>	● 35°C		
ECO104	96	48	ECO113	85	48	16	●	0.07m <sup>2</sup>	-		
ECO116	103	64	ECO127	95	56	16	●	0.07m <sup>2</sup>	-		
ECO128	116	64	ECO142	108	56	16	●	0.07m <sup>2</sup>	-		
ECO139	128	64	ECO156	118	64	16	●	0.07m <sup>2</sup>	-		




BSP 390		830	W +/- 10%	LED	740	W +/- 10%	LED	kg	max 35°C	m <sup>2</sup>	max Ta
GRN32	27	16	GRN29	21	16	16	●	0.07m <sup>2</sup>	● 35°C		
GRN40	34	32	GRN39	27	32	16	●	0.07m <sup>2</sup>	● 35°C		
GRN48	41	32	GRN49	34	32	16	●	0.07m <sup>2</sup>	● 35°C		
GRN56	47	48	GRN59	40	48	16	●	0.07m <sup>2</sup>	● 35°C		
GRN64	54	48	GRN68	47	48	16	●	0.07m <sup>2</sup>	● 35°C		
GRN72	60	64	-	-	-	16	●	0.07m <sup>2</sup>	● 35°C		
GRN80	69	64	GRN78	55	48	16	●	0.07m <sup>2</sup>	● 35°C		
GRN88	74	64	GRN88	60	64	16	●	0.07m <sup>2</sup>	● 35°C		






# BSP390 C5K







# BSP390 JB






3










**LUMISTEP**



**DYNADIMMER**



RF



**PHILIPS**  
LLC7300 9137 003 420  
Starsense Wireless  
I - IOV/DALI

U i	220 - 240V	PFTYYWW
f i	50 - 60 Hz	N
t i	-30 ... +65°C	L
t i	80°C	L1
p	i 480VA	I - IOV/DALI+
		I - IOV/DALI-

Made in Poland

000981379400

000981379400

000981379400

000981379400

