




# RS010 SPOT




	LEDs	Output(lm)	P(W)	Ø mm	kg
RS010B LED5 fixed	5x LED	500	6,0	65	0,14
RS011B LED5 adjustable	5x LED	500	6,0	65	0,14
RS011B LED8 adjustable	10x LED	800	8,5	76	0,16


## Fixed LED5



## Adjustable LED5




## Adjustable LED8







Fixed= Ø65mm  
Adjustable= Ø76mm




1a



1b





2a





2b




Ø6-13mm




2c




3a



3b



3c



The luminaire shall, under no circumstances, be covered with insulating matting or similar material. !

4

Only to be installed outside arms reach as recessed ceiling luminaire.  
If the external flexible luminaire cable or cord is damaged, it shall be exclusively repaired/replaced by the manufacturer or his service agent or a similar qualified person in order to avoid hazard.  
For complete and updated list of advised dimmers, please check the RS010 Spot page on the Philips Lighting eCatalog: <http://www.ecat.lighting.philips.com>