iW Graze EC Powercore

Cost-effective linear exterior LED wall grazing luminaires with intelligent white light

iW Graze EC Powercore is a cost-effective high-performance, exterior linear luminaire designed to highlight architectural features ranging from surface textures and molding details to archways and windows. Graze Intelligent White luminaires offer channels of cool, neutral, and warm white LEDs to offer color temperatures ranging from 2700 K to 6500 K. Multiple luminiare lengths, beam angles, output levels, and power consumption levels support a large range of façade or surface illumination applications. Low-profile housing, connectorized cabling, a universal power input range, and direct line voltage operation make Graze luminaires easy to install and operate.

- Tailor light output to specific applications—Available in four standard lengths (1 ft, 2 ft, 3 ft, and 4 ft), four performance levels (MX, QLX, QLX 5W, and EC), and six standard 9° x 9°, 10° x 60°, 15° x 30°, 30° x 60°, 60° x 30°, and 90° x 90° (EC only) beam angles.
- Flexible integration—Graze's ultra-low profile lets it fit discretely into almost any layout, from simple to elaborate.

Date:	
Туре:	
Firm Name:	
Project:	



Product page

Beam Angle	90° x 90					
Lumens per foot*	412					
Efficacy [†]	29.6					
Color Temperature ^s	2700 K to 6500 K					

Input Voltage	100 to 277 VAC, auto-ranging, 50/60 Hz
Housing Material	Extruded anodized aluminium
Approbations	UL/cUL, FCC Class A, CE, PSE, C-Tick
Environment	Dry/Damp/Wet Location, IP66
Applications	Wall Grazing, Wall Washing

Specification Sheets

PDF Download	Beam Angle	Lumens*	Efficacy [†]	CRI‡	Power	Weight	ltem Number	12 NC
90° x 90° Beam Angle, 305 mm (1 ft)	90° x 90°	412	29.6	82	10 W	1 kg (2.1 lb)	523-000079-40	910503703684
<u>90° x 90° Beam Angle, 610 mm (2 ft)</u>	90° x 90°	824	29.6	82	20 W	2.1 kg (4.6 lb)	523-000079-41	910503703685



Specification Sheets (cont.)

PDF Download	Beam Angle	Lumens*	Efficacy [†]	CRI‡	Power	Weight	ltem Number	12 NC
90° x 90° Beam Angle, 914 mm (3 ft)	90° x 90°	1,236	29.6	82	30 W	3.2 kg (7.1 lb)	523-000079-42	910503703686
<u>90° x 90° Beam Angle, 1219 mm (4 ft)</u>	90° x 90°	1,648	29.6	82	40 W	4.2 kg (9.3 lb)	523-000079-43	910503703687

* 305 mm (1 ft) lumen output measurements comply with IES LM-79-08 testing procedures. 610 mm (2 ft), 914 mm (3 ft), and 1219 mm (4 ft) measurements are estimated based on the 305 mm (1 ft) ¹ Efficacy measurements.
¹ Efficacy measurements are estimated based on the 305 mm (1 ft) measurements.
³ Correlated color temperature (CCT) complies with ANSI C78.377-2008 for the chromaticity of solid state lighting products.
⁴ CRI refers to CRI Ra value, CRI R9 refers to R9 value in accordance with IESNA LM-79 standards.



© 2019 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.