

Philips Lighting



EU Declaration of Conformity

Document No.: 0123/A/18

Year in which CE Mark was first affixed: 18

Manufacturer: Philips Lighting

I.B.R.S./C.C.R.I./Numero 10462

5601 VB Eindhoven, The Netherlands

This declaration of conformity is issued under the sole responsibility of the manufacturer.

Product Range:	NAME: FlexBlend - see Annex DESCRIPTION: Luminaires for emergency lighting
Product Code:	RC340B...EL... 220-240V 50/60Hz PF>0.9 IP20, IP54 (for PCS, OPAL version only) Ta25°C

The designated product(s) is (are) in conformity with the following Union harmonization legislation and with the applicable requirements of the following harmonized standards and technical specifications:

Low Voltage Directive (LVD), 2014/35/EU

- EN 60598-1:2015+AC:2015+AC:2016
- EN 60598-2-2:2012
- EN 60598-2-22:2014+AC:2015

Electromagnetic compatibility Directive (EMC), 2014/30/EU

- EN 55015:2013 (CISPR 15:2013+ IS1:2013 + IS2:2013)
- EN 61000-3-2:2014
- EN 61000-3-3:2013
- EN 62493:2015

EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures

- 1194/2012

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU

- EN 50581:2012

and is/are produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.

Eindhoven, October 19, 2018
High Tech Campus 48
5656 AE Eindhoven The Netherlands

Peter Linssen
Head of Quality
RBU Prof Europe

SIGNATURE


Philips Lighting



EU Declaration of Conformity

Document No.: 0123/A/18

RC341B LED36S/840 PSD-T W15L180 BCV PCS SWZ ELD1 W4 AIR SB2 SC



1	RC340B	
1	RC341B	Recessed Luminaire (Housing type, geometry body)
1	RC342B	
1	RC343B	

LUMEN OUTPUT

2	LED28S	2800lm
2	LED36S	3600lm
2	LED42S	4200lm

COLOUR LAMP

3	830	Warm White (3000K)
3	840	Neutral White (4000K)

LIGHT REGULATION

4	PSD	power supply driver-dimmable (DALI)
4	PSU	power supply driver- non-dimmable
4	PSD-CLO	power supply driver-dimmable (DALI) – CLO
4	PSD-T	power supply driver-dimmable (DALI) & Touch Switch
4	SRD	power supply driver-System Ready interface
4	POE	power supply driver-Power over Ethernet

DIMENSIONS

5	W60L60	Square 597x597mm
5	W30L120	Rectangular 297x1197
5	W62L62	Square 617x617mm
5	W67L67	Square 667x667mm
5	W15L120	Rectangular 147x1197
5	W15L125	Rectangular 147x1247
5	W17L125	Rectangular 167x1247
5	W15L180	Rectangular 147x1797
5	W30L135	Rectangular 297x1347
5	W31x125	Rectangular 307x1247

VERSION

6	PCV	Plaster Ceiling Version
6	CPC	Concealed Profile Ceiling
6	VPC	Visual Profile Ceiling
6	FLC	Fineline Ceiling
6	BCV	Bandraster

Philips Lighting



EU Declaration of Conformity

Document No.: 0123/A/18

OPTICS

7	PCS	Poly Textured Structure
7	O	Non- office compliant
7	MLO	Office compliant MLO

LIGHT CONTROL UNIT

8	SWZ	Space Wise
8	IA3	InterAct Office

EMERGENCY MODULE

9	ELB1	Emergency Lighting 1 hours (Emergency Lighting Module with TrustSight Basic)
9	ELB3	Emergency Lighting 3 hours (Emergency Lighting Module with TrustSight Basic)
9	ELP1	Emergency Lighting 1 hours (Emergency Lighting Module with TrustSight PRO)
9	ELP3	Emergency Lighting 3 hours (Emergency Lighting Module with TrustSight PRO)
9	ELD1	Emergency Lighting 1 hours (Emergency Lighting Module with TrustSight DALI)
9	ELD3	Emergency Lighting 3 hours (Emergency Lighting Module with TrustSight DALI)
9	ELE1	Emergency Lighting 1 hours (Emergency Lighting Module with POE controller)
9	ELE3	Emergency Lighting 3 hours (Emergency Lighting Module with POE controller)

CONNECTION

10	PIP	Push-in with pull relief
10	W	Wieland GST18
10	W4	Wieland GST18/4

AIR HANDLING

11	AIR	Air - handling
----	-----	----------------

SAFETY BRACKET

12	SB1	Safety bracket GPS100
12	SB2	Safety bracket Standart BCV
12	SB3	Safety bracket C/U profile BCV

SAFETY DEVICE

13	SC	Safety Cable
----	----	--------------