




GreenSpace Accent Elbow


Installation instructions

Instructions de montage	Instrucciones de montaje	Kokoonpano- ja kiinnitysohjeet	Szerelési utasítás
Montageanleitung	Instruções de montagem	Montaj yönergesi	Návod k montáži
Montage instructie	Monteringsinstruktioner	Odhgjez synarmologhshz	Инструкция по монтажу
Instruzioni di montaggio	Monteringsvejledning	Instrukcja montazu	Návod k montáži




														
														
RS342B LED19S/FMT PSU-E	•	•	•	•	•	•	0°C	35°C	1,25 kg	36W	•	•		
RS342B LED19S/FMT PSD-E	•	•	•	•	•	•	0°C	35°C	1,25 kg	36W	•	•		
RS342B LED27S/CH PSU-E	•	•	•	•	•	•	0°C	35°C	1,25 kg	51W	•	•		
RS342B LED27S/CH PSD-E	•	•	•	•	•	•	0°C	35°C	1,25 kg	51W	•	•		




Minimal build-in dimensions



1.





Optical unit changing, and cleaning instructions





2.


Only with soft cloths!






Wirings for LED19S/FMT PSU-E driver



Wirings for PSD-E driver and LED27S/CH PSU-E driver



CABLE FOR POWER SUPPLY
~220-240V



LED19S/FMT PSU-E		LED19S/FMT PSD-E		LED27S/CH PSU-E		LED27S/CH PSD-E	
LED driver 36W 0.3-1A 48V I 230V		XITANIUM 36W LH 0.3-1A 48V TD/I 230V		Xitanium 50 W LH 0.7-1.5 A 48 V TD/I 230 V		Xitanium 50 W LH 0.7-1.5 A 48 V TD/I 230 V	
Inom[A]	0.152	Inom[A]	0.141	Inom[A]	0.228	Inom[A]	0.228
I _{max} [A]	6	I _{max} [A]	5.3	I _{max} [A]	5.3	I _{max} [A]	5.3
Tref[us]	0.055	Tref[us]	0.7	Tref[us]	0.7	Tref[us]	0.7
MCB	Max products [pcs]*	MCB	Max products [pcs]*	MCB	Max products [pcs]*	MCB	Max products [pcs]*
B-16A	40	B-16A	24	B-16A	30	B-16A	30

* According to IEC60555 test conditions