



HNF901

Mounting instruction 安装说明





Type Number 产品型号	Lamp 光源		Referect 反射器	Bracket 安装支架	
HNF901 Narrow	SON-T250W	1m 2m (1000W)	Narrow bean	Standerd	8
HNF901 Wide	SON-T400W		Wide bean	Standerd	8
HNF901 Narrow BKT	HPI-T250W HPI-T400W SON-T1000W		Narrow bean	Heavy duty	9



Warning: For SON-T 1000W lamp, only use to fit into 230V/ 240V/ 50Hz.

When supply voltage to be 230V/50Hz, the lamp's life is 8500 hours.




警告：当供应电压是230V/50Hz时，SON-T1000W光源的寿命是8500小时。



Philips Lighting Luminaires (Shanghai) Co., Ltd.
Address: No. 2688, Huayi Road, Jiading, Shanghai, China
Postalcode: 201801

飞利浦灯具（上海）有限公司
地址：中国上海市嘉定区马陆镇沪宜公路2688号
邮编：201801

PHILIPS



Do not cover the luminaire with combustible.
灯具不允许被可燃物覆盖。