

Installation instructions

Instructions de montage

Instrucciones de montaje

Kokoonpano- ja kiinnitysohjeet

Szerelési utasítások

Montageanleitung

Instruções de montagem

Montaj yönergeleri

Návod k montáži

Montage instructie

Monteringsinstruktioner

Οδηγίες συναρμολόγησης




ИНСТРУКЦИЯ ПО МОНТАЖУ

Istruzioni di montaggio

Monteringsvejledning

Instrukcja montażu


Návod k montáži



		A	B	C-D	E	 Ta 25°	 Ta 35°	 IP.	 IP...	 kg
FWG251	2x PL-C/4PI8-26W HF	424	143	214x238		✓			65	1.90
	2x PL-C/4PI8W HF ELI									2.80
FWG201	1x PL-C/4PI8W HF	340	116	167x186						1.35
	2x PL-C/4PI8W HF									1.45
	1x MAX70W-E27 CL I I						X			1.30
	1x PL-C/4PI8W HF ELI						65		2.00	
FWG211	1x PL-C/4PI8-26W HF	292	87	135x135					65	0.95
	1x MAX53W-E27 CL I I									X
FWG221	1x PL-C/4PI8W HF	292	95	135x135					65	1.15
FWG231	1x PL-C/4PI8W HF	296	87	76x144	174					0.85
FWG241	1x PL-C/4PI8W HF	296	98	76x144	174		0.95			
BWG201 (24W)	1x LED700/830 PSU	340	116	167x186		✓	1.70			
	1x LED700/840 PSU						1.70			


FWG201 / BWG201(LED)

FWG201(E27)⇒




FWG211 / FWG221

FWG211(E27)⇒



FWG251



FWG231
FWG241

