

CoreLine Recessed Spot RS140



220V
240V

50Hz
60Hz



LEDs

IK02


Max.
35 °C
Min.
0 °C

GLOW
WIRE
650 °C










	P(W)	Ø mm	kg
RS140B LED6S fixed	10	78	0.54
RS141B LED6S adjustable	10	80	0.56
RS141B LED7S adjustable	16	80	0.56
RS141B LED12S adjustable	16	80	0.56

Fixed



Adjustable





- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- Only to be installed outside arms reach as recessed ceiling luminaire.
- For complete and updated list of advised dimmers, please check the CoreLine Recessed Spot RS140 page on the Philips Lighting eCatalog: <http://www.ecat.lighting.philips.com>