







SMTT









SMS



Philips Lighting
www.philips.com

4422 003 41084
07/10
Printed in the Netherlands
Data subject to change



Use Philips lamps for optimum performance
Funzionamento ottimale garantito con lampade Philips
Resultados óptimos con lámparas Philips
Toimii parhaiten Philips-lamppujen kanssa
Funciona melhor com lâmpadas Philips no interior
Werkt het best met Philips-lampen

Fonctionnement optimal avec lampes Philips
Bestes Betriebsergebnis mit Philips-Lampen
Fungerer bedst med Philips-lamper
Fungerer mest optimalt med Philips-lamper
Fungerar bäst med lampor från Philips

SmartForm TPS 460/ 462/ 464/ 466


Installation instructions

Instructions de montage
Montageanleitung
Montage instructie
Istruzioni di montaggio
Instruções de montagem
Montaj yönergeleri
Οδηγίες συναρμολόγησης
Instrukcja montażu
Kokoonpano- ja kiinnitysohjeet
Montaj yönergeleri
Οδηγίες συναρμολόγησης
Instrukcja montażu
Szerelési utasítások
Návod k montáži
ИНСТРУКЦИЯ ПО МОНТАЖУ
Návod k montáži

IP 20 - IP 40




This luminaire must be earthed.
Ce luminaire doit être mis à la terre.
Diese Leuchte muß geerdet werden.
Dit armatuur moet worden geaard.
Questa armatura deve essere collegata a terra.
La Luminaria debe estar conectada a tierra.

Class I




All dimensions are in mm


Power (W)	L	W1	W2	W3	A	C
25/28/50/54 W	1240	157	217	332	49	1186
32/35/45/49/73/80 W	1540	157	217	332	49	1486




SMT I




SMTT




SMT2




SMT1/SMT2



SMTT



SMS



PHILIPS

SMT1 / SMTT / SMT2 / SMS

L

—

BLACK / BROWN

⊕

—

YELLOW - GREEN

N

—

BLUE

DA

DA

L

—

BLACK

⊕

—

YELLOW - GREEN

N

—

BLUE

+

/

T

/

LL

/

LS

—

ORANGE / BROWN

-

/

NS

—

PURPLE / GREY


Viktigt !

Lederen med grøn/gul isolation må kun tilsluttes en klemme mærket


⊕

eller


⊖



SMT1 / SMTT / SMT2



SMS



SMT2

