


Electrical Specifications

IZT-2S54-D@120V							
Brand Name	MARK 7 0-10V						
Ballast Type	Electronic Dimming						
Starting Method	Programmed Start						
Lamp Connection	Series						
Input Voltage	120-277						
Input Frequency	50/60 HZ						
Status	Active						

Lamp Type	Num. of Lamps	Rated Lamp Watts	Min. Start Temp (°F/C)	Input Input Power Current (Watts) (Amps) (min/max)		Ballast Factor (min/max)	MAX THD %	Power Factor	Lamp Current Crest Factor	B.E.F.
* F54T5/HO	2	54	50/10	0.98	16/118	0.03/1.00	10	0.98	1.7	0.85
F54T5/HO/49W	2	49	60/16	0.91	16/109	0.03/1.00	10	0.98	1.7	0.92
FC12T5/HO	2	55	50/10	0.82	18/98	0.03/0.80	10	0.98	1.7	0.82
FT55W/2G11	2	55	50/10	0.90	16/108	0.03/0.80	10	0.98	1.7	0.74

Wiring Diagram




The wiring diagram that appears above is for the lamp type denoted by the asterisk (*)

Standard Lead Length (inches)

			in	cm.
in.	cm.			0111.
0	0	Yellow/B	ue	0
0	0	Blue/Wh	ite	0
0	0	Bro	wn	0
	0	Oran	ae	0
0	0		<u> </u>	0
0	0			0
	0	Black/Wh	nite	0
	0	Red/Wh	ite	0
	in. 0 0 0 0	0 0 0 0 0 0	0 0 Yellow/B 0 0 Blue/Wh 0 0 Bro 0 0 Orange/Bla 0 0 Black/Wh	0 0 Yellow/Blue 0 0 Blue/White 0 0 Orange

Enclosure



Enclosure Dimensions

COMPLIANT

OverAll (L)	Width (W)	Height (H)	Mounting (M)
16.70 "	1.18 "	1.00 "	16.34 "
16 7/10	1 9/50	1	16 17/50
42.4 cm	3 cm	2.5 cm	41.5 cm



Revised 07/31/13

Data is based upon tests performed by Philips Lighting N.A in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.

Philips Lighting Electronic N.A

10275 West Higgins Road Rosemont, IL 60018 Tel.: 800-322-2086 Fax: 888-432-1882 Customer Support/Technical Service: 800-372-3331 · OEM Support: 866-915-5886

PHILIPS ADVANCE

Electrical Specifications

Notes:

Section I - Physical Characteristics

1.1 Ballast shall be physically interchangeable with standard electromagnetic or standard electronic ballasts, where applicable.

1.2 Ballast shall be available in a plastic/metal can or all metal can construction to meet all plenum requirements.

1.3 Ballast shall be provided with poke-in wire trap connectors or integral leads color coded per ANSI C82.11.

Section II - Performance Requirements

2.1 Ballast shall be Programmed Start.

2.2 VZT-4PSP32-G ballast shall provide Independent Lamp Operation (ILO) allowing remaining lamp(s) to maintain full light output when one or more lamps fail.

2.3 Ballast shall be provided with integral protection circuitry to withstand connection of low voltage control leads to mains power supply. In this event, ballast shall default to maximum light output.

2.4 Ballast shall contain auto restart circuitry in order to restart lamps without resetting power.

2.5 Ballast shall operate from 50/60 Hz input source of 120V or 277V or 347V with sustained variations of +/- 10% (voltage and frequency). IntelliVolt models shall operate from 50/60 Hz input source of 120V through 277V with sustained variations of +/- 10% (voltage and frequency).
2.6 Ballast shall be high frequency electronic type and operate lamps at a frequency above 42 kHz to avoid interference with infrared devices and eliminate visible flicker.

2.7 Ballast shall have a Power Factor greater than 0.98 at full light output and greater than 0.90 throughout the dimming range for primary lamp.

2.8 Ballast shall have a minimum ballast factor of 1.00 (120V and 277V 1-3 lamp models) or 0.88 (120V and 277V 4 lamp models and 347V 2-3 lamp models) or 1.18 (277V 4 lamp HL models) at maximum light output and 0.03 at minimum light output for primary lamp.

2.9 Ballast shall provide for a Lamp Current Crest Factor of 1.7 or less.

2.10 Ballast input current shall have Total Harmonic Distortion (THD) of less than 10% when operated at nominal line voltage and 100% power.

2.11 Ballast shall have a Class A sound rating.

2.12 Ballast shall have a minimum starting temperature of 10C (50F) for primary lamp.

2.13 Ballast shall provide Lamp EOL Protection Circuit for all T5, T5/HO and CFL lamps.

2.14 Ballast shall control lamp light output from 100% - 3% relative light output for series operation T8 and CFL lamps, 100% - 10% relative light output for parallel operation T8 and 100% - 1% relative light output for T5/HO lamps.

2.15 Ballast shall ignite the lamps at any light output setting without first going to another output setting.

2.16 Ballast shall tolerate sustained open circuit and short circuit output conditions.

Section III - Regulatory Requirements

3.1 Ballast shall not contain any Polychlorinated Biphenyl (PCB).

3.2 Ballast shall be Underwriters Laboratories (UL) listed, Class P and Type 1 Outdoor; and Canadian Standards Association (CSA) certified where applicable.

3.3 Ballast shall comply with ANSI C62.41 Category A for Transient protection.

3.4 Ballast shall comply with ANSI C82.11 where applicable.

3.5 Ballast shall comply with the requirements of the Federal Communications Commission (FCC) rules and regulations, Title 47 CFR part 18, Non-Consumer (Class A) for EMI/RFI (conducted and radiated).

3.6 Ballast shall comply with NEMA 410 for in-rush current limits.

Section IV - Other

4.1 Ballast shall be manufactured in a factory certified to ISO 9001 Quality System Standards.

4.2 Ballast shall carry a five-year warranty from date of manufacture against defects in material or workmanship, including replacement, for operation at a maximum case temperature of 70C.

4.3 Manufacturer shall have a twenty-year history of producing electronic ballasts for the North American market.

4.4 Ballast shall be controlled by a Class 1 or Class 2 low voltage 0-10VDC controller.

IZT-2S54-D@120V							
MARK 7 0-10V							
Electronic Dimming							
Programmed Start							
Series							
120-277							
50/60 HZ							
Active							

4.5 Ballast shall be Philips Advance part # _____ or approved equal.





Revised 07/31/13

Data is based upon tests performed by Philips Lighting Electronic N.A. in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.

Philips Lighting Electronic N.A. 10275 West Higgins Road Rosemont, IL 60018 Tel.: 800-322-2086 Fax: 888-432-1882 Customer Support/Technical Service: 800-372-3331 OEM Support: 866-915-5886




Electrical Specifications

IZT-2S54-D@277V							
Brand Name	MARK 7 0-10V						
Ballast Type	Electronic Dimming						
Starting Method	Programmed Start						
Lamp Connection	Series						
Input Voltage	120-277						
Input Frequency	50/60 HZ						
Status	Active						

Lamp Type	Num. of Lamps	Rated Lamp Watts	Min. Start Temp (۴/C)	Input Current (Amps)	Input Power (Watts) (min/max)	Ballast Factor (min/max)	MAX THD %	Power Factor	Lamp Current Crest Factor	B.E.F.
* F54T5/HO	2	54	50/10	0.41	16/118	0.03/1.00	10	0.98	1.7	0.85
F54T5/HO/49W	2	49	60/16	0.38	16/109	0.03/1.00	10	0.98	1.7	0.92
FC12T5/HO	2	55	50/10	0.35	18/98	0.03/0.80	10	0.98	1.7	0.82
FT55W/2G11	2	55	50/10	0.38	16/108	0.03/0.80	10	0.98	1.7	0.74

Wiring Diagram




The wiring diagram that appears above is for the lamp type denoted by the asterisk (*)

Standard Lead Length (inches)

	in.	cm.		in.	cm.
Black	0	0	Yellow/Blue		0
White	0	0	Blue/White		0
Blue	0	0	Brown		0
	0	0	Orange		0
Red	0	0	Orange/Black		0
Yellow	0	0	Black/White		0
Gray		0	Red/White		0
Violet		0	Tred/White		0





Enclosure Dimensions

COMPLIANT

OverAll (L)	Width (W)	Height (H)	Mounting (M)
16.70 "	1.18 "	1.00 "	16.34 "
16 7/10	1 9/50	1	16 17/50
42.4 cm	3 cm	2.5 cm	41.5 cm



Revised 07/31/13

Data is based upon tests performed by Philips Lighting N.A in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.

Philips Lighting Electronic N.A

10275 West Higgins Road Rosemont, IL 60018 Tel.: 800-322-2086 Fax: 888-432-1882 Customer Support/Technical Service: 800-372-3331 · OEM Support: 866-915-5886

PHILIPS ADVANCE

Electrical Specifications

Notes:

Section I - Physical Characteristics

1.1 Ballast shall be physically interchangeable with standard electromagnetic or standard electronic ballasts, where applicable.

1.2 Ballast shall be available in a plastic/metal can or all metal can construction to meet all plenum requirements.

1.3 Ballast shall be provided with poke-in wire trap connectors or integral leads color coded per ANSI C82.11.

Section II - Performance Requirements

2.1 Ballast shall be Programmed Start.

2.2 VZT-4PSP32-G ballast shall provide Independent Lamp Operation (ILO) allowing remaining lamp(s) to maintain full light output when one or more lamps fail.

2.3 Ballast shall be provided with integral protection circuitry to withstand connection of low voltage control leads to mains power supply. In this event, ballast shall default to maximum light output.

2.4 Ballast shall contain auto restart circuitry in order to restart lamps without resetting power.

2.5 Ballast shall operate from 50/60 Hz input source of 120V or 277V or 347V with sustained variations of +/- 10% (voltage and frequency). IntelliVolt models shall operate from 50/60 Hz input source of 120V through 277V with sustained variations of +/- 10% (voltage and frequency).
2.6 Ballast shall be high frequency electronic type and operate lamps at a frequency above 42 kHz to avoid interference with infrared devices and eliminate visible flicker.

2.7 Ballast shall have a Power Factor greater than 0.98 at full light output and greater than 0.90 throughout the dimming range for primary lamp.

2.8 Ballast shall have a minimum ballast factor of 1.00 (120V and 277V 1-3 lamp models) or 0.88 (120V and 277V 4 lamp models and 347V 2-3 lamp models) or 1.18 (277V 4 lamp HL models) at maximum light output and 0.03 at minimum light output for primary lamp.

2.9 Ballast shall provide for a Lamp Current Crest Factor of 1.7 or less.

2.10 Ballast input current shall have Total Harmonic Distortion (THD) of less than 10% when operated at nominal line voltage and 100% power.

2.11 Ballast shall have a Class A sound rating.

2.12 Ballast shall have a minimum starting temperature of 10C (50F) for primary lamp.

2.13 Ballast shall provide Lamp EOL Protection Circuit for all T5, T5/HO and CFL lamps.

2.14 Ballast shall control lamp light output from 100% - 3% relative light output for series operation T8 and CFL lamps, 100% - 10% relative light output for parallel operation T8 and 100% - 1% relative light output for T5/HO lamps.

2.15 Ballast shall ignite the lamps at any light output setting without first going to another output setting.

2.16 Ballast shall tolerate sustained open circuit and short circuit output conditions.

Section III - Regulatory Requirements

3.1 Ballast shall not contain any Polychlorinated Biphenyl (PCB).

3.2 Ballast shall be Underwriters Laboratories (UL) listed, Class P and Type 1 Outdoor; and Canadian Standards Association (CSA) certified where applicable.

3.3 Ballast shall comply with ANSI C62.41 Category A for Transient protection.

3.4 Ballast shall comply with ANSI C82.11 where applicable.

3.5 Ballast shall comply with the requirements of the Federal Communications Commission (FCC) rules and regulations, Title 47 CFR part 18, Non-Consumer (Class A) for EMI/RFI (conducted and radiated).

3.6 Ballast shall comply with NEMA 410 for in-rush current limits.

Section IV - Other

4.1 Ballast shall be manufactured in a factory certified to ISO 9001 Quality System Standards.

4.2 Ballast shall carry a five-year warranty from date of manufacture against defects in material or workmanship, including replacement, for operation at a maximum case temperature of 70C.

4.3 Manufacturer shall have a twenty-year history of producing electronic ballasts for the North American market.

4.4 Ballast shall be controlled by a Class 1 or Class 2 low voltage 0-10VDC controller.

IZT-2S54-D@277V							
MARK 7 0-10V							
Electronic Dimming							
Programmed Start							
Series							
120-277							
50/60 HZ							
Active							

4.5 Ballast shall be Philips Advance part # _____ or approved equal.





Revised 07/31/13

Data is based upon tests performed by Philips Lighting Electronic N.A. in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.

Philips Lighting Electronic N.A. 10275 West Higgins Road Rosemont, IL 60018 Tel.: 800-322-2086 Fax: 888-432-1882 Customer Support/Technical Service: 800-372-3331 OEM Support: 866-915-5886