



© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PLi-1531BN 06/16 philips.com/luminaires

Philips Lighting
North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd.
Markham, ON,
Canada L6C 2S3
Tel. 800-668-9008

PHILIPS
LIGHTOLIER

Track

Spot LED

Track heads



Actual Size



Next generation lighting perfected

Performance-grade track lighting



Actual size

Spot LED

The perfect balance between energy savings and visual performance.

A high brightness LED track solution in a multi-optic LED design. Ideal for customers concerned with energy, beam quality and visual performance. Multiple accessories available to customize the light output and visual appearance of the fixture.

Features

- Efficacy: Up to 78 lm/w at 3000K
- Lumens: 600, 1000, 2000, 3000
- Correlated Color Temp. (CCT): 2700K, 3000K, 4000K
- Color Rendering Index (CRI): 80-85
- Reflectors: Spot, Narrow Flood, Flood
- Finishes: White, Black, Aluminum
- Dimming: Trailing edge (ELV)


Components

1. Fixture
2. Diffusion filter
3. Hex cell louver
4. Snoot
5. Accessory holder




LLABS & LLAB0

10W/600lm 14W/1000lm



LLAB1


26W/2000lm



LLAB3

39W/3000lm

The 3000lm 8° Spot (RS) delivers more than 82,000 CBCP (Center Beam Candle Power) for excellent punch.



Comprised of a fixture and a combination of optional accessories.

Fixture

Series	W/Lumen	CCT	Reflector	Adapter	Finish	Version
LLAB	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
LLAB Spot LED	S 10W/ 600lm	27 2700K 30 3000K	RS 9° Spot RNF 20° N. Flood RF 36° Flood	— Lightolier H Halo J Juno GT GTek GH HTek	WH White AL Alum. BK Black	VA Version A (not applicable to any LLABS configurations - leave blank)
	0 14W/ 1000lm	27 2700K 30 3000K 40 4000K	RS 9° Spot RNF 20° N. Flood RF 36° Flood			
	1 26W/ 2000lm	27 2700K 30 3000K 40 4000K	RS 8° Spot RNF 20° N. Flood RF 38° Flood			
	3 39W/ 3000lm	27 2700K 30 3000K 40 4000K	RS 8° Spot RNF 23° N. Flood RF 40° Flood			

example: LLAB130RSALVA

Accessories¹

Series	Finish
<input type="checkbox"/>	<input type="checkbox"/>
Accessory holders	
LLABSAH for LLABS & LLAB0 series 8595 for LLAB1 & LLAB3 series ²	WH White BK Black
Compatible snoots	
23N30 for LLABS & LLAB0 series 23NT6 for LLAB1 & LLAB3 series	WH White AL Alum. BK Black

example: 23NT6AL

Diffusion filters

AF3 for LLABS & LLAB0 series
AF4 for LLAB1 & LLAB3 series

Color filters

ADF3 for LLAB0 series³
ADF4 for LLAB1 & LLAB3 series³

Hex cell louvers (matte black)

AL3HC for LLABS & LLAB0 series
AL4HC for LLAB1 and LLAB3 series

Labels

cULus, I.B.E.W.
5 year warranty.
(direct ceiling and wall mount only).

Customization

Compatible with 4, 9 & 12 LED array track heads



Shown with matte black accessory holder, aluminum snoot and hex cell louver.



Shown with matte black accessory holder and hex cell louver.



Shown with matte black accessory holder and aluminum snoot.

See specification sheets **LLABS**, **LLAB0-VA**, **LLAB1-VA**, or **LLAB3-VA** for quick ship options, additional drawings and information.

