



RS750B, RS751B
RS752B




RS750B Performance, Fixed										
		Color temperature (K)	P (W)					Beam angle		
					Ø mm			NB	MB	WB
RS750B Performance, Fixed	LED39S	827, 830, 840	35,5	1,4	155	x			x	x
		930	45	1,4	155	x			x	x
	LED49S	827, 830, 840	46	1,4	155	x			x	x
		930	55	1,4	155	x			x	x
	LED40S	827, 830, 840, 930	53	1,4	155	x		x		
RS751 Performance, Adjustable	LED39S	827, 830, 840	35,5	1,4	155		x		x	x
		930	45	1,4	155		x		x	x
	LED49S	827, 830, 840	46	1,4	155		x		x	x
		930	55	1,4	155		x		x	x
	LED40S	827, 830, 840, 930	53	1,4	155		x	x		
RS752 Performance, Elbow	LED27S	827, 830, 840	25	1,2	155		x		x	x
		930	30,5	1,2	155		x		x	x
	LED39S	827, 830, 840	35,5	1,2	155		x		x	x
		930	45	1,3	155		x		x	x
	LED49S	827, 830, 840	46	1,3	155		x		x	x
		930	55	1,3	155		x		x	x
	LED40S	827, 830, 840, 930	53	1,2	155		x	x		



Dimensions in mm



30°




82°




RS750B
RS751B
RS752B



Minimal built-in dimensions




1a




1b




2a




PS-E WH



Mains cable





DALI cable




2b

PS-E LH



DALI cable



Mains cable




PSE-E LH




2c


2d




3a






3b




3c








Xitanium 36W LH 0.3-1A 48V I 230V (PSE-E)			Xitanium 36W WH 0.3-1A 54V TD/I 230V (PSED-E)			Xitanium 50W LH 0.7-1.5A 48V 230V (PSE-E)			Xitanium 50W LH 0.7-1.5A 48V TD/I 230V (PSED-E)		
Lum. Pack	CCT	I _{nom.} (A)	Lum. Pack	CCT	I _{nom.} (A)	Lum. Pack	CCT	I _{nom.} (A)	Lum. Pack	CCT	I _{nom.} (A)
LED27S	827/830/840	0,133	LED27S	827/830/840	0,133	LED39S	930	0,196	LED39S	930	0,196
	930	0,133		930	0,133						
LED39S	827/830/840	0,154	LED39S	827/830/840	0,154	LED40S	827/830 840/930	0,228	LED40S	827/830 840/930	0,228
						LED49S	827/830/840 930	0,2 0,24	LED49S	827/830/840 930	0,2 0,24
I _{max.} (A)	14,5		I _{max.} (A)	5,3		I _{max.} (A)	23,5		I _{max.} (A)	5,3	
T _{ref.} (ms)	0,22		T _{ref.} (ms)	0,7		T _{ref.} (ms)	0,272		T _{ref.} (ms)	0,7	
MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*	
B-10A	20		B-10A	15		B-10A	15		B-10A	18	
B-16A	32		B-16A	24		B-16A	24		B-16A	30	
C-10A	33		C-10A	24		C-10A	24		C-10A	31	
C-16A	54		C-16A	40		C-16A	40		C-16A	51	



Luminaire not suitable for being covered with thermally insulating material.



Reflector accessory changing instructions



Only with soft clothes!
Do not push hard!



© 2016 Philips Lighting Holding B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V.
The Netherlands