



**PHILIPS  
LIGHTOLIER**

Track

Spot LED

Recessed multiple track heads



## Next generation lighting perfected

Performance-grade track lighting

© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PLi-1532BN 06/16 [philips.com/luminaires](http://philips.com/luminaires)

Philips Lighting  
North America Corporation  
200 Franklin Square Drive  
Somerset, NJ 08873  
Tel. 855-486-2216

Philips Lighting Canada Ltd.  
281 Hillmount Rd.  
Markham, ON,  
Canada L6C 2S3  
Tel. 800-668-9008



Actual size

# Spot LED recessed

The perfect balance between energy savings and visual performance.


Spot LED recessed is a two-part system that offers a high-performing architectural approach to demanding accent lighting needs. Multiple heads provide 360° rotation and 90° tilt with the flexibility to both harness and focus light in the built environment.




Track Heads  
.....  
Spot LED recessed  
.....

Aperture ring allows for multiple accessories.


## LLABR9




## LLABR17



## LLABR24



## LLABR32



### Features

- Efficacy: Up to 84 lm/w at 3000K
- Lumens: 1000, 1600
- Correlated Color Temp. (CCT): 2700K, 3000K, 4000K
- Color Rendering Index (CRI): 80-85
- Reflectors: Spot, Narrow Flood, Flood
- Finishes: White, Black
- Dimming: Non-dimmable (consult factory for dimmable)

### Components

1. Frame-in kit
2. Trim kit
3. Diffusion filter
4. Hex cell louver
5. Snoot
6. Accessory holder

Comprised of a frame-in kit + trim kit + mud-in kit, and a combination of optional accessories.

### Frame-in kit

example: LLABR24WH130H3RSVA

| Series                               | Length   | Finish   | Engine  | CCT  | Install  | Reflector  | Version             |
|--------------------------------------|--|--|---|--|--|--|---------------------|
| <b>LLABR</b>                         | <input type="checkbox"/>   | <input type="checkbox"/>                       | <input type="checkbox"/>                        | <input type="checkbox"/>   | <input type="checkbox"/>   | <input type="checkbox"/>                                     | <b>VA</b>           |
| <b>LLABR</b><br>Spot LED<br>recessed | <b>9</b> 9" for 1 head<br><b>17</b> 17" for 2 head<br><b>24</b> 24" for 3 head<br><b>32</b> 32" for 4 head | <b>WH</b> Matte White<br><b>BK</b> Matte Black | <b>0</b> 13W (9 LEDs)<br><b>1</b> 22W (12 LEDs) | <b>27</b> 2700K<br><b>30</b> 3000K<br><b>40</b> 4000K (consult factory for availability) | <b>H1</b> 1 head<br><b>H2</b> 2 head<br><b>H3</b> 3 head<br><b>H4</b> 4 head | <b>RS</b> Spot<br><b>RNF</b> Narrow flood<br><b>RF</b> Flood | <b>VA</b> Version A |

### Trim kit

example: LLABR24WHW

| Series                               | Length   | Finish   | Flange  |
|--------------------------------------|--|--|---|
| <b>LLABR</b>                         | <input type="checkbox"/>   | <input type="checkbox"/>                       | <input type="checkbox"/>                          |
| <b>LLABR</b><br>Spot LED<br>recessed | <b>9</b> 9" for 1 head<br><b>17</b> 17" for 2 head<br><b>24</b> 24" for 3 head<br><b>32</b> 32" for 4 head | <b>WH</b> Matte White<br><b>BK</b> Matte Black | <b>W</b> With flange<br><b>FT</b> Flangeless trim |

### Accessories<sup>1</sup>

example: LLAB1AH

| Series  | Finish  |
|---|---|
| <input type="checkbox"/>  | <input type="checkbox"/>  |
| <b>Accessory holders</b><br><b>8595</b> for 13W (0) series<br><b>LLAB1AH</b> for 22W (1) series | <b>WH</b> Matte white<br><b>BK</b> Matte black  |
| <b>Compatible snoots</b><br><b>23SNT6</b> for 13W (0) & 22W (1) series                          | <b>WH</b> Matte white<br><b>BK</b> Matte black  |
| <b>Diffusion filters</b><br><b>AF4</b> for 13W (0) & 22W (1) series                             | <b>LS</b> Linear Spread<br><b>SY</b> Symmetrical Spread<br><b>SF</b> Soft Focus<br><b>FR</b> Frosted Etched |

### Mud-in kit

example: LLABR24MK

| Series                               | Length   | Option   |
|--------------------------------------|--|--|
| <b>LLABR</b>                         | <input type="checkbox"/>   | <b>MK</b>  |
| <b>LLABR</b><br>Spot LED<br>recessed | <b>9</b> 9" for 1 head<br><b>17</b> 17" for 2 head<br><b>24</b> 24" for 3 head<br><b>32</b> 32" for 4 head | <b>MK</b> Mud-in kit only available with flangeless trim kit (FT) option |

1. Accessories are not ENERGY STAR<sup>®</sup> qualified.
2. Color filters will project colored light on ceiling.

### Color filters<sup>2</sup>

**ADF4** for 13W (0) & 22W (1) series

### Hex cell louvers (matte black)

**AL4HC** for 13W (0) & 22W (1) series

### Labels

cULus, I.B.E.W.  
5 year warranty.  
(direct ceiling and wall mount only).



See specification sheet **LLABR** for quick ship options, additional drawings and information.