



PHILIPS

LuxSpace Accent Compact Elbow

RS742B



220 V
240 V

50 Hz
60 Hz



Max. 40 °C
Min. 10 °C







GLOW
WIRE
650 °C



IK02

IP20


		Color temp. (K)	PSU	P (W)	PSE	PSED	kg	mm	Beam angle			
									NB	MB	WB	VWB
RS742B	LED12S	827	10,2	9,8	10,2	1,1	0,8			x	x	x
		830	10,7	9,6	10	1,1	0,8			x	x	x
		840	9,8	9,4	9,8	1,1	0,8			x	x	x
		PW9	12,2	11,6	12,2	1,1	0,8			x	x	x
		CRW	15,2	14,6	15,2	1,1	0,8			x	x	x
	LED15S	CRW	26,5	26	25,5	1,1	0,8	x				
		827	14,2	13,8	14,2	1,1	0,8			x	x	x
	LED17S	830	13,6	13	13,6	1,1	0,8			x	x	x
		840	13	12,4	13	1,1	0,8			x	x	x
		PW9	16,6	16	16,6	1,1	0,8			x	x	x
		CRW	21,5	21	21	1,1	0,8			x	x	x
		CH	25	24,5	24	1,1	0,8			x	x	x
	LED19S	FMT	27	26,5	26	1,1	0,8			x	x	x
		827	26	25,5	25	1,1	0,8	x				
	LED20S	830	26	25,5	25	1,1	0,8	x				
		840	26	25,5	25	1,1	0,8	x				
		PW9	26	25,5	25	1,1	0,8	x				
		CH	46	46	44,5	1,1	0,8			x	x	x
	LED27S	827	22,5	22	22	1,1	0,8			x	x	x
		830	21,5	21	20,5	1,1	0,8			x	x	x
		840	20,5	20,5	20	1,1	0,8			x	x	x
		PW9	27	26,5	26	1,1	0,8			x	x	x
		CRW	36,5	35,5	35	1,1	0,8			x	x	x
	LED26S	FMT	40	39	38	1,1	0,8			x	x	x
		827	33	32,5	32	1,1	0,8			x	x	x
	LED39S	830	32	31	30,5	1,1	0,8			x	x	x
		840	29,5	29	28,5	1,1	0,8			x	x	x
		PW9	40	38,5	38	1,1	0,8			x	x	x





Minimum built-in dimensions






1a




1b




2a




PS-E LH




2c




Mains cable




PS-E LH




2d



PSU-E





Mains cable




2e

Cable to LED module

~220-240V



LED driver 36W 0.3-1A 48V I 230V (PSU-E)			Xitanium 36W LH 0.3-1A 48V I 230V (PSE-E)			Xitanium 36W WH 0.3-1A 54V TD/Is 230V (PSED-E)			Xitanium 20W/m 0.15-0.5A 48V 230V (PSU-E)			Xitanium 20W LH 0.15-0.5A 48V Is 230V (PSE-E)			Xitanium 20W WH 0.15-0.5A 54V TD/Is 230V (PSED-E)		
Lum. Pack	CCT	Inom. (A)	Lum. Pack	CCT	Inom. (A)	Lum. Pack	CCT	Inom. (A)	Lum. Pack	CCT	Inom. (A)	Lum. Pack	CCT	Inom. (A)	Lum. Pack	CCT	Inom. (A)
LED15S	CRW	0,115	LED15S	CRW	0,113	LED15S	CRW	0,111	LED12S	827	0,044	LED12S	827	0,043	LED12S	827	0,044
LED17S	CRW	0,093	LED17S	CRW	0,091	LED17S	CRW	0,091		830	0,047		830	0,042		830	0,043
	CH	0,109		CH	0,107		CH	0,104		840	0,043		840	0,041		840	0,043
LED19S	FMT	0,117	LED19S	FMT	0,115	LED19S	FMT	0,113		PW9	0,053		PW9	0,050		PW9	0,053
LED20S	827/830/840/PW9	0,113	LED20S	827/830/840/PW9	0,111	LED20S	827/830/840/PW9	0,109	LED17S	827	0,062	LED17S	827	0,060	LED17S	827	0,062
	827	0,098		827	0,096		827	0,096		830	0,059		830	0,057		830	0,059
	830	0,093		830	0,091		830	0,089		840	0,057		840	0,054		840	0,057
	840	0,089		840	0,089		840	0,087		PW9	0,072		PW9	0,070		PW9	0,072
	PW9	0,117		PW9	0,115		PW9	0,113									
	CRW	0,159		CRW	0,154		CRW	0,152									
LED26S	FMT	0,174	LED26S	FMT	0,170	LED26S	FMT	0,165									
LED39S	827	0,143	LED39S	827	0,141	LED39S	827	0,139									
	830	0,139		830	0,135		830	0,133									
	840	0,128		840	0,126		840	0,124									
	PW9	0,174		PW9	0,167		PW9	0,165									
Imax. (A)	6		Imax. (A)	14,5		Imax. (A)	20,4		Imax. (A)	18,6		Imax. (A)	14		Imax. (A)	20,4	
Tref. (ms)	0,055		Tref. (ms)	0,22		Tref. (ms)	0,195		Tref. (ms)	0,24		Tref. (ms)	0,24		Tref. (ms)	0,195	
MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*	
B-10A	25		B-10A	20		B-10A	15		B-10A	21		B-10A	23		B-10A	15	
B-16A	40		B-16A	32		B-16A	24		B-16A	34		B-16A	38		B-16A	24	
C-10A	41		C-10A	33		C-10A	24		C-10A	35		C-10A	39		C-10A	24	
C-16A	68		C-16A	54		C-16A	40		C-16A	57		C-16A	64		C-16A	40	



Xitanium LED Driver 50W 0.7-1.5A 44V I 230V (PSU-E)			Xitanium 50W LH 0.7-1.5A 48V 230V (PSE-E)			Xitanium 50W WH 0.7-1.5A 48V TD/Is 230V (PSED-E)		
Lum. Pack	CCT	Inom. (A)	Lum. Pack	CCT	Inom. (A)	Lum. Pack	CCT	Inom. (A)
LED27S	CH	0,200	LED27S	CH	0,200	LED27S	CH	0,193
Imax. (A)	23		Imax. (A)	23,5		Imax. (A)	5,3	
Tref. (ms)	0,28		Tref. (ms)	0,272		Tref. (ms)	0,7	
MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*		MCB	Max. Products (pcs)*	
B-10A	11		B-10A	15		B-10A	18	
B-16A	19		B-16A	24		B-16A	30	
C-10A	19		C-10A	24		C-10A	31	
C-16A	32		C-16A	40		C-16A	51	

© 2016 Philips Lighting Holding B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V.
The Netherlands

