





LUMISTEP



DYNADIMMER



RF / CTC



Philips Iridium gen3 Medium/Large (BGP382/BGP383)

Mounting instructions

Instructions de montage
Montageanleitung
Montage instructie
Instruzioni di montaggio

Instrucciones de montaje
Instruções de montagem
Monteringsinstruktioner
Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet
Montaj yönergesi
Οδηγίες συναμολογησης
Instrukcja montazu

Szerelési utasítások
Návod k montáži
Инструкция по монтажу
Návod k montáži




BGP 382

LINE	LED	W +/- 10%	kg	Inrush current		
GRN 50/830	40	38	10	80A/150us	●	●
GRN 55/740	40	38	10	80A/150us	●	●
GRN 60/830	40	46,1	10	80A/150us	●	●
GRN 65/740	40	46,1	10	80A/150us	●	●
GRN 70/830	40	55,9	10	80A/150us	●	●
GRN 75/740	40	54,7	10	80A/150us	●	●
GRN 80/830	40	64,6	10	80A/150us	●	●
GRN 85/740	40	62,7	10	80A/150us	●	●
GRN 90/830	40	73,1	10	80A/150us	●	●
GRN 95/740	40	70,6	10	80A/150us	●	●
GRN100/830	40	82,9	10	80A/150us	●	●
GRN 105/740	40	79,2	10	80A/150us	●	●
GRN 115/740	40	86,5	10	80A/150us	●	●



BGP 383

LINE	LED	W +/- 10%	kg	Inrush current		
GRN 81/830	64	60,6	12	108A/140us	●	●
GRN 91/830	64	69,1	12	108A/140us	●	●
GRN 96/740	64	66,1	12	108A/140us	●	●
GRN 101/830	64	77,5	12	108A/140us	●	●
GRN 106/740	64	74,6	12	108A/140us	●	●
GRN 110/830	64	85,2	12	108A/140us	●	●
GRN 116/740	64	82,4	12	108A/140us	●	●
GRN 120/830	64	95	12	108A/140us	●	●
GRN 125/740	64	90,1	12	108A/140us	●	●
GRN130/830	64	103,5	12	108A/140us	●	●
GRN 135/740	64	97,9	12	108A/140us	●	●
GRN 140/830	64	112,6	12	108A/140us	●	●
GRN 145/740	64	105,6	12	108A/140us	●	●
GRN 150/830	64	121,6	12	108A/140us	●	●
GRN 155/740	64	114,6	12	108A/140us	●	●
GRN 160/830	64	130,7	12	108A/140us	●	●
GRN 165/740	64	122,7	12	108A/140us	●	●
GRN 175/740	64	130,7	12	108A/140us	●	●
GRN 185/740	64	137,8	12	108A/140us	●	●






I2NC 4427 I01 59151
Versiondate: 03/03/2015
Data subject to change without notice
Printed in Poland
www.philips.com/lighting





2 Version without cable



2' Version with cable

