

CitySoul Mini (CGP430)

Mounting instructions

Instructions de montage

Montageanleitung

Montage instructie

Istruzioni di montaggio

Instrucciones de montaje

Instruções de montagem

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet

Montaj yönergesi

Οδηγίες τήξεσσηομηθτθΧ

Instrukcja montazu

Szerelési utasítások

Návod k montázi


bycnherwbz gj vjynf:e

Návod k montázi



	kg maxi	max	min	IP..			Lampholder
SON-T 50W	9,4	25	-20	66	●	●	7
SON-T 70W	9,5	25	-20	66	●	●	7
SON-T 100W	9,5	25	-20	66	●	●	1
CDO-TT 70W	9,5	25	-20	66	●	●	7
CDO-TT 100W	9,5	25	-20	66	●	●	1
CDM-T 35W	9,5	25	-20	66	●	●	7
CDM-T 70W	9,6	25	-20	66	●	●	7
CPO-T 45W	9,6	25	-20	66	●	●	5
CPO-T 60W	9,6	25	-20	66	●	●	5
CPO-T 90W	9,6	25	-20	66	●	●	5
PL-T 32W	9,6	25	-20	66	●	●	1
PL-T 42W	9,6	25	-20	66	●	●	1


Standard Post Top



SCx 0.049 m² max.

SCx 0.056 m² max.


Standard Post Top Tiltable



SCx 0.049 m² max.

SCx 0.056 m² max.

Standard Side Entry



SCx 0.049 m² max.

SCx 0.056 m² max.



T 3-4-5-6-8



4





T 8-10-15






Use Philips lamps for optimum performance

- Fonctionnement optimal avec lampes Philips
- Optimale Bestriebsleistung mit Philips-Lampen
- Toimii parhaiten Philips-lamppujen kanssa
- Fungerar bäst med lampor från Philips

- Funzionamento ottimale garantito con lampade Philips
- Funciona melhor com lâmpadas Philips no interior
- Fungerer bedst med Philips-lamper


- Werkt het best met Philips-lampen
- Resultados óptimos con lámparas Philips
- Fungerer mest optimalt med Philips-lamper









	P3 Electromagnetic		P3 Electronic	
	a)	b)	c)	d)
	a)	b)	c)	d)


Functional ground
 Security ground
 C : Control line
 N : Neutral line
 L : Phase







CHRONOSENSE








CPO CDM
SON/CDO 50-70 W



CDO 100 W
SON 100 W
FLT 32/42 W



2,5 N.m



2,5 N.m

