

**PHILIPS
LUMEC**

Urban

Optima

OT10 OT20 & XL10



Designed
to **enhance**



Optima

LED post top luminaires

The Philips Lumec Optima LED post top luminaires are the perfect choice for urban projects such as streets, walkways and public spaces that compel that extra little bit of detail. This timeless luminaire is made from top-quality materials, is easy to maintain, and adds a distinctive decorative aspect to any contemporary environment. Paired with the latest LED technology, its IP66 rating, multiple lumen outputs, various luminaire style options and energy-saving control options are well suited to meet wide range of project requirements.



Benefits

- Versatile luminaires available with various style options.
- Post top luminaire suited wide range of applications.
- Multiple lumen packages with output of up to 7,853 lumens.
- Type 2, 3, 4, & 5 optics available.
- Highly efficient IP66 optics are protected from the elements and ensure optimal photometric performance.
- Color temperatures of 4000K and 3000K are available.
- Dimming driver standard.
- Maximizes energy savings with multiple driver options and programmed dimming options.



Lumen range: 2,601-7,853

Wattage range: 37-80

Efficacy range: 64-101

Post top




OT10




OT20

Dimensions



OT10
(shown w/globe)

EPA: 1.74 sq.ft.
Weight: 47 lbs. (21.3 kg)



OT20
(shown w/sag lens)

EPA: 1.42 sq.ft.
Weight: 47 lbs. (21.3 kg)



Lumen range: 2,601-7,853

Wattage range: 37-80


Efficacy range: 64-101

Post top



XL10

Dimensions



XL10
(shown w/globe)

EPA: 1.91 sq.ft.
Weight: 40 lbs. (18.1 kg)

Unify your light and space

See how **Philips Lumec Optima LED** luminaires can help you unify lighting with the environment it occupies.

Visit **philips.com/luminaires** for more information.

Prior to ordering, consult specification sheets for the most current information, notes, and exclusions.





© 2017 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PLu-1702BR 05/17 philips.com/luminaires

Philips Lighting
North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd,
Markham, ON,
Canada L6C 2S3
Tel. 800-668-9008