



CoreView Panel RC165V/166V




Geometry	Driver	Dimension (LxWxH)	Lumen	CCT	
Square	PSU	597x597x46	3400 lm	3000K 4000k	4.1
Square	PSD	597x597x46 622x622x46	3400 lm	4000K 3000K	4.1 4.3
Rectangular	PSU PSD	1197x297x46	3400 lm	3000K 4000K	4.2

Square




Rectangular




1. Please do not remove the protect film before installing to avoid scraping or dirtying the optical part.
2. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
3. The luminaire shall, under no circumstance, be covered with thermal insulation matting or similar material.
4. When cleaning the product, please use dry soft cottoncloth only.
5. Indoor use only.



A Recessed mounting






Safety cable




B Suspension mounting



	PSU	PSD
Electrical Characteristics		
I _{max} (A)	20	5.3
T _{ref} (μs)	250	700
MCB	No. of driver max.	
16A-B	32	24





Suspended mounting – using RC165Z SME-2 WH / RC165Z SME-4 WH

