


PHILIPS ADVANCE

High Pressure Sodium Lamp Ballast

Catalog Number 71A9928_150W
For 150W S55
60 Hz R-HPF
Status: Active

DIMENSIONS AND DATA



Capacitor: 7C520P24RA



Capacitance: 52
Dia/Oval Dim: 1.85
Height: 3.7
Temp Rating: 105°C


Ignitor: LI551-H4



Ballast to Lamp Distance
(BTL) = 2 feet
Temp Rating: 105°C

INPUT VOLTS	120				
CIRCUIT TYPE	R-HPF				
POWER FACTOR (min)	90%				
REGULATION					
Line Volts	±5%				
Lamp Watts	WITHIN TRAPEZOID				
LINE CURRENT (Amps)					
Operating.....	1.50				
Open Circuit.....	2.35				
Starting.....	2.45				
UL TEMPERATURE RATINGS					
Insulation Class	N(200°C)				
Coil Temperature Code	1029				
MIN. AMBIENT STARTING TEMP.	-40°F or -40°C				
NOM. OPEN CIRCUIT VOLTAGE	120				
INPUT VOLTAGE AT LAMP DROPOUT.....	96				
INPUT WATTS	173				
RECOMMENDED FUSE (Amps).....	6				
CORE and COIL					
Dimension (A)	2.05				
Dimension (B)	3.45				
Weight (lbs.)	3.5				
Lead Lengths	.1"				
CAPACITOR REQUIREMENT					
Microfarads	52.0				
Volts (min.)	120				
Fault Current Withstand (amps)					
60 Hz TEST PROCEDURES (Refer to Advance Test Procedure for HID Ballasts - Form 1270)					
High Potential Test (Volts)					
1 minute	1500				
2 seconds	2500				
Open Circuit Voltage Test (Volts)	112-126				
Short-Circuit Current Test (Amps)					
Secondary Current	4.20-5.20				
Input Current.....	1.90-2.90	-	-	-	-

Wiring Diagram:



Ordering Information

Order Suffix	Description

Data is based upon tests performed by Philips Lighting Electronic N.A. in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

Philips Lighting Electronic N.A.

10275 West Higgins Road · Rosemont, IL 60018 · Tel:800-322-2086 Fax:888-432-1882
Customer Support/ Technical Service:800-372-3331 · OEM Support: 866-915-5886

08/14/13