




Housing	Lumen package	CCT [K]	P [W]		Driver		Optics			Cable	
			typ.	max.	PSU-E	PSD-E	NB	MB	WB	CW	CW-L
RS343B	LED17S	827	15	19	•	•		•	•	•	•
		830	15	19	•	•		•	•	•	•
		840	14	18	•	•		•	•	•	•
		CRW	23.5	30	•	•		•	•	•	•
		PW9	18.6	24	•	•		•	•	•	•
	LED19S	FMT	26	33	•	•		•	•	•	•
	LED26S	FMT	39	50	•	•		•	•	•	•
	LED27S	827	26	33	•	•	•	•	•	•	•
		830	27	35	•	•	•	•	•	•	•
		840	24	31	•	•	•	•	•	•	•
		CH	44.5	57	•	•	•	•	•	•	•
		CRW	35	45	•	•	•	•	•	•	•
		PW9	31	40	•	•	•	•	•	•	•
	LED39S	827	37	47	•	•		•	•	•	•
		830	34.5	44	•	•		•	•	•	•
		840	33	42	•	•		•	•	•	•
		PW9	39.5	50	•	•		•	•	•	•


Main dimensions (in mm)








Installation positions



Built in box size







© 2016 Philips Lighting Holding B.V.
 All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.
 The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use.
 Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V.
 The Netherlands

