













| Dimensions in mm |       |      |      |    | Sensor/<br>Blind sensor<br>holder. | kg  |
|------------------|-------|------|------|----|------------------------------------|-----|
| Suspended        | A     | B    | C    | D  |                                    |     |
| Standalone       | L1130 | 1130 | 1064 |    |                                    | 3.2 |
|                  | L1170 | 1170 | 1104 |    | •                                  | 3.4 |
|                  | L1410 | 1409 | 1344 | 33 |                                    | 3.8 |
|                  | L1450 | 1449 | 1384 |    | •                                  | 4.1 |
| Line End         | L1130 | 1128 | 1095 |    |                                    | 3.2 |
|                  | L1170 | 1168 | 1135 |    | •                                  | 3.4 |
|                  | L1410 | 1408 | 1375 | 33 |                                    | 3.8 |
|                  | L1450 | 1448 | 1415 |    | •                                  | 4.1 |
| Line Feature     | L1130 | 1127 | 1127 |    |                                    | 3.2 |
|                  | L1170 | 1167 | 1167 |    | •                                  | 3.4 |
|                  | L1410 | 1406 | 1406 | 0  |                                    | 3.8 |
|                  | L1450 | 1446 | 1446 |    | •                                  | 4.1 |

| Suspension set contents |              |   |   |    | 2x cable | 3x |   |    |
|-------------------------|--------------|---|---|----|----------|----|---|----|
| SM2                     | SP530P BV/LE | • | • | •  | •        | •  |   |    |
|                         | SP530P LF    |   |   | •  | •        |    | • |    |
| SMTT                    | SP530P BV/LE |   |   | 2x | •        | •  |   | 2x |
|                         | SP530P LF    |   |   | •  | •        |    | • | •  |
| SW2                     | SP530P BV/LE |   |   | 2x | •        |    |   |    |
|                         | SP530P LF    |   |   | •  | •        |    | • |    |











### Push-in (PIP) PSD PI-5 Line End / Line Feature




8a





### PI-7


#### Line End / Line Feature




8b



### asymmetric LightEngine




9a




9b

9c




9d




### PoE

Condition Philips to specify to the customers (instruction):  
> to use UTP (Unshielded Twisted Pair) CAT5E or CAT6 cable.  
> the maximum length of the cable to be 20 meters.  
Apply a minimum radius of the Ethernet cable of 4x the cable diameter.




### Cover remover (ZZS400 OCR)



Replace 9a, b, c,

### Inrush current



| I <sub>max</sub> (A)          | 19              |
|-------------------------------|-----------------|
| T <sub>ref</sub> (μs)         | 280             |
| Condition: Input voltage 220V |                 |
| MCB                           | Luminaires Max. |
| B-10A                         | 15              |
| B-13A                         | 19              |
| B-16A                         | 24              |
| B-20A                         | 30              |
| C-25A                         | 37              |
| C-10A                         | 24              |
| C-13A                         | 32              |
| C-16A                         | 40              |
| C-20A                         | 49              |
| C-25A                         | 62              |