


# PHILIPS ADVANCE

## Electrical Specifications

VH-2Q26-TP-BLS	
Brand Name	COMPACT-HPF
Ballast Type	Magnetic
Starting Method	Pre-Heat
Lamp Connection	Series
Input Voltage	277
Input Frequency	60 HZ
Status	Active

Lamp Type	Num. of Lamps	Rated Lamp Watts	Min. Start Temp (°F/°C)	Input Current (Amps)	Starting Current (Amps)	Open Circuit (Amps)	Input Power (Watts)	Ballast Factor	MAX THD %	Power Factor
* CFM26W/GX24Q	2	26	50/10	0.21	0.32	0.00	58	0.94	25	1.00
CFQ26W/G24D	2	26	50/10	0.20	0.32	0.00	55	0.87	20	0.99

## Wiring Diagram



Diag. 51


The wiring diagram that appears above is for the lamp type denoted by the asterisk (\*)

## Standard Lead Length (inches)

	in.	cm.
Black	7	17.8
White		0
Blue	7	17.8
Red	7	17.8
Yellow		0
Gray		0
Violet		0

	in.	cm.
Yellow/Blue		0
Blue/White		0
Brown		0
Orange		0
Orange/Black		0
Black/White		0
Red/White		0

## Enclosure



## Enclosure Dimensions

OverAll (L)	Width (std)/(TP)	Height (H)	Mounting (M)
9.50 "	2.375 "	1.6875 "	8.90625 "
9 1/2	2 3/8	1 11/16	8 29/32
24.1 cm	6 cm / 0 cm	4.3 cm	22.6 cm



Revised 09/28/99

Data is based upon tests performed by Philips Lighting N.A in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.

## Philips Lighting Electronic N.A

10275 West Higgins Road Rosemont, IL 60018 Tel.: 800-322-2086 Fax: 888-432-1882  
Customer Support/Technical Service: 800-372-3331 · OEM Support: 866-915-5886