




PHILIPS

TrueLine


RC530B EL




					kg	kg
			A	B	VPC	PCV
Recessed	VPC	W8L150	1497	1450	4.3	
Recessed	PCV	W8L145	1472	1450		4.4
Recessed Line	VPC/PCV	W8L145	1448		4.2	4.5



Optional: RC530Z EP SET WH



Inrush current




I _{max} (A)	19
T _{ref} (μs)	280

Condition:
Input voltage 220V


MCB	Luminaire's Max.
B-10A	15
B-13A	19
B-16A	24
B-20A	30
B-25A	37
C-10A	24
C-13A	32
C-16A	40
C-20A	49
C-25A	62




Recessed



1






Wieland







2

3





PCV








4

5








Recessed Line





3



4


5




4



1




6a



6b



2



7



3

