


PHILIPS ADVANCE

High Pressure Sodium Lamp Ballast


Catalog Number 71A86F5
For 750W S111
60 Hz CWA
Status: Active

DIMENSIONS AND DATA




INPUT VOLTS	277	347	480		
CIRCUIT TYPE	CWA				
POWER FACTOR (min)	90%				
REGULATION	±10%				
Line Volts	WITHIN TRAPEZOID				
Lamp Watts					
LINE CURRENT (Amps)					
Operating.....	3.10	2.50	1.78		
Open Circuit.....	1.50	1.20	0.90		
Starting.....	3.00	2.30	1.65		
UL TEMPERATURE RATINGS					
Insulation Class	H(180°C)				
Coil Temperature Code	1029				
MIN. AMBIENT STARTING TEMP.	-40°F or -40°C				
NOM. OPEN CIRCUIT VOLTAGE	225				
INPUT VOLTAGE AT LAMP DROPOUT.....	208	260	360		
INPUT WATTS	840				
RECOMMENDED FUSE (Amps).....	10	10	5		
CORE and COIL					
Dimension (A)	3.12				
Dimension (B)	5.13				
Weight (lbs.)	23				
Lead Lengths	12"				
CAPACITOR REQUIREMENT					
Microfarads	75.0				
Volts (min.)	280				
Fault Current Withstand (amps)					
60 Hz TEST PROCEDURES (Refer to Advance Test Procedure for HID Ballasts - Form 1270)					
High Potential Test (Volts)					
1 minute	2000				
2 seconds	2500				
Open Circuit Voltage Test (Volts)	200-245				
Short-Circuit Current Test (Amps)					
Secondary Current	9.50-11.70				
Input Current.....	2.00-3.00	1.60-2.40	1.10-1.70	-	-

Capacitor: 7C750S28RA



Capacitance: 75
 Dia/Oval Dim: 2.05
 Height: 5
 Temp Rating: 105°C

Wiring Diagram:




Ordering Information

Order Suffix

Description

Ignitor:

LI561-H5



Ballast to Lamp Distance (BTL) = 5 feet
 Temp Rating: 105°C

Data is based upon tests performed by Philips Lighting Electronic N.A. in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

Philips Lighting Electronic N.A.

10275 West Higgins Road · Rosemont, IL 60018 · Tel:800-322-2086 Fax:888-432-1882
 Customer Support/ Technical Service:800-372-3331 · OEM Support: 866-915-5886

08/14/13