

PHILIPS EcoStyle

Installation instructions

Instructions de montage

Montageanleitung

Montage instruktio

Istruzioni di montaggio

Instrucciones de montaje

Instruções de montagem

Monteringsinstruktioner

Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet

Montaj yönergesi

Odhgiez synarmologhshz









Instrukcja montazu

Szerelési utasítás

Návod k montázi

Инструкция по монтажу

Návod k montázi



	min	max	kg	P _{max}	GLOW WIRE 650°C	IK02
ST440T LED17S/830 PSU MB II BK	10°C	40°C	1	19 W	•	•
ST440T LED17S/840 PSU MB II BK	10°C	40°C	1	19 W	•	•
ST440T LED17S/830 PSU WB II BK	10°C	40°C	1	19 W	•	•
ST440T LED17S/840 PSU WB II BK	10°C	40°C	1	19 W	•	•
ST440T LED17S/830 PSU MB II WH	10°C	40°C	1	19 W	•	•
ST440T LED17S/840 PSU MB II WH	10°C	40°C	1	19 W	•	•
ST440T LED17S/830 PSU WB II WH	10°C	40°C	1	19 W	•	•
ST440T LED17S/840 PSU WB II WH	10°C	40°C	1	19 W	•	•
						•
ST440T LED27S/830 PSU MB II BK	10°C	40°C	1	31 W	•	•
ST440T LED27S/840 PSU MB II BK	10°C	40°C	1	31 W	•	•
ST440T LED27S/830 PSU WB II BK	10°C	40°C	1	31 W	•	•
ST440T LED27S/840 PSU WB II BK	10°C	40°C	1	31 W	•	•
ST440T LED27S/830 PSU MB II WH	10°C	40°C	1	31 W	•	•
ST440T LED27S/840 PSU MB II WH	10°C	40°C	1	31 W	•	•
ST440T LED27S/830 PSU WB II WH	10°C	40°C	1	31 W	•	•
ST440T LED27S/840 PSU WB II WH	10°C	40°C	1	31 W	•	•
ST440T LED35S/830 PSU MB II BK	10°C	40°C	1	39 W	•	•
ST440T LED35S/840 PSU MB II BK	10°C	40°C	1	39 W	•	•
ST440T LED35S/830 PSU WB II BK	10°C	40°C	1	39 W	•	•
ST440T LED35S/840 PSU WB II BK	10°C	40°C	1	39 W	•	•
ST440T LED35S/830 PSU MB II WH	10°C	40°C	1	39 W	•	•
ST440T LED35S/840 PSU MB II WH	10°C	40°C	1	39 W	•	•
ST440T LED35S/830 PSU WB II WH	10°C	40°C	1	39 W	•	•
ST440T LED35S/840 PSU WB II WH	10°C	40°C	1	39 W	•	•

4443 160 06642

Version date : 12/05/15

Printed in The EU

Data subject to change without notice


© 12 / 2015, Koninklijke Philips Electronics N.V. All rights reserved

Keep for future reference: www.philips.com/lighting

PHILIPS







ST440T

GA69






GLOBAL Trac Base

Connection
230 V AC, 16 A, 3.7 kW



DRIVER	Xitanium 36W LH 0.3-1A 48V 230V 929000838903	LED driver 36W 0.3-1A 48V 230V 929000892506
Inom(A)	0,19	0,2
I _{max} (A)	20	6
T _{ref} (us)	250 (@ I _{max} 50%)	55
MCB	Max. products	Max. products
B-16A	31	39



Luminaire shall be mounted out of arms reach!

