

For projector types :

Optoma DM161

Optoma DS216

Optoma DS316

Optoma DS316L

Optoma DS323

Optoma DW318

Optoma DX319

Optoma DX319p

Optoma DX623

Optoma ES526

Optoma ET766XE

Optoma EW531

Optoma EW536

Optoma EX531

Optoma EX531p

Optoma EX531p EDU

Optoma EX536

Optoma EX536L

Optoma HD600X

Optoma HD600X-LV

Optoma HD66

Optoma HD67

Optoma HD6700

Optoma HD6720

Optoma HD67N

Optoma HW536

Optoma IS500

Optoma OP280W

Optoma OPX2510

Optoma OPX2610

Optoma OPX3000

Optoma PRO150S

Optoma PRO250X

Optoma PRO350W

Optoma RS528

Optoma TS526

Optoma TW536

Optoma TX536

Optoma X115

Optoma XE136

Optoma XE152