

Fugato Compact Adjustable








MBS262/LBS262

Installation instruction/ 安装说明

MBS262 - M001a



Compact Adjustable Ø175mm	MBS262	G12	1XCDM-T 70W	Ø115×3 heat strengthen glass	3.2
			1XCDM-T 150W	Ø115×3 钢化玻璃	4.1








Don't push glass
勿施力于玻璃上

Philips Lighting Luminaires (Shanghai) Co., Ltd.
Address: No. 2688, Huyi Road, Jiading, Shanghai, China
Postalcode: 201801

飞利浦灯具(上海)有限公司
地址: 中国上海市嘉定区马陆镇沪宜公路2688号
邮编: 201801

PHILIPS



1. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
灯具应由有资格的电工安装，接线要符合IEE 电气标准或国家标准。
2. The luminaire shall, under no circumstance, be covered with thermal insulation matting or similar material.
灯具不适合被隔热或类似材料覆盖。
3. The luminaire shall only be used complete with its protective shield.
灯具应只能完整地带有保护屏使用。