



EC Declaration of Conformity

We, Philips Lighting Holding B.V.

Internal Ref. Nr.: HU02-DoC-068-002

Year in which CE Mark was first affixed: 2016

Philips Lighting Hungary Korlátolt Felelősségű Társaság
Szabadság u. 107, 7090 Tamási, Hungary as seat &
Brand offices at 1117 Budapest, Aliz u. 1 & 2440 Százhalombatta Iparos utca 4.

Declare under our responsibility for the product(s):

Product Range:	NAME: Luxspace Accent 3 Family
Product Code:	DESCRIPTION: Recessed indoor luminaires for general purpose with LED modules RS7xx (Details in Annex, see page 2 to 19)

The designated product(s) is (are) in conformity with the essential requirements of the following European Directives and harmonized standards:

Low Voltage Directive (LVD), 2014/35/EU

- EN 60598-1:2015 + AC:2016 >> Luminaires - Part 1: General requirements and tests
- EN 60598-2-2:2012 >> Luminaires - Part 2: Section 2 - Recessed luminaires
- EN 62471:2008 >> Photobiological safety of lamps and lamp systems
- EN 62493 :2010 >> Assessment of lighting equipment related to human exposure to electromagnetic fields (EMF)
- EN 60529:1991 + A1:2000 >> Degrees of protection provided by enclosures (IP Code)

Electromagnetic Compatibility Directive (EMC), 2014/30/EU (valid from 20th April 2016)

- EN 55015:2013 >> Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment (CISPR 15:2013 + IS1:2013 + IS2:2013)
- EN 61547:2009 >> Equipment for general lighting purposes – EMC immunity requirements
- EN 61000-3-2:2014 >> Limits for Harmonic emissions (≤16A per phase)
- EN 61000-3-3:2013 >> Limits - Limitation of voltage changes, voltage fluctuations and flicker in public low-voltage supply systems, for equipment with rated current ≤ 16 A per phase and not subject to conditional connection

Radio Equipment Directive (RED), 2014/53/EU (valid from 13th June 2016)

- ETSI EN 301 489-3 V1.6.1 (2011-09) >> Electromagnetic compatibility and Radio spectrum Matters (ERM); ElectroMagnetic Compatibility (EMC) standard for radio equipment and services; Part 1: Specific conditions for Short-Range Devices (SRD)
- ETSI EN 300 220-2 V2.4.1 (2014-02) >> Electromagnetic compatibility and Radio spectrum Matters (ERM); Short Range Devices (SRD); Part 2: Harmonized EN covering essential requirements

EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures

- EC/1194/2012 >> Directional lamps, light emitting diode lamps and related equipment

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU

- EN 50581:2012 >> Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances

Factory Qualifications

Quality Management System ISO9001:2008
Environmental Management System ISO 14001:2004 Occupational
Health & Safety Management System OHSAS 18001:2007

Quality system in production :
100% electrical testing on both safety aspects and functioning
Sampling and inspection of packed products according to production
quality inspection system

Tamási, 28. August, 2016

Krisztián Németh
Quality Manager



PHILIPS Lighting Hungary Kft.
7090 Tamási, Szabadság u. 107,
16.



Annex to EC Declaration of Conformity

10/12NC	EAN	Product Description	Remarks
910500457411	8718696848944	RS730B LED11S/827 PSE-E NB BK	
910500457413	8718696848937	RS730B LED11S/827 PSED-E NB BK	
910500457917	8718696848951	RS730B LED11S/830 PSE-E NB BK	
910500458820	8718696855249	RS730B LED11S/830 PSE-E NB WH	
910500459139	8718696917275	RS730B LED11S/830 PSED-E NB BK	
910500457414	8718696978641	RS730B LED11S/830 PSED-E NB WH	
910500457415	8718696848968	RS730B LED11S/840 PSE-E NB BK	
910500458349	8718696848975	RS730B LED11S/930 PSE-E NB BK	
910500457417	8718696885246	RS730B LED11S/930 PSE-E NB WH	
910500458210	8718696848999	RS730B LED12S/827 PSE-E MB BK	
910500457416	8718696881613	RS730B LED12S/827 PSE-E MB WH	
910500458278	8718696848982	RS730B LED12S/827 PSED-E MB BK	
910500457262	8718696883815	RS730B LED12S/827 PSED-E WB WH	
910500458063	8718696847350	RS730B LED12S/830 PSE-E MB BK	
910500458821	8718696878453	RS730B LED12S/830 PSE-E MB WH	
910500457263	8718696917282	RS730B LED12S/830 PSE-E MB ALU	
910500458824	8718696847367	RS730B LED12S/830 PSE-E MB SI	
910500457285	8718696917312	RS730B LED12S/830 PSE-E WB BK	
910500458825	8718696847619	RS730B LED12S/830 PSE-E WB WH	
910500458043	8718696917329	RS730B LED12S/830 PSED-E MB BK	
910771117522	8718696877777	RS730B LED12S/830 PSED-E MB WH	
910500457286	8718699160258	RS730B LED12S/830 PSED-E WB BK	
910500458991	8718696847626	RS730B LED12S/830 PSED-E WB WH	
910500458242	8718696972267	RS730B LED12S/830 PSE-E MB BK CW3	
910500458992	8718696883051	RS730B LED12S/830 PSED-E MB BK CW3 C1KBST2	
910500459152	8718696972274	RS730B LED12S/830 PSE-E MB BK CW-L	
910500458994	8718696978924	RS730B LED12S/830 PSE-E MB WH CW-L	
910500458995	8718696972298	RS730B LED12S/830 PSE-E MB BK CU3	
910500457419	8718696972304	RS730B LED12S/830 PSED-E MB BK CU5	
910500458905	8718696849019	RS730B LED12S/840 PSE-E MB BK	
910500457540	8718696918661	RS730B LED12S/840 PSE-E MB WH	
910500457291	8718696850299	RS730B LED12S/840 PSE-E MB ALU	
910500457292	8718696847671	RS730B LED12S/840 PSE-E WB WH	
910500458132	8718696847688	RS730B LED12S/840 PSED-E WB WH	
910500457420	8718696879887	RS730B LED12S/840 PSED-E WB SI	
910500457289	8718696849026	RS730B LED12S/930 PSE-E MB BK	
910500459167	8718696847657	RS730B LED12S/930 PSE-E MB WH	
910500458279	8718696979587	RS730B LED12S/930 PSE-E MB SI	
910500458739	8718696883822	RS730B LED12S/930 PSE-E WB WH	
910500458094	8718696915677	RS730B LED12S/930 PSED-E WB BK	

Tamási, 28. August 2016

 Krisztián Németh
 Quality Manager
 

 PHILIPS Lighting Hungary Kft.
 7090 Tamási, Szabadság u. 107.
 16.



Annex to EC Declaration of Conformity

910500457189	8718696878972	RS730B LED12S/930 PSE-E WB WH CW-L	
910500457188	8718696846087	RS730B LED12S/CRW PSE-E MB BK	
910500457191	8718696846070	RS730B LED12S/CRW PSED-E MB BK	
910500457190	8718696846100	RS730B LED14S/CRW PSE-E NB BK	
910500459087	8718696846094	RS730B LED14S/CRW PSED-E NB BK	
910500459088	8718696974049	RS731B LED11S/827 PSE-E NB WH	
910500458205	8718696974056	RS731B LED11S/827 PSED-E NB BK	
910500457918	8718696881309	RS731B LED11S/827 PSED-E NB WH	
910500458111	8718696855256	RS731B LED11S/830 PSE-E NB BK	
910771117523	8718696879214	RS731B LED11S/830 PSE-E NB WH	
910500457888	8718699160265	RS731B LED11S/830 PSED-E NB BK	
910500458208	8718696854457	RS731B LED11S/830 PSED-E NB WH	
910500458902	8718696881590	RS731B LED11S/840 PSE-E NB WH	
910500458330	8718696918616	RS731B LED11S/840 PSED-E NB WH	
910500457283	8718696884799	RS731B LED11S/930 PSE-E NB BK	
910500459203	8718696847596	RS731B LED11S/930 PSE-E NB WH	
910500457284	8718699075507	RS731B LED11S/930 PSED-E NB WH	
910500458951	8718696847602	RS731B LED12S/827 PSE-E MB WH	
910500458566	8718696919644	RS731B LED12S/827 PSE-E WB WH	
910500458576	8718696912478	RS731B LED12S/827 PSED-E MB WH	
910500457264	8718696912614	RS731B LED12S/827 PSED-E WB WH	
910500457812	8718696847374	RS731B LED12S/830 PSE-E MB BK	
910500457287	8718696853696	RS731B LED12S/830 PSE-E MB WH	
910771117524	8718696847633	RS731B LED12S/830 PSE-E WB WH	
910500457889	8718699160272	RS731B LED12S/830 PSED-E MB BK	
910500458608	8718696854464	RS731B LED12S/830 PSED-E MB WH	
910500457288	8718696913697	RS731B LED12S/830 PSED-E WB BK	
910500458993	8718696847640	RS731B LED12S/830 PSED-E WB WH	
910500459153	8718696972281	RS731B LED12S/830 PSED-E WB SI	
910500458076	8718696978931	RS731B LED12S/830 PSE-E MB WH CW-L	
910500457293	8718696878781	RS731B LED12S/840 PSE-E MB WH	
910500458490	8718696847695	RS731B LED12S/840 PSE-E WB WH	
910500458567	8718696911198	RS731B LED12S/840 PSE-E WB SI	
910500457294	8718696912485	RS731B LED12S/840 PSED-E MB WH	
910500458288	8718696847701	RS731B LED12S/840 PSED-E WB WH	
910500458289	8718696884171	RS731B LED12S/840 PSED-E MB WH CU5	
910500457290	8718696884188	RS731B LED12S/840 PSED-E WB BK CU5	
910500458929	8718696847664	RS731B LED12S/930 PSE-E MB WH	
910500458147	8718696919323	RS731B LED12S/930 PSE-E WB BK	
910500458148	8718696880104	RS731B LED12S/930 PSED-E MB WH	
910500457244	8718696880111	RS731B LED12S/930 PSED-E WB WH	

Tamási, 28. August 2016

 Krisztián Németh
 Quality Manager
 

 PHILIPS Lighting Hungary Kft.
 7090 Tamási, Szabadság u. 107.
 16.



Annex to EC Declaration of Conformity

910500457421	8718696847091	RS740B LED15S/CRW PSE-E NB BK	
910500458561	8718696849033	RS740B LED17S/827 PSU-E MB BK	
910500457265	8718696912263	RS740B LED17S/827 PSU-E WB WH	
910500457936	8718696847381	RS740B LED17S/830 PSU-E MB BK	
910500459067	8718696855546	RS740B LED17S/830 PSU-E MB WH	
910500457266	8718696973325	RS740B LED17S/830 PSU-E MB ALU	
910500459066	8718696847398	RS740B LED17S/830 PSU-E MB SI	
910500458214	8718696973318	RS740B LED17S/830 PSU-E WB BK	
910500457752	8718696881736	RS740B LED17S/830 PSU-E WB WH	
910500458241	8718696852989	RS740B LED17S/830 PSED-E MB BK	
910500457919	8718696883044	RS740B LED17S/830 PSED-E MB WH	
910500457245	8718696855263	RS740B LED17S/830 PSED-E WB WH	
910500458528	8718696847107	RS740B LED17S/830 PSU-E MB BK LIN	
910500458996	8718696911938	RS740B LED17S/830 PSED-E WB WH LIN	
910500458952	8718696972311	RS740B LED17S/830 PSE-E MB BK	
910500458997	8718696919651	RS740B LED17S/830 PSE-E MB WH	
910500459010	8718696972328	RS740B LED17S/830 PSE-E MB ALU	
910500458998	8718696972502	RS740B LED17S/830 PSE-E MB SI	
910500457423	8718696972335	RS740B LED17S/830 PSE-E WB BK	
910500459183	8718696849057	RS740B LED17S/840 PSU-E MB BK	
910500458805	8718696979914	RS740B LED17S/840 PSU-E WB WH	
910500457424	8718696917039	RS740B LED17S/840 PSE-E MB WH LIN	
910500458740	8718696849064	RS740B LED17S/930 PSU-E MB BK	
910500458389	8718696915684	RS740B LED17S/930 PSED-E WB BK LIN	
910500457425	8718696885796	RS740B LED17S/930 PSE-E WB WH LIN	
910500457558	8718696849071	RS740B LED17S/CH PSU-E MB BK	
910500457193	8718696850503	RS740B LED17S/CH PSU-E MB WH	
910500457192	8718696846124	RS740B LED17S/CRW PSE-E MB BK	
910500459062	8718696846117	RS740B LED17S/CRW PSED-E MB BK	
910500459076	8718696973240	RS740B LED17S/PW9 PSE-E MB BK	
910500459077	8718696973929	RS740B LED17S/PW9 PSE-E MB WH	
910500457426	8718696973936	RS740B LED17S/PW9 PSED-E MB WH	
910500457559	8718696849088	RS740B LED19S/FMT PSU-E MB BK	
910500457427	8718696850510	RS740B LED19S/FMT PSU-E MB WH	
910500457428	8718696849095	RS740B LED20S/827 PSU-E NB BK	
910771117620	8718696849101	RS740B LED20S/830 PSU-E NB BK	
910500458999	8718699161248	RS740B LED20S/830 PSED-E NB WH	
910500457429	8718696972342	RS740B LED20S/830 PSE-E NB BK	
910500457430	8718696849118	RS740B LED20S/840 PSU-E NB BK	
910500459063	8718696849125	RS740B LED20S/930 PSU-E NB BK	
910500459046	8718696973257	RS740B LED20S/PW9 PSE-E NB BK	

Tamási, 28. August 2016

Krisztián Németh
Quality Manager

PHILIPS Lighting Hungary Kft.
7090 Tamási, Szabadság u. 107.
16.



Annex to EC Declaration of Conformity

910500459078	8718696973080	RS740B LED20S/PW9 PSE-E NB WH	
910500459047	8718696973943	RS740B LED20S/PW9 PSED-E NB BK	
910500457432	8718696973097	RS740B LED20S/PW9 PSED-E NB WH	
910500457433	8718696849149	RS740B LED27S/827 PSU-E MB BK	
910500458052	8718696849156	RS740B LED27S/830 PSU-E MB BK	
910500458669	8718696878040	RS740B LED27S/830 PSU-E MB WH	
910500458127	8718696914687	RS740B LED27S/830 PSU-E WB BK	
910500458670	8718696879771	RS740B LED27S/830 PSU-E WB WH	
910771117621	8718696914694	RS740B LED27S/830 PSU-E WB SI	
910500457890	8718699161255	RS740B LED27S/830 PSED-E MB WH	
910500458953	8718696854471	RS740B LED27S/830 PSED-E WB WH	
910500458529	8718696919668	RS740B LED27S/830 PSED-E WB WH CW-L	
910500458520	8718696911945	RS740B LED27S/830 PSED-E WB WH LIN	
910500457434	8718696911747	RS740B LED27S/830 PSE-E WB WH	
910500459184	8718696849163	RS740B LED27S/840 PSU-E MB BK	
910500458620	8718696979921	RS740B LED27S/840 PSU-E MB WH	
910500458521	8718696913949	RS740B LED27S/840 PSU-E WB BK	
910500457541	8718696911754	RS740B LED27S/840 PSU-E WB WH	
910500458621	8718696850305	RS740B LED27S/840 PSU-E WB ALU	
910500457697	8718696913956	RS740B LED27S/840 PSU-E WB SI	
910500458548	8718696852187	RS740B LED27S/840 PSED-E WB WH	
910500457435	8718696912133	RS740B LED27S/840 PSE-E WB WH	
910500458351	8718696849170	RS740B LED27S/930 PSU-E MB BK	
910500458390	8718696885321	RS740B LED27S/930 PSED-E WB WH	
910500457195	8718696885802	RS740B LED27S/930 PSE-E WB WH LIN	
910500457194	8718696846148	RS740B LED27S/CRW PSE-E MB BK	
910500457222	8718696846131	RS740B LED27S/CRW PSED-E MB BK	
910500459064	8718696846544	RS740B LED27S/CRW PSE-E MB BK CU3	
910500459175	8718696973264	RS740B LED27S/PW9 PSE-E MB BK	
910500459001	8718696979839	RS740B LED27S/PW9 PSE-E WB WH	
910500457438	8718696972359	RS740B LED27S/PW9 PSED-E MB BK	
910500457437	8718696849200	RS740B LED39S/827 PSE-E MB BK	
910500457439	8718696849194	RS740B LED39S/827 PSED-E MB BK	
910500458549	8718696849217	RS740B LED39S/830 PSE-E MB BK	
910500458494	8718696912140	RS740B LED39S/830 PSE-E MB WH	
910500459002	8718696911235	RS740B LED39S/830 PSE-E WB WH	
910771117622	8718696972366	RS740B LED39S/830 PSED-E MB BK	
910500458582	8718699161262	RS740B LED39S/830 PSED-E MB WH	
910500458495	8718696913079	RS740B LED39S/830 PSED-E WB BK	
910500458609	8718696911242	RS740B LED39S/830 PSED-E WB WH	
910500457440	8718696913703	RS740B LED39S/830 PSE-E WB WH LIN	

Tamási, 28. August 2016

 Krisztián Németh
 Quality Manager
 

 PHILIPS Lighting Hungary Kft.
 7090 Tamási, Szabadság u. 107.
 16.



Annex to EC Declaration of Conformity

910500459188	8718696849224	RS740B LED39S/840 PSE-E MB BK	
910500459206	8718699075224	RS740B LED39S/840 PSE-E MB SI	
910500457441	8718699075620	RS740B LED39S/840 PSE-E WB WH	
910500458045	8718696849231	RS740B LED39S/930 PSE-E MB BK	
910500459003	8718696877814	RS740B LED39S/930 PSE-E MB WH	
910500459048	8718696972373	RS740B LED39S/PW9 PSE-E MB BK	
910500459049	8718696973103	RS740B LED39S/PW9 PSE-E MB WH	
910500459065	8718696973110	RS740B LED39S/PW9 PSED-E MB WH CU5	
910500459050	8718696973271	RS740B LED49S/PW9 PSE-E MB BK	
910500459051	8718696973127	RS740B LED49S/PW9 PSE-E MB WH	
910500459052	8718696973134	RS740B LED49S/PW9 PSED-E MB WH CU5	
910500459053	8718696973141	RS740B LED49S/830 PSE-E MB WH	
910500459176	8718696973158	RS740B LED49S/830 PSED-E MB WH CU5	
910500457110	8718696979846	RS740B LED49S/930 PSE-E MB BK	
910500459116	8718696263785	RS741B LED15S/CRW PSE-E NB WH	
910500457639	8718696976234	RS741B LED17S/827 PSU-E MB BK	
910500459089	8718696851340	RS741B LED17S/827 PSU-E MB WH	
910500459090	8718696974063	RS741B LED17S/827 PSED-E MB BK	
910500459091	8718696974070	RS741B LED17S/827 PSED-E MB WH	
910500457332	8718696974087	RS741B LED17S/827 PSE-E MB BK	
910500458318	8718696848098	RS741B LED17S/827 PSE-E MB WH	
910500457267	8718696884577	RS741B LED17S/827 PSE-E WB WH LIN	
910500458215	8718696847404	RS741B LED17S/830 PSU-E MB BK	
910500458671	8718696881743	RS741B LED17S/830 PSU-E MB WH	
910500457637	8718696914700	RS741B LED17S/830 PSU-E MB SI	
910771117525	8718696851326	RS741B LED17S/830 PSU-E WB WH	
910771117526	8718699160289	RS741B LED17S/830 PSED-E MB BK	
910771117527	8718699160296	RS741B LED17S/830 PSED-E MB WH	
910500458930	8718699160302	RS741B LED17S/830 PSED-E WB BK	
910500459127	8718696919330	RS741B LED17S/830 PSED-E WB WH	
910500458228	8718696976487	RS741B LED17S/830 PSED-E WB WH LIN	
910500458931	8718696882856	RS741B LED17S/830 PSU-E WB WH CW3 LIN	
910500458280	8718696919347	RS741B LED17S/830 PSE-E MB BK	
910500458932	8718696883839	RS741B LED17S/830 PSE-E MB WH	
910500457334	8718696919354	RS741B LED17S/830 PSE-E MB SI	
910500458798	8718696848111	RS741B LED17S/830 PSE-E WB WH	
910500458622	8718696916933	RS741B LED17S/830 PSE-E WB WH LIN	
910500458522	8718696913963	RS741B LED17S/840 PSU-E MB BK	
910500458623	8718696911761	RS741B LED17S/840 PSU-E MB WH	
910500457640	8718696913970	RS741B LED17S/840 PSU-E MB SI	
910500459166	8718696851357	RS741B LED17S/840 PSU-E WB WH	

Tamási, 28. August 2016

 Krisztián Németh
 Quality Manager

 PHILIPS Lighting Hungary Kft.
 7090 Tamási, Szabadság u. 107.
 16.



Annex to EC Declaration of Conformity

910500458290	8718696979297	RS741B LED17S/840 PSED-E WB WH	
910500459204	8718696884195	RS741B LED17S/840 PSED-E MB WH CU5	
910500459140	8718699075514	RS741B LED17S/840 PSU-E WB WH LIN	
910500459141	8718696978658	RS741B LED17S/840 PSED-E MB BK LIN	
910500459168	8718696978665	RS741B LED17S/840 PSED-E WB BK LIN	
910500458151	8718696979594	RS741B LED17S/840 PSED-E WB WH LIN	
910500457336	8718696880142	RS741B LED17S/840 PSED-E WB WH CW3 LIN	
910500458234	8718696848135	RS741B LED17S/840 PSE-E WB WH	
910500458287	8718696882931	RS741B LED17S/840 PSE-E WB WH LIN	
910500457641	8718696884164	RS741B LED17S/930 PSU-E MB BK	
910500458128	8718696851364	RS741B LED17S/930 PSU-E MB WH	
910500458152	8718696879788	RS741B LED17S/930 PSED-E MB BK CU5	
910771117615	8718696880159	RS741B LED17S/930 PSED-E WB WH CW3 LIN	
910500457338	8718699161194	RS741B LED17S/930 PSE-E MB BK	
910500458418	8718696848159	RS741B LED17S/930 PSE-E MB WH	
910500458806	8718696910191	RS741B LED17S/930 PSE-E WB WH	
910500458235	8718696917046	RS741B LED17S/930 PSE-E MB WH LIN	
910500457394	8718696882948	RS741B LED17S/930 PSE-E WB WH LIN	
910500457090	8718696848715	RS741B LED17S/CH PSU-E MB BK	
910500457403	8718696263594	RS741B LED17S/CH PSU-E MB WH	
910500458231	8718696848852	RS741B LED17S/CH PSU-E WB WH	
910500458236	8718696882894	RS741B LED17S/CH PSU-E MB WH LIN	
910500457111	8718696882955	RS741B LED17S/CH PSU-E WB WH LIN	
910500457112	8718696263792	RS741B LED17S/CRW PSE-E MB WH	
910500459205	8718696263808	RS741B LED17S/CRW PSE-E WB WH	
910500458644	8718699075521	RS741B LED17S/CRW PSE-E WB WH LIN	
910500457393	8718696914342	RS741B LED17S/CRW PSED-E MB WH	
910500457091	8718696848708	RS741B LED19S/FMT PSU-E WB BK	
910771117528	8718696263600	RS741B LED19S/FMT PSU-E WB WH	
910771117529	8718699160319	RS741B LED19S/FMT PSED-E MB BK	
910771117530	8718699160326	RS741B LED19S/FMT PSED-E MB WH	
910771117531	8718699160333	RS741B LED19S/FMT PSED-E WB BK	
910500457282	8718699160340	RS741B LED19S/FMT PSED-E WB WH	
910500458232	8718696847589	RS741B LED19S/FMT PSED-E MB BK CW3	
910500459117	8718696882900	RS741B LED19S/FMT PSU-E MB WH LIN	
910500458848	8718696976241	RS741B LED20S/827 PSU-E NB WH	
910771117532	8718696917725	RS741B LED20S/827 PSE-E NB WH	
910500458277	8718699160357	RS741B LED20S/830 PSED-E NB BK	
910500458849	8718696883747	RS741B LED20S/830 PSED-E NB WH	
910500458149	8718696917732	RS741B LED20S/830 PSE-E NB WH	
910500458216	8718696880128	RS741B LED20S/840 PSED-E NB WH	

Tamási, 28. August 2016

 Krisztián Németh
 Quality Manager

 PHILIPS Lighting Hungary Kft.
 7090 Tamási, Szabadság u. 107.
 16.



Annex to EC Declaration of Conformity

910500457642	8718696881750	RS741B LED20S/840 PSE-E NB WH	
910500458150	8718696851371	RS741B LED20S/930 PSU-E NB WH	
910500457331	8718696880135	RS741B LED20S/930 PSED-E NB WH	
910500459054	8718696848081	RS741B LED20S/930 PSE-E NB WH	
910500459055	8718696973165	RS741B LED20S/PW9 PSE-E NB WH	
910500457643	8718696973172	RS741B LED20S/PW9 PSED-E NB WH	
910500458594	8718696851388	RS741B LED27S/827 PSU-E MB WH	
910500458510	8718696913383	RS741B LED27S/827 PSU-E WB BK	
910500458340	8718696911556	RS741B LED27S/827 PSED-E MB WH	
910500458096	8718696884959	RS741B LED27S/827 PSU-E MB WH CW3	
910500458097	8718696878996	RS741B LED27S/827 PSED-E MB BK CW-L	
910500458098	8718696879009	RS741B LED27S/827 PSED-E MB WH CW-L	
910500458099	8718696879016	RS741B LED27S/827 PSED-E MB SI CW-L	
910500457644	8718696879023	RS741B LED27S/827 PSED-E WB SI CW-L	
910500458571	8718696851395	RS741B LED27S/827 PSU-E WB WH LIN	
910500458435	8718696912522	RS741B LED27S/827 PSED-E WB WH LIN	
910500458101	8718696910481	RS741B LED27S/827 PSED-E WB SI LIN	
910500457333	8718696879030	RS741B LED27S/827 PSED-E WB WH CW-L LIN	
910500459207	8718696848104	RS741B LED27S/827 PSE-E MB WH	
910500459208	8718699075637	RS741B LED27S/827 PSE-E MB BK CW-L	
910500459209	8718699075644	RS741B LED27S/827 PSE-E MB SI CW-L	
910500457340	8718699075651	RS741B LED27S/827 PSE-E WB SI CW-L	
910500457671	8718696848173	RS741B LED27S/827 PSE-E WB WH LIN	
910500457899	8718696851708	RS741B LED27S/830 PSU-E MB BK	
910500457901	8718696854587	RS741B LED27S/830 PSU-E MB WH	
910500457638	8718696854594	RS741B LED27S/830 PSU-E MB SI	
910500457926	8718696851333	RS741B LED27S/830 PSU-E WB WH	
910771117533	8718696855508	RS741B LED27S/830 PSU-E WB SI	
910500458211	8718699160364	RS741B LED27S/830 PSED-E MB BK	
910771117534	8718696881620	RS741B LED27S/830 PSED-E MB WH	
910500458927	8718699160371	RS741B LED27S/830 PSED-E WB BK	
910500458436	8718696919286	RS741B LED27S/830 PSED-E WB WH	
910500458967	8718696910498	RS741B LED27S/830 PSED-E WB SI	
910500458102	8718696919996	RS741B LED27S/830 PSU-E MB SI CW3	
910500458103	8718696879047	RS741B LED27S/830 PSED-E MB WH CW-L	
910500458104	8718696879054	RS741B LED27S/830 PSED-E MB SI CW-L	
910500458105	8718696879061	RS741B LED27S/830 PSED-E WB WH CW-L	
910500458572	8718696879078	RS741B LED27S/830 PSED-E WB SI CW-L	
910500458106	8718696912539	RS741B LED27S/830 PSED-E WB WH LIN	
910500457335	8718696879085	RS741B LED27S/830 PSED-E WB WH CW-L LIN	
910500458760	8718696848128	RS741B LED27S/830 PSE-E WB WH	

Tamási, 28. August 2016

Krisztián Németh
Quality Manager

PHILIPS Lighting Hungary Kft.
7090 Tamási, Szabadság u. 107.
16.



Annex to EC Declaration of Conformity

910500459210	8718696916216	RS741B LED27S/830 PSE-E MB WH CW3	
910500459211	8718699075668	RS741B LED27S/830 PSE-E MB WH CW-L	
910500459212	8718699075675	RS741B LED27S/830 PSE-E MB SI CW-L	
910500458674	8718699075682	RS741B LED27S/830 PSE-E WB SI CW-L	
910500458068	8718696914885	RS741B LED27S/830 PSE-E WB WH LIN	
910500457542	8718696878507	RS741B LED27S/840 PSU-E MB WH	
910500457645	8718696850312	RS741B LED27S/840 PSU-E MB SI	
910500457543	8718696851401	RS741B LED27S/840 PSU-E WB WH	
910500459142	8718696850329	RS741B LED27S/840 PSU-E WB SI	
910500459143	8718696978672	RS741B LED27S/840 PSED-E MB WH	
910771117614	8718696978689	RS741B LED27S/840 PSED-E WB WH	
910500457337	8718699161187	RS741B LED27S/840 PSE-E MB WH	
910500458645	8718696848142	RS741B LED27S/840 PSE-E WB WH	
910500457646	8718696914359	RS741B LED27S/930 PSU-E MB BK	
910500457990	8718696851418	RS741B LED27S/930 PSU-E MB WH	
910500458588	8718696876930	RS741B LED27S/930 PSU-E WB WH	
910500458324	8718696913246	RS741B LED27S/930 PSED-E WB BK	
910500457339	8718696884683	RS741B LED27S/930 PSU-E WB WH LIN	
910500457113	8718696848166	RS741B LED27S/930 PSE-E MB WH	
910500457114	8718696263815	RS741B LED27S/CRW PSE-E MB WH	
910771117535	8718696263822	RS741B LED27S/CRW PSE-E WB WH	
910771117536	8718699160388	RS741B LED27S/CRW PSED-E MB BK	
910771117537	8718699160395	RS741B LED27S/CRW PSED-E MB WH	
910771117538	8718699160401	RS741B LED27S/CRW PSED-E WB BK	
910500459079	8718699160418	RS741B LED27S/CRW PSED-E WB WH	
910500459080	8718696973950	RS741B LED27S/PW9 PSE-E WB WH	
910500457295	8718696973967	RS741B LED27S/PW9 PSED-E WB WH	
910500458207	8718696847718	RS741B LED39S/827 PSE-E MB WH	
910500457299	8718696881552	RS741B LED39S/827 PSE-E WB WH	
910500457672	8718696847756	RS741B LED39S/827 PSE-E WB WH LIN	
910500458064	8718696851715	RS741B LED39S/830 PSE-E MB BK	
910500458065	8718696878460	RS741B LED39S/830 PSE-E MB WH	
910500459072	8718696878477	RS741B LED39S/830 PSE-E MB SI	
910500457296	8718696973417	RS741B LED39S/830 PSE-E WB BK	
910771117539	8718696847725	RS741B LED39S/830 PSE-E WB WH	
910500458496	8718699160425	RS741B LED39S/830 PSED-E MB BK	
910771117540	8718696911259	RS741B LED39S/830 PSED-E MB WH	
910500458791	8718699160432	RS741B LED39S/830 PSED-E WB BK	
910500458487	8718696916728	RS741B LED39S/830 PSED-E WB WH	
910500458066	8718696911037	RS741B LED39S/830 PSE-E WB WH LIN	
910500458067	8718696878484	RS741B LED39S/840 PSE-E MB WH	

Tamási, 28. August 2016

Krisztián Németh
Quality Manager

PHILIPS Lighting Hungary Kft.
7090 Tamási, Szabadság u. 107.
16.



Annex to EC Declaration of Conformity

910500457297	8718696878491	RS741B LED39S/840 PSE-E MB SI	
910500459092	8718696847732	RS741B LED39S/840 PSE-E WB WH	
910500457673	8718696974094	RS741B LED39S/840 PSED-E WB WH LIN	
910500457298	8718696851722	RS741B LED39S/930 PSE-E MB BK	
910500458199	8718696847749	RS741B LED39S/930 PSE-E MB WH	
910500457496	8718696881255	RS741B LED39S/930 PSE-E WB WH	
910500458586	8718696849828	RS741B LED39S/930 PSED-E MB BK	
910500459081	8718696913116	RS741B LED39S/930 PSED-E MB WH	
910500459056	8718696973974	RS741B LED39S/PW9 PSE-E MB BK	
910500459082	8718696973189	RS741B LED39S/PW9 PSE-E MB WH	
910500459057	8718696973981	RS741B LED39S/PW9 PSED-E MB BK	
910500459177	8718696973196	RS741B LED39S/PW9 PSED-E MB WH CU5	
910500459058	8718696979853	RS741B LED49S/PW9 PSE-E MB BK	
910500459059	8718696973202	RS741B LED49S/PW9 PSE-E MB WH	
910500459105	8718696973219	RS741B LED49S/PW9 PSED-E MB WH CU5	
910500459104	8718696976043	RS741B LED49S/827 PSE-E MB BK	
910500459060	8718696976036	RS741B LED49S/830 PSE-E MB BK	
910500459083	8718696973226	RS741B LED49S/830 PSE-E MB WH	
910500459061	8718696973998	RS741B LED49S/830 PSED-E MB BK	
910500459103	8718696973233	RS741B LED49S/830 PSED-E MB WH CU5	
910500459084	8718696976029	RS741B LED49S/840 PSE-E MB BK	
910500459102	8718696974001	RS741B LED49S/840 PSED-E MB BK	
910500459085	8718696976012	RS741B LED49S/930 PSE-E MB BK	
910500458675	8718696974018	RS741B LED49S/930 PSED-E MB BK	
910500459488	8718699167837	RS742B LED12S/827 PSU-E MB BK	
910500459489	8718699167844	RS742B LED15S/CRW PSE-E NB BK	
910500459490	8718699167851	RS742B LED17S/830 PSU-E WB WH	
910500459491	8718699167868	RS742B LED19S/FMT PSU-E MB SI	
910500459492	8718699167875	RS742B LED20S/827 PSE-E NB BK	
910500459493	8718699167882	RS742B LED26S/FMT PSU-E VWB WH	
910500459494	8718699167899	RS742B LED27S/840 PSU-E VWB SI	
910500459495	8718699167905	RS742B LED27S/CH PSE-E MB WH	
910500459496	8718699167912	RS742B LED39S/830 PSED-E VWB WH	
910500459497	8718699167929	RS742B LED39S/PW9 PSU-E WB WH	
910500459004	8718696914892	RS750B LED19S/ROSE PSE-E MB BK	
910500458676	8718696972380	RS750B LED19S/ROSE PSED-E MB BK	
910500457431	8718696914908	RS750B LED26S/ROSE PSE-E MB BK	
910500457197	8718696849132	RS750B LED26S/FMT PSE-E MB BK	
910500457196	8718696846162	RS750B LED26S/CRW PSE-E NB BK	
910500457436	8718696846155	RS750B LED26S/CRW PSED-E NB BK	
910500458053	8718696849187	RS750B LED27S/CH PSE-E MB BK	

Tamási, 28. August 2016

Krisztián Németh
Quality Manager

PHILIPS Lighting Hungary Kft.
7090 Tamási, Szabadság u. 107.
16.



Annex to EC Declaration of Conformity

910500457785	8718696878057	RS750B LED27S/CH PSE-E WB WH	
910500457268	8718696853436	RS750B LED39S/827 PSE-E MB BK	
910500457680	8718696847411	RS750B LED39S/830 PSE-E MB BK	
910500459005	8718696851906	RS750B LED39S/830 PSE-E MB WH	
910500459006	8718696972397	RS750B LED39S/830 PSE-E MB ALU-BK	
910500457269	8718696972403	RS750B LED39S/830 PSE-E MB ALU-WH	
910500459007	8718696847428	RS750B LED39S/830 PSE-E MB SI	
910500458118	8718696972410	RS750B LED39S/830 PSE-E WB BK	
910500459008	8718696879603	RS750B LED39S/830 PSE-E WB WH	
910500458347	8718696972427	RS750B LED39S/830 PSE-E VWB BK	
910771117623	8718696885161	RS750B LED39S/830 PSE-E VWB WH	
910500458497	8718699161279	RS750B LED39S/830 PSED-E MB WH	
910500459173	8718696911266	RS750B LED39S/830 PSED-E WB WH	
910500459213	8718696979808	RS750B LED39S/830 PSED-E VWB WH	
910500458624	8718699075699	RS750B LED39S/830 PSE-E VWB SI CW-L	
910500458532	8718696913987	RS750B LED39S/830 PSED-E VWB WH CW-L	
910500457243	8718696911976	RS750B LED39S/830 PSED-E VWB SI CW-L	
910500458533	8718696847084	RS750B LED39S/830 PSE-E MB BK LIN	
910500457786	8718696911983	RS750B LED39S/830 PSED-E WB WH CW-L LIN	
910500458550	8718696853443	RS750B LED39S/840 PSE-E MB BK	
910500458272	8718696912157	RS750B LED39S/840 PSE-E WB WH	
910500458516	8718696883693	RS750B LED39S/840 PSE-E VWB WH	
910500458391	8718696911617	RS750B LED39S/840 PSED-E WB WH	
910500457787	8718696885819	RS750B LED39S/840 PSED-E VWB WH	
910500458625	8718696853450	RS750B LED39S/930 PSE-E MB BK	
910500458741	8718696913994	RS750B LED39S/930 PSED-E VWB BK LIN	
910500457199	8718696915691	RS750B LED39S/930 PSED-E VWB WH LIN	
910500457198	8718696846186	RS750B LED39S/CRW PSE-E MB BK	
910500457223	8718696846179	RS750B LED39S/CRW PSED-E MB BK	
910500457442	8718696846551	RS750B LED39S/CRW PSED-E MB BK CU5 LIN	
910500457443	8718696849248	RS750B LED40S/827 PSE-E NB BK	
910771117624	8718696849255	RS750B LED40S/830 PSE-E NB BK	
910500457444	8718699161286	RS750B LED40S/830 PSED-E NB WH	
910771117517	8718696849262	RS750B LED40S/840 PSE-E NB BK	
910500457445	8718699160203	RS750B LED40S/840 PSE-E NB WH	
910500457522	8718696849279	RS750B LED40S/930 PSE-E NB BK	
910500457447	8718696850077	RS750B LED40S/930 PSED-E NB BK	
910500457446	8718696849293	RS750B LED49S/827 PSE-E MB BK	
910500457448	8718696849286	RS750B LED49S/827 PSED-E MB BK	
910500458498	8718696849309	RS750B LED49S/830 PSE-E MB BK	
910500458499	8718696911273	RS750B LED49S/830 PSE-E MB WH	

Tamási, 28. August 2016

Krisztián Németh
Quality Manager

PHILIPS Lighting Hungary Kft.
7090 Tamási, Szabadság u. 107.
16.



Annex to EC Declaration of Conformity

910500458501	8718696911280	RS750B LED49S/830 PSE-E WB WH	
910500459009	8718696911297	RS750B LED49S/830 PSE-E VWB WH	
910500458502	8718696972434	RS750B LED49S/830 PSED-E MB BK	
910500458503	8718696911303	RS750B LED49S/830 PSED-E MB WH	
910500458504	8718696911310	RS750B LED49S/830 PSED-E WB WH	
910500458040	8718696911327	RS750B LED49S/830 PSED-E VWB WH	
910500458954	8718696877746	RS750B LED49S/830 PSED-E MB BK CW3 C1KBST2	
910500458955	8718696919675	RS750B LED49S/830 PSE-E WB WH CW-L	
910500458534	8718696919682	RS750B LED49S/830 PSED-E WB WH CW-L	
910500459214	8718696911990	RS750B LED49S/830 PSED-E VWB WH CW-L	
910500457449	8718699075705	RS750B LED49S/830 PSE-E WB BK CU3	
910500458874	8718696849316	RS750B LED49S/840 PSE-E MB BK	
910500458206	8718696918227	RS750B LED49S/840 PSE-E MB WH	
910500458348	8718696881446	RS750B LED49S/840 PSE-E WB WH	
910500458392	8718696885178	RS750B LED49S/840 PSE-E VWB WH	
910500459169	8718696885826	RS750B LED49S/840 PSED-E MB WH	
910500458551	8718696979600	RS750B LED49S/840 PSED-E WB WH	
910500457450	8718696912164	RS750B LED49S/840 PSED-E VWB WH	
910500458021	8718696849323	RS750B LED49S/930 PSE-E MB BK	
910500457523	8718696877401	RS750B LED49S/930 PSE-E MB WH	
910500458411	8718696850084	RS750B LED49S/930 PSED-E MB BK	
910500458412	8718696910047	RS751B LED19S/ROSE PSE-E WB WH	
910500458413	8718696910054	RS751B LED19S/ROSE PSE-E VWB WH	
910500458901	8718696910061	RS751B LED19S/ROSE PSE-E WB WH LIN	
910500458611	8718696918609	RS751B LED19S/ROSE PSED-E WB WH LIN	
910500458973	8718696913727	RS751B LED19S/ROSE PSED-E WB ALU-BK LIN	
910500458535	8718696971956	RS751B LED19S/ROSE PSED-E WB SI LIN	
910500458970	8718696912003	RS751B LED19S/ROSE PSED-E WB WH CW-L LIN	
910500458414	8718696971925	RS751B LED26S/ROSE PSE-E MB BK	
910500458742	8718696910078	RS751B LED26S/ROSE PSE-E WB WH	
910500458517	8718696915707	RS751B LED26S/ROSE PSE-E WB SI	
910771117541	8718696911686	RS751B LED26S/ROSE PSE-E VWB SI	
910771117542	8718699160449	RS751B LED26S/ROSE PSED-E MB BK	
910771117543	8718699160456	RS751B LED26S/ROSE PSED-E MB WH	
910771117544	8718699160463	RS751B LED26S/ROSE PSED-E WB BK	
910500458536	8718699160470	RS751B LED26S/ROSE PSED-E WB WH	
910500458570	8718696912010	RS751B LED26S/ROSE PSED-E WB WH CW-L LIN	
910771117545	8718696912515	RS751B LED26S/FMT PSE-E WB WH	
910771117546	8718699160487	RS751B LED26S/FMT PSED-E MB BK	
910771117547	8718699160494	RS751B LED26S/FMT PSED-E MB WH	
910771117548	8718699160500	RS751B LED26S/FMT PSED-E WB BK	

Tamási, 28. August 2016

 Krisztián Németh
 Quality Manager

 PHILIPS Lighting Hungary Kft.
 7090 Tamási, Szabadság u. 107.
 16.



Annex to EC Declaration of Conformity

910500457093	8718699160517	RS751B LED26S/FMT PSED-E WB WH	
910771117549	8718696263624	RS751B LED26S/FMT PSED-E WB WH LIN	
910771117550	8718699160524	RS751B LED26S/CRW PSED-E NB BK	
910500459154	8718699160531	RS751B LED26S/CRW PSED-E NB WH	
910500458352	8718696978948	RS751B LED27S/CH PSE-E VWB SI	
910500457092	8718696885338	RS751B LED27S/CH PSED-E MB WH	
910500457115	8718696263617	RS751B LED27S/CH PSE-E WB WH LIN	
910500457116	8718696263839	RS751B LED27S/CRW PSE-E MB WH	
910500457554	8718696263846	RS751B LED27S/CRW PSE-E WB WH	
910500457302	8718696850435	RS751B LED39S/827 PSE-E MB BK	
910500457555	8718696847770	RS751B LED39S/827 PSE-E MB WH	
910500457556	8718696850442	RS751B LED39S/827 PSE-E MB ALU-BK	
910500457557	8718696850459	RS751B LED39S/827 PSE-E MB ALU-WH	
910500457733	8718696850466	RS751B LED39S/827 PSE-E MB SI	
910500457927	8718696852798	RS751B LED39S/827 PSE-E WB WH	
910771117702	8718696855515	RS751B LED39S/827 PSE-E WB SI	
910500458319	8718699162191	RS751B LED39S/827 PSE-E VWB BK	
910500458010	8718696884584	RS751B LED39S/827 PSE-E VWB WH	
910500459093	8718696877241	RS751B LED39S/827 PSE-E VWB SI	
910500459094	8718696974100	RS751B LED39S/827 PSED-E MB BK	
910500458583	8718696974117	RS751B LED39S/827 PSED-E MB WH	
910500457310	8718696913086	RS751B LED39S/827 PSE-E MB WH LIN	
910500457270	8718696847855	RS751B LED39S/827 PSE-E WB WH LIN	
910500458015	8718696847435	RS751B LED39S/830 PSE-E MB BK	
910500458672	8718696877296	RS751B LED39S/830 PSE-E MB WH	
910500457304	8718696914717	RS751B LED39S/830 PSE-E MB SI	
910500459073	8718696847794	RS751B LED39S/830 PSE-E WB WH	
910500458341	8718696973424	RS751B LED39S/830 PSE-E VWB BK	
910500458011	8718696884966	RS751B LED39S/830 PSE-E VWB WH	
910500458552	8718696877258	RS751B LED39S/830 PSE-E VWB SI	
910500459074	8718696912171	RS751B LED39S/830 PSED-E MB WH	
910500457734	8718696973431	RS751B LED39S/830 PSED-E WB WH	
910500458584	8718696852804	RS751B LED39S/830 PSE-E WB WH CU3	
910500458342	8718696913093	RS751B LED39S/830 PSE-E MB WH LIN	
910500458626	8718696884973	RS751B LED39S/830 PSE-E VWB WH LIN	
910500458523	8718696914007	RS751B LED39S/840 PSE-E MB BK	
910500458627	8718696911778	RS751B LED39S/840 PSE-E MB WH	
910500458869	8718696914014	RS751B LED39S/840 PSE-E MB SI	
910500457308	8718696918029	RS751B LED39S/840 PSE-E WB WH	
910500458012	8718696847831	RS751B LED39S/840 PSE-E VWB WH	
910500458568	8718696877265	RS751B LED39S/840 PSE-E VWB SI	

Tamási, 28. August 2016

 Krisztián Németh
 Quality Manager

 PHILIPS Lighting Hungary Kft.
 7090 Tamási, Szabadság u. 107.
 16.



Annex to EC Declaration of Conformity

910500458569	8718696912492	RS751B LED39S/840 PSED-E MB WH	
910500457735	8718696912508	RS751B LED39S/840 PSED-E WB WH	
910500458771	8718696852811	RS751B LED39S/840 PSE-E WB WH CU3	
910500457306	8718696916407	RS751B LED39S/840 PSED-E WB WH LIN	
910500458792	8718696847817	RS751B LED39S/930 PSE-E MB WH	
910500458317	8718696916735	RS751B LED39S/930 PSED-E VWB WH	
910500457117	8718696884515	RS751B LED39S/930 PSE-E WB WH LIN	
910500457118	8718696263853	RS751B LED39S/CRW PSE-E MB WH	
910771117551	8718696263860	RS751B LED39S/CRW PSE-E WB WH	
910771117552	8718699160548	RS751B LED39S/CRW PSED-E MB BK	
910771117553	8718699160555	RS751B LED39S/CRW PSED-E MB WH	
910771117554	8718699160562	RS751B LED39S/CRW PSED-E WB BK	
910500459114	8718699160579	RS751B LED39S/CRW PSED-E WB WH	
910500459115	8718696976173	RS751B LED40S/827 PSED-E NB BK	
910500458016	8718696976180	RS751B LED40S/827 PSED-E NB WH	
910771117555	8718696877302	RS751B LED40S/830 PSE-E NB WH	
910771117556	8718699160586	RS751B LED40S/830 PSED-E NB BK	
910500458322	8718699160593	RS751B LED40S/830 PSED-E NB WH	
910500458577	8718696884621	RS751B LED40S/840 PSE-E NB WH	
910500457301	8718696912621	RS751B LED40S/840 PSED-E NB WH	
910500457303	8718696847763	RS751B LED40S/930 PSE-E NB WH	
910771117703	8718696847787	RS751B LED49S/827 PSE-E MB WH	
910500458511	8718699162207	RS751B LED49S/827 PSE-E VWB BK	
910500457311	8718696911563	RS751B LED49S/827 PSED-E MB WH	
910500458017	8718696847862	RS751B LED49S/827 PSE-E WB WH LIN	
910500457305	8718696877319	RS751B LED49S/830 PSE-E MB WH	
910500458493	8718696847800	RS751B LED49S/830 PSE-E WB WH	
910771117557	8718696911228	RS751B LED49S/830 PSE-E VWB WH	
910500458505	8718699160609	RS751B LED49S/830 PSED-E MB BK	
910771117558	8718696911334	RS751B LED49S/830 PSED-E MB WH	
910500458506	8718699160616	RS751B LED49S/830 PSED-E WB BK	
910500458956	8718696911341	RS751B LED49S/830 PSED-E WB WH	
910500458323	8718696919699	RS751B LED49S/830 PSED-E VWB WH	
910500458553	8718696884638	RS751B LED49S/840 PSE-E MB WH	
910500457309	8718696912188	RS751B LED49S/840 PSE-E WB WH	
910500458554	8718696847848	RS751B LED49S/840 PSE-E VWB WH	
910500458555	8718696912195	RS751B LED49S/840 PSED-E MB WH	
910500458851	8718696912201	RS751B LED49S/840 PSED-E WB WH	
910500457307	8718696917787	RS751B LED49S/840 PSED-E VWB WH	
910500457524	8718696847824	RS751B LED49S/930 PSE-E MB WH	
910500458589	8718696850091	RS751B LED49S/930 PSE-E WB BK	

Tamási, 28. August 2016

 Krisztián Németh
 Quality Manager

 PHILIPS Lighting Hungary Kft.
 7090 Tamási, Szabadság u. 107.
 16.



Annex to EC Declaration of Conformity

910500458793	8718696913253	RS751B LED49S/930 PSE-E WB WH	
910500458850	8718696916742	RS751B LED49S/930 PSED-E VWB WH	
910500458415	8718696917749	RS751B LED49S/930 PSE-E VWB WH LIN	
910500458743	8718696910085	RS752B LED19S/ROSE PSE-E WB WH	
910500458654	8718696915714	RS752B LED19S/ROSE PSE-E VWB WH	
910500458655	8718696914458	RS752B LED19S/ROSE PSE-E MB WH CW3	
910500458537	8718696914465	RS752B LED19S/ROSE PSED-E WB WH CW3	
910500458538	8718696912027	RS752B LED19S/ROSE PSE-E MB BK CW-L	
910500458656	8718696912034	RS752B LED19S/ROSE PSE-E MB WH CW-L	
910500458657	8718696914472	RS752B LED19S/ROSE PSE-E WB WH CW3 LIN	
910500458658	8718696914489	RS752B LED19S/ROSE PSED-E VWB WH CW3 LIN	
910500459215	8718696914496	RS752B LED19S/ROSE PSED-E VWB SI CW3 LIN	
910500459118	8718699075712	RS752B LED19S/ROSE PSE-E WB WH CW-L LIN	
910500459119	8718696976258	RS752B LED19S/ROSE PSED-E VWB WH CW-L LIN	
910500458508	8718696976265	RS752B LED19S/ROSE PSED-E VWB SI CW-L LIN	
910500458416	8718696911501	RS752B LED26S/ROSE PSE-E MB WH	
910500458761	8718696910092	RS752B LED26S/ROSE PSE-E WB WH	
910500458417	8718696916223	RS752B LED26S/ROSE PSE-E WB SI	
910500458429	8718696910108	RS752B LED26S/ROSE PSE-E VWB WH	
910500458637	8718696910344	RS752B LED26S/ROSE PSED-E MB BK	
910500459216	8718696914212	RS752B LED26S/ROSE PSED-E VWB WH CW3	
910500458659	8718699075729	RS752B LED26S/ROSE PSE-E MB WH CW-L	
910500459120	8718696914502	RS752B LED26S/ROSE PSED-E VWB WH CW3 LIN	
910500457202	8718696976272	RS752B LED26S/ROSE PSED-E VWB WH CW-L LIN	
910500457201	8718696846209	RS752B LED26S/CRW PSE-E NB BK	
910500457647	8718696846193	RS752B LED26S/CRW PSED-E NB BK	
910500458518	8718696851425	RS752B LED27S/827 PSE-E MB BK	
910500457525	8718696911693	RS752B LED27S/827 PSE-E VWB SI	
910500458353	8718696850107	RS752B LED27S/827 PSED-E MB BK	
910500458358	8718696885345	RS752B LED27S/827 PSED-E MB WH	
910500458419	8718696885390	RS752B LED27S/827 PSE-E VWB WH CW-L	
910500458834	8718696910207	RS752B LED27S/827 PSED-E WB WH CW-L	
910500457326	8718696917541	RS752B LED27S/827 PSED-E VWB WH CW-L	
910500457679	8718696848012	RS752B LED27S/827 PSE-E WB WH LIN	
910500458018	8718696851852	RS752B LED27S/830 PSE-E MB BK	
910500457312	8718696877326	RS752B LED27S/830 PSE-E MB WH	
910500458762	8718696847879	RS752B LED27S/830 PSE-E WB WH	
910500457737	8718696916230	RS752B LED27S/830 PSE-E WB SI	
910500458519	8718696852835	RS752B LED27S/830 PSE-E VWB WH	
910500457526	8718696911709	RS752B LED27S/830 PSE-E VWB SI	
910500458826	8718696850114	RS752B LED27S/830 PSED-E MB BK	

Tamási, 28. August 2016

Krisztián Németh
Quality Manager

PHILIPS Lighting Hungary Kft.
7090 Tamási, Szabadság u. 107.
16.



Annex to EC Declaration of Conformity

910771117625	8718696917411	RS752B LED27S/830 PSED-E MB WH	
910500457891	8718699161293	RS752B LED27S/830 PSED-E WB WH	
910500459249	8718696854488	RS752B LED27S/830 PSED-E VWB WH	
910500458223	8718699076412	RS752B LED27S/830 PSE-E WB WH CW3	
910771117518	8718696882672	RS752B LED27S/830 PSE-E MB WH CW-L	
910771117519	8718699160210	RS752B LED27S/830 PSE-E MB SI CW-L	
910500459250	8718699160227	RS752B LED27S/830 PSE-E WB WH CW-L	
910500459217	8718699076429	RS752B LED27S/830 PSE-E WB WH CW3 LIN	
910500458539	8718699075736	RS752B LED27S/830 PSE-E MB SI CW-L LIN	
910500458344	8718696912041	RS752B LED27S/830 PSED-E MB SI CW-L LIN	
910500457788	8718696885093	RS752B LED27S/830 PSED-E WB WH CW-L LIN	
910500458790	8718696853467	RS752B LED27S/840 PSE-E MB BK	
910500457738	8718696916674	RS752B LED27S/840 PSE-E MB WH	
910500457322	8718696852842	RS752B LED27S/840 PSE-E WB WH	
910500458315	8718696847978	RS752B LED27S/840 PSE-E VWB WH	
910500457732	8718696884492	RS752B LED27S/840 PSED-E WB WH	
910500457789	8718696852774	RS752B LED27S/840 PSE-E WB WH CW3	
910500457318	8718696853474	RS752B LED27S/930 PSE-E MB BK	
910500458628	8718696847930	RS752B LED27S/930 PSE-E MB WH	
910500458744	8718696914021	RS752B LED27S/930 PSED-E VWB BK	
910500458060	8718696915721	RS752B LED27S/930 PSED-E VWB WH	
910500458061	8718696878422	RS752B LED27S/930 PSE-E MB WH CW3	
910500458062	8718696878439	RS752B LED27S/930 PSE-E WB WH CW3	
910500458540	8718696878446	RS752B LED27S/930 PSE-E VWB WH CW3	
910500458359	8718696912058	RS752B LED27S/930 PSE-E MB BK CW-L	
910500458360	8718696885406	RS752B LED27S/930 PSE-E MB WH CW-L	
910500458541	8718696885413	RS752B LED27S/930 PSE-E MB SI CW-L	
910500458361	8718696912065	RS752B LED27S/930 PSE-E WB BK CW-L	
910500458629	8718696885420	RS752B LED27S/930 PSE-E WB WH CW-L	
910500457204	8718696914038	RS752B LED27S/930 PSED-E VWB BK LIN	
910500457119	8718696846223	RS752B LED27S/CRW PSE-E MB BK	
910500457120	8718696263877	RS752B LED27S/CRW PSE-E MB WH	
910500458807	8718696263884	RS752B LED27S/CRW PSE-E WB WH	
910500457203	8718696917053	RS752B LED27S/CRW PSE-E WB WH LIN	
910500458141	8718696846216	RS752B LED27S/CRW PSED-E MB BK	
910500458142	8718696880043	RS752B LED27S/CRW PSE-E MB WH CW3	
910500458143	8718696880050	RS752B LED27S/CRW PSE-E WB WH CW3	
910500458144	8718696880067	RS752B LED27S/CRW PSE-E VWB WH CW3	
910500458145	8718696880074	RS752B LED27S/CRW PSED-E MB WH CW3	
910500458146	8718696880081	RS752B LED27S/CRW PSED-E WB WH CW3	
910500457316	8718696880098	RS752B LED27S/CRW PSED-E VWB WH CW3	

Tamási, 28. August 2016

Krisztián Németh
Quality Manager

PHILIPS Lighting Hungary Kft.
7090 Tamási, Szabadság u. 107.
16.



Annex to EC Declaration of Conformity

910500457739	8718696847916	RS752B LED39S/827 PSE-E MB WH	
910500457740	8718696852859	RS752B LED39S/827 PSE-E MB SI	
910500457741	8718696852866	RS752B LED39S/827 PSE-E WB WH	
910500457747	8718696852873	RS752B LED39S/827 PSE-E WB SI	
910500458284	8718696852934	RS752B LED39S/827 PSE-E VWB WH	
910500458354	8718696883877	RS752B LED39S/827 PSED-E MB SI	
910500458420	8718696885352	RS752B LED39S/827 PSED-E WB WH	
910500457327	8718696910214	RS752B LED39S/827 PSE-E WB WH CW-L	
910500457271	8718696848029	RS752B LED39S/827 PSE-E WB WH LIN	
910500457742	8718696847442	RS752B LED39S/830 PSE-E MB BK	
910500457313	8718696852880	RS752B LED39S/830 PSE-E MB WH	
910500457748	8718696847886	RS752B LED39S/830 PSE-E WB WH	
910771117626	8718696852941	RS752B LED39S/830 PSE-E VWB WH	
910771117627	8718699161309	RS752B LED39S/830 PSED-E MB WH	
910500458530	8718699161316	RS752B LED39S/830 PSED-E WB WH	
910500458531	8718696911952	RS752B LED39S/830 PSE-E MB WH CW3	
910500458421	8718696911969	RS752B LED39S/830 PSE-E WB WH CW3	
910771117520	8718696910221	RS752B LED39S/830 PSE-E WB WH CW-L	
910500458630	8718699160234	RS752B LED39S/830 PSE-E WB WH CW-L LIN	
910500459095	8718696914045	RS752B LED39S/830 PSED-E WB WH CW-L LIN	
910500457743	8718696974124	RS752B LED39S/840 PSE-E MB WH	
910500457323	8718696852897	RS752B LED39S/840 PSE-E WB WH	
910500458333	8718696847985	RS752B LED39S/840 PSE-E VWB WH	
910500458827	8718696884881	RS752B LED39S/840 PSED-E MB BK	
910500458393	8718696917428	RS752B LED39S/840 PSED-E MB WH	
910500457946	8718696885833	RS752B LED39S/840 PSED-E VWB WH	
910500458285	8718696855744	RS752B LED39S/840 PSE-E MB WH CW3	
910500457319	8718696883884	RS752B LED39S/840 PSED-E WB WH LIN	
910500458362	8718696847947	RS752B LED39S/930 PSE-E MB WH	
910500458363	8718696885437	RS752B LED39S/930 PSE-E WB WH CW-L	
910500457206	8718696885444	RS752B LED39S/930 PSE-E WB WH CW-L LIN	
910500457121	8718696846247	RS752B LED39S/CRW PSE-E MB BK	
910500457122	8718696263891	RS752B LED39S/CRW PSE-E MB WH	
910500457205	8718696263907	RS752B LED39S/CRW PSE-E WB WH	
910500459194	8718696846230	RS752B LED39S/CRW PSED-E MB BK	
910500457224	8718699075385	RS752B LED39S/CRW PSE-E MB WH CW3	
910500459195	8718696846568	RS752B LED39S/CRW PSE-E MB BK CW3 LIN	
910500459196	8718699075392	RS752B LED39S/CRW PSE-E WB WH CW3	
910500459197	8718699075408	RS752B LED39S/CRW PSE-E WB SI CW3	
910500458364	8718699075415	RS752B LED39S/CRW PSE-E VWB WH CW3	
910500458019	8718696885451	RS752B LED39S/CRW PSE-E WB WH CW-L LIN	

Tamási, 28. August 2016

 Krisztián Németh
 Quality Manager

 PHILIPS Lighting Hungary Kft.
 7090 Tamási, Szabadság u. 107.
 16.



Annex to EC Declaration of Conformity

910771117628	8718696877333	RS752B LED40S/830 PSE-E NB WH	
910500457527	8718699161323	RS752B LED40S/830 PSED-E NB WH	
910500457528	8718696850121	RS752B LED40S/930 PSE-E NB BK	
910500457317	8718696850138	RS752B LED40S/930 PSED-E NB BK	
910500457947	8718696847923	RS752B LED49S/827 PSE-E MB WH	
910500457328	8718696855751	RS752B LED49S/827 PSE-E VWB WH CW3	
910500457329	8718696848036	RS752B LED49S/827 PSE-E WB WH LIN	
910500458020	8718696848043	RS752B LED49S/827 PSED-E WB WH LIN	
910500457314	8718696877340	RS752B LED49S/830 PSE-E MB WH	
910500458507	8718696847893	RS752B LED49S/830 PSE-E WB WH	
910500459128	8718696911419	RS752B LED49S/830 PSE-E VWB WH	
910500457315	8718696976494	RS752B LED49S/830 PSED-E MB WH	
910500458974	8718696847909	RS752B LED49S/830 PSED-E WB WH	
910500458437	8718696971963	RS752B LED49S/830 PSED-E WB SI	
910500457948	8718696910504	RS752B LED49S/830 PSED-E VWB ALU-BK	
910500458334	8718696855768	RS752B LED49S/830 PSE-E VWB WH CW3	
910500458524	8718696884898	RS752B LED49S/830 PSED-E WB BK LIN	
910500458906	8718696911785	RS752B LED49S/840 PSE-E MB WH	
910500457324	8718696918678	RS752B LED49S/840 PSE-E WB WH	
910500458335	8718696847992	RS752B LED49S/840 PSE-E VWB WH	
910500458336	8718696884904	RS752B LED49S/840 PSED-E MB BK	
910500457325	8718696884911	RS752B LED49S/840 PSED-E MB WH	
910500458337	8718696848005	RS752B LED49S/840 PSED-E VWB WH	
910500457529	8718696884928	RS752B LED49S/840 PSED-E WB BK LIN	
910500457320	8718696850145	RS752B LED49S/930 PSE-E MB BK	
910500457530	8718696847954	RS752B LED49S/930 PSE-E MB WH	
910500457321	8718696850152	RS752B LED49S/930 PSED-E MB BK	
910500459218	8718696847961	RS752B LED49S/930 PSED-E MB WH	
910771117689	8718699075743	RS752B LED49S/930 PSE-E WB WH CW-L LIN	
910771117690	8718699162061	RS752B LED19S/ROSE PSED-E VWB WH CW-L C1KBST2	
910771117691	8718699162078	RS752B LED19S/ROSE PSED-E VWB SI CW-L C1KBST2	
910500458638	8718699162085	RS752B LED26S/ROSE PSED-E VWB WH CW-L C1KBST2	
910500458365	8718696914229	RS752B LED27S/827 PSED-E WB WH CW-L C1KBST2	
910500458376	8718696885468	RS752B LED27S/827 PSED-E VWB WH CW-L C1KBST2	
910500458372	8718696885604	RS752B LED27S/827 PSED-E VWB SI CW-L C1KBST2	
910500458377	8718696885543	RS752B LED27S/930 PSED-E VWB WH CW-L C1KBST2	
910500458366	8718696885611	RS752B LED27S/930 PSED-E VWB SI CW-L C1KBST2	
910500458373	8718696885475	RS752B LED27S/930 PSED-E WB WH CW-L C1KBST2	
910500458368	8718696885550	RS752B LED27S/930 PSED-E WB WH CW-L C1KBST2 LIN	
910500458369	8718696885499	RS752B LED27S/930 PSED-E MB SI CW-L C1KBST2	
910500458370	8718696885505	RS752B LED27S/930 PSED-E MB WH CW-L C1KBST2	

Tamási, 28. August 2016

 Krisztián Németh
 Quality Manager
 

 PHILIPS Lighting Hungary Kft.
 7090 Tamási, Szabadság u. 107.
 16.



Annex to EC Declaration of Conformity

910771117521	8718696885512	RS752B LED39S/CRW PSED-E WB WH CW-L C1KBST2 LIN	
910500458355	8718699160241	RS752B LED39S/830 PSED-E WB WH CW-L C1KBST2	
910500458374	8718696885369	RS752B LED39S/930 PSED-E WB WH CW-L C1KBST2	
910500458367	8718696885581	RS752B LED39S/930 PSED-E WB SI CW-L C1KBST2	
910500458375	8718696885482	RS752B LED39S/930 PSED-E WB WH CW-L C1KBST2 LIN	
910500458357	8718696885598	RS752B LED39S/827 PSED-E WB SI CW-L C1KBST2	
910500458356	8718696885383	RS752B LED39S/930 PSED-E MB WH CW-L C1KBST2	
910500458371	8718696885376	RS752B LED49S/930 PSED-E WB WH CW-L C1KBST2	
910500458422	8718696885536	RS752B LED49S/930 PSED-E VWB WH CW-L C1KBST2 LIN	
910500458673	8718696910238	RS752B LED49S/930 PSED-E WB WH CW-L C1KBST2 LIN	
	8718696914724	RS752B LED19S/ROSE PSED-E WB SI CW-L C1KBST2	

– End of Annex –

Tamási, 28. August 2016

Krisztián Németh
Quality Manager



PHILIPS Lighting Hungary Kft.
7090 Tamási, Szabadság u. 107.
16.