

Gimbal rings with a
**clean
design**
for a close fit

LYTESPAN GIMBAL RING PAR30 AND PAR38 TRACK LUMINAIRES

The Philips Lightolier Lytespan Gimbal Ring PAR30 and PAR38 Track Luminaires offer form factors specifically designed to create a close fit with LED lamps, with cleanly miniaturized detailed yokes and ring-shaped lampholders. These new form factors keep the attention where it's meant to be, not on your ceilings. Front re-lamping for easy maintenance. Units adjust horizontally up to 350°, vertically up to 90°.

Available with Philips LED lamps


Also available for order with Philips LED lamps. These lamps have been tested in-situ to confirm lamp life projections are maintained as well as ensuring a perfect fit.




PHILIPS
LIGHTOLIER

LYTESPAN GIMBAL RING PAR30 AND PAR38 TRACK LUMINAIRES

9030N Gimbal Ring PAR30



9038N Gimbal Ring PAR38



Features

- Designed with minimalistic form to create a close fit with LED lamps
- Miniaturized detailed yoke and ring-shaped lampholder for a clean appearance
- Front re-lamping for easy maintenance
- Units adjust horizontally up to 350° and vertically up to 90°
- Molded polycarbonate bodies allow for scratch free handling during installation and re-lamping
- Available in white, black, or aluminum finishes

The Philips Lightolier Lytespan Gimbal Ring PAR30 and PAR38 Track Luminaires feature a minimalistic form designed with LED lamps in mind, helping keep the customer's focus where you want it to be.

Ordering guide

example with lamp: 9030NLRNFWH
example without lamp: 9030NWH

| Catalog No. | Lamping | Optics | Finish |
|--------------------------------|--|---|------------------------|
| <input type="text"/> | <input type="text"/> | <input type="text"/> | <input type="text"/> |
| 9030N PAR30 gimbal ring | Blank No lamp included | Blank No lamp included | WH Matte White |
| 9038N PAR38 gimbal ring | LR Philips LED 12W PAR30 or 19W PAR38 retail lamp | NF Narrow Flood (lamp available in black or white) | BK* Matte Black |
| | | F Flood (lamp only available in white) | AL Aluminum |

Lamping: 75W PAR30 maximum for 9030N. 120W PAR38 maximum for 9038N. Philips LED 12W PAR30 or 19W PAR38 included if LR specified. Go to www.philips.com/airflux for specs and information.

Track: Mounting compatible with all Lytespan Track Systems.

* Black LED lamp only available in Narrow Flood (NF) option.



© 2014 Koninklijke Philips N.V. All rights reserved.
Specifications are subject to change without notice.
www.philips.com/luminaires

PLi-1401BN 02/14

Philips Lighting
North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Phone: 855-486-2216

Philips Lighting Company
281 Hillmount Road
Markham ON, Canada L6C 2S3
Phone: 800-668-9008