


PHILIPS

LUXSPACE

DN570B/571B



IP20





50Hz
60Hz

230V
240V




GLOW
WIRE
850 °C







	LEDs	A	B	C	T° K	P max	kg
DN570B/DN571B	LED38S	300mm	800mm	≥10mm	830/840	42 W	1.93 kg










	H	Ø mm	Ø
DN570B	96,5 mm	200 mm	214 mm
DN571B	119 mm	200 mm	214 mm





FIX PSE-E







**DALI dimming
range 1-100%**

Electrical Characteristics
Current AC / Current DC

Inom (A)	
Imax (A)	
Tref (μs)	
MCB	r. Drivers Max
B-10A	x10
B-16A	x17
C-10A	x16
C-16A	x26




ZBS260 OCS.




Chiffon doux
Soft cloth
Weiches Tuch
Zacht doekje
Panno morbido
Tejido Suave
Blødt stykke stof
Pehmeá kangas
Mięka ściereczka
Páno macio




RIMLESS Version



RIM Accessory




	H	Ø
DN570B	98,5 mm	189 mm
DN571B	121 mm	189 mm





DN570/571 Ø200 ±2mm


6a




6d




6b




6e



6c



6f





© 2016 Philips Lighting Holding B.V.
All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.
The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable
and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use.
Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Philips Lighting Holding B.V.
The Netherlands