



RBX LED High Bay

10,000 Nominal Delivered Lumens, 3500K, 80 CRI, 16" White Acrylic Reflector

10,000 Nominal Delivered Lumens, 3500K, 80 CRI, 16" White Acrylic Reflector - 127 lm/W

The RBX LED high bay luminaires have the familiar look and feel of traditional high bay luminaires. Available with acrylic or aluminum reflectors and a variety of lumen packages and color temperatures, the RBX is ideal for retail, industrial, and commercial applications.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	3500K
CRI	80
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Voltages	120/208/240/277/347/UNIV V
Luminaire Input Watts	86
Mechanical and Housing	
Fixture Size	16 in
Shape	Round
Approval and Application	
Energy Certifications	DLC Standard

DesignLights Consortium Qualified	DesignLights Consortium Qualified Product List
Product List	
Initial Performance (IEC Compliant)	
Luminaire Lumens	10000
Efficacy	127 lm/W
Product Data	
Order product name	10,000 Nominal Delivered Lumens, 3500K, 80 CRI, 16" White Acrylic Reflector
Order code	RBX10L835-ARR16SL
Material Nr. (12NC)	CFI00001883
Catalog Number	RBX10L835-ARR16SL
Catalog Number Description	10,000 Nominal Delivered Lumens, 3500K, 80 CRI, 16" White Acrylic Reflector