



Maxos LED Performer – efficient and precise line lighting

Maxos LED Performer

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Benefits

- Extremely fast payback
- Breakthrough optical system for precise beam shaping
- Flexible in terms of retrofits, spots, changes, accessories

Features


- Low energy consumption compared to fluorescent
- Excellent beam shaping for less spill light and exact light distribution in horizontal and vertical planes
- Proven Philips LED engines (Fortimo)
- Can be mounted, new or retrofit, onto a Maxos rail
- Also available in a flexible panel version 4MX800 or high-efficiency version 4MX850

Application

- Supermarkets
- Warehouses
- Production facilities

Maxos LED Performer

Dimensional drawing




Product details

IPDP_4MX900i_0001-Detail
photo



IPDP_4MX900i_0003-Detail
photo



IPDP_4MX900i_0011-Detail
photo



Maxos LED Performer

Product details



General Information

CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Product family code	4MX900
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	≥80
Number of light sources	1

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Approval and Application

Protection class IEC	Safety class I
Mech. impact protection code	IK02
Ingress protection code	IP40

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------

General Information

Order Code	Full Product Name	Lamp family code
66387399	4MX900 LED40S/840 PSD WB WH L1200	LED40S
66388099	4MX900 LED40S/840 PSD MB WH L1200	LED40S
66389799	4MX900 LED40S/840 PSD NB WH L1200	LED40S
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	LED40S
66444399	4MX900 LED60S/840 PSD WB WH L1800	LED60S
66445099	4MX900 LED60S/840 PSD MB WH L1800	LED60S
66446799	4MX900 LED60S/840 PSD NB WH L1800	LED60S
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	LED60S
66460399	4MX900 LED90S/840 PSD WB WH L1800	LED90S
66461099	4MX900 LED90S/840 PSD MB WH L1800	LED90S
66462799	4MX900 LED90S/840 PSD NB WH L1800	LED90S
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	LED90S
66476499	4MX900 581 LED40S/840 PSU WB WH	LED40S
66477199	4MX900 581 LED40S/840 PSU MB WH	LED40S
66492499	4MX900 491 LED40S/840 PSU WB WH	LED40S
66493199	4MX900 491 LED40S/840 PSU MB WH	LED40S
66612699	4MX900 LED40S/840 PSU WB WH L1200	LED40S
66624999	4MX900 491 LED40S/840 PSD WB WH	LED40S
66625699	4MX900 491 LED40S/840 PSD MB WH	LED40S
66626399	4MX900 491 LED40S/840 PSD NB WH	LED40S
66628799	4MX900 491 LED50S/840 PSD WB WH	LED50S
66629499	4MX900 491 LED50S/840 PSD MB WH	LED50S
66630099	4MX900 491 LED50S/840 PSD NB WH	LED50S
66631799	4MX900 491 LED50S/840 PSD DA20 WH	LED50S
66633199	4MX900 LED40S/840 PSD A30 WH L1200	LED40S
66635599	4MX900 LED60S/840 PSD A30 WH L1800	LED60S
66636299	4MX900 581 LED40S/840 PSU A30 WH	LED40S
66637999	4MX900 581 LED50S/840 PSU A30 WH	LED50S
66638699	4MX900 491 LED40S/840 PSU A30 WH	LED40S
66640999	4MX900 581 LED50S/840 PSU WB WH	LED50S
66641699	4MX900 581 LED50S/840 PSU MB WH	LED50S
66644799	4MX900 491 LED50S/840 PSU WB WH	LED50S
66645499	4MX900 491 LED50S/840 PSU MB WH	LED50S
66646199	4MX900 491 LED50S/840 PSU NB WH	LED50S
66681299	4MX900 LED90S/840 PSD A30 WH L1800	LED90S
66790199	4MX900 491 LED75S/840 PSU WB WH	LED75S
66801499	4MX900 491 LED75S/840 PSD MB WH	LED75S

Maxos LED Performer

Order Code	Full Product Name	Lamp family code
66379899	4MX900 LED40S/840 PSD WB SI L1200	LED40S
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	LED40S
66436899	4MX900 LED60S/840 PSD WB SI L1800	LED60S
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	LED60S
66452899	4MX900 LED90S/840 PSD WB SI L1800	LED90S
66453599	4MX900 LED90S/840 PSD MB SI L1800	LED90S
66484999	4MX900 491 LED40S/840 PSU WB SI	LED40S
66485699	4MX900 491 LED40S/840 PSU MB SI	LED40S

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
66387399	4MX900 LED40S/840 PSD WB WH L1200	154 lm/W	4,000 lm	Wide beam
66388099	4MX900 LED40S/840 PSD MB WH L1200	154 lm/W	4,000 lm	Medium beam
66389799	4MX900 LED40S/840 PSD NB WH L1200	154 lm/W	4,000 lm	Narrow beam
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	154 lm/W	4,000 lm	Double asymmetric optic 20°
66444399	4MX900 LED60S/840 PSD WB WH L1800	161 lm/W	6,000 lm	Wide beam
66445099	4MX900 LED60S/840 PSD MB WH L1800	161 lm/W	6,000 lm	Medium beam
66446799	4MX900 LED60S/840 PSD NB WH L1800	161 lm/W	6,000 lm	Narrow beam
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	161 lm/W	6,000 lm	Double asymmetric optic 20°
66460399	4MX900 LED90S/840 PSD WB WH L1800	150 lm/W	9,000 lm	Wide beam
66461099	4MX900 LED90S/840 PSD MB WH L1800	150 lm/W	9,000 lm	Medium beam
66462799	4MX900 LED90S/840 PSD NB WH L1800	150 lm/W	9,000 lm	Narrow beam
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	150 lm/W	9,000 lm	Double asymmetric optic 20°
66476499	4MX900 581 LED40S/840 PSU WB WH	159 lm/W	4,000 lm	Wide beam
66477199	4MX900 581 LED40S/840 PSU MB WH	159 lm/W	4,000 lm	Medium beam
66492499	4MX900 491 LED40S/840 PSU WB WH	159 lm/W	4,000 lm	Wide beam

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
66493199	4MX900 491 LED40S/840 PSU MB WH	159 lm/W	4,000 lm	Medium beam
66612699	4MX900 LED40S/840 PSU WB WH L1200	154 lm/W	4,000 lm	Wide beam
66624999	4MX900 491 LED40S/840 PSD WB WH	159 lm/W	4,000 lm	Wide beam
66625699	4MX900 491 LED40S/840 PSD MB WH	159 lm/W	4,000 lm	Medium beam
66626399	4MX900 491 LED40S/840 PSD NB WH	159 lm/W	4,000 lm	Narrow beam
66628799	4MX900 491 LED50S/840 PSD WB WH	155 lm/W	5,000 lm	Wide beam
66629499	4MX900 491 LED50S/840 PSD MB WH	155 lm/W	5,000 lm	Medium beam
66630099	4MX900 491 LED50S/840 PSD NB WH	155 lm/W	5,000 lm	Narrow beam
66631799	4MX900 491 LED50S/840 PSD DA20 WH	155 lm/W	5,000 lm	Double asymmetric optic 20°
66633199	4MX900 LED40S/840 PSD A30 WH L1200	154 lm/W	4,000 lm	Asymmetrical mirror axis angle 30°
66635599	4MX900 LED60S/840 PSD A30 WH L1800	161 lm/W	6,000 lm	Asymmetrical mirror axis angle 30°
66636299	4MX900 581 LED40S/840 PSU A30 WH	159 lm/W	4,000 lm	Asymmetrical mirror axis angle 30°
66637999	4MX900 581 LED50S/840 PSU A30 WH	155 lm/W	5,000 lm	Asymmetrical mirror axis angle 30°

Maxos LED Performer

Order Code	Full Product Name	Luminous	Luminous	Optic type
		Efficacy (rated) (Nom)		
66638699	4MX900 491 LED40S/840 PSU A30 WH	159 lm/W	4,000 lm	Asymmetrical mirror axis angle 30°
66640999	4MX900 581 LED50S/840 PSU WB WH	155 lm/W	5,000 lm	Wide beam
66641699	4MX900 581 LED50S/840 PSU MB WH	155 lm/W	5,000 lm	Medium beam
66644799	4MX900 491 LED50S/840 PSU WB WH	155 lm/W	5,000 lm	Wide beam
66645499	4MX900 491 LED50S/840 PSU MB WH	155 lm/W	5,000 lm	Medium beam
66646199	4MX900 491 LED50S/840 PSU NB WH	155 lm/W	5,000 lm	Narrow beam
66681299	4MX900 LED90S/840 PSD A30 WH L1800	150 lm/W	9,000 lm	Asymmetrical mirror axis angle 30°
66790199	4MX900 491 LED75S/840 PSU WB WH	149 lm/W	7,500 lm	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption
66387399	4MX900 LED40S/840 PSD WB WH L1200	25.9 W
66388099	4MX900 LED40S/840 PSD MB WH L1200	25.9 W
66389799	4MX900 LED40S/840 PSD NB WH L1200	25.9 W
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	25.9 W
66444399	4MX900 LED60S/840 PSD WB WH L1800	37.3 W
66445099	4MX900 LED60S/840 PSD MB WH L1800	37.3 W
66446799	4MX900 LED60S/840 PSD NB WH L1800	37.3 W
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	37.3 W
66460399	4MX900 LED90S/840 PSD WB WH L1800	60.1 W
66461099	4MX900 LED90S/840 PSD MB WH L1800	60.1 W
66462799	4MX900 LED90S/840 PSD NB WH L1800	60.1 W
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	60.1 W
66476499	4MX900 581 LED40S/840 PSU WB WH	25.2 W
66477199	4MX900 581 LED40S/840 PSU MB WH	25.2 W
66492499	4MX900 491 LED40S/840 PSU WB WH	25.2 W
66493199	4MX900 491 LED40S/840 PSU MB WH	25.2 W
66612699	4MX900 LED40S/840 PSU WB WH L1200	25.9 W
66624999	4MX900 491 LED40S/840 PSD WB WH	25.2 W
66625699	4MX900 491 LED40S/840 PSD MB WH	25.2 W
66626399	4MX900 491 LED40S/840 PSD NB WH	25.2 W
66628799	4MX900 491 LED50S/840 PSD WB WH	32.2 W
66629499	4MX900 491 LED50S/840 PSD MB WH	32.2 W

Order Code	Full Product Name	Luminous	Luminous	Optic type
		Efficacy (rated) (Nom)		
66801499	4MX900 491 LED75S/840 PSD MB WH	149 lm/W	7,500 lm	Medium beam
66379899	4MX900 LED40S/840 PSD WB SI L1200	154 lm/W	4,000 lm	Wide beam
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	154 lm/W	4,000 lm	Double asymmetric optic 20°
66436899	4MX900 LED60S/840 PSD WB SI L1800	161 lm/W	6,000 lm	Wide beam
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	161 lm/W	6,000 lm	Double asymmetric optic 20°
66452899	4MX900 LED90S/840 PSD WB SI L1800	150 lm/W	9,000 lm	Wide beam
66453599	4MX900 LED90S/840 PSD MB SI L1800	150 lm/W	9,000 lm	Medium beam
66484999	4MX900 491 LED40S/840 PSU WB SI	159 lm/W	4,000 lm	Wide beam
66485699	4MX900 491 LED40S/840 PSU MB SI	159 lm/W	4,000 lm	Medium beam

Order Code	Full Product Name	Power Consumption
66630099	4MX900 491 LED50S/840 PSD NB WH	32.2 W
66631799	4MX900 491 LED50S/840 PSD DA20 WH	32.2 W
66633199	4MX900 LED40S/840 PSD A30 WH L1200	25.9 W
66635599	4MX900 LED60S/840 PSD A30 WH L1800	37.3 W
66636299	4MX900 581 LED40S/840 PSU A30 WH	25.2 W
66637999	4MX900 581 LED50S/840 PSU A30 WH	32.2 W
66638699	4MX900 491 LED40S/840 PSU A30 WH	25.2 W
66640999	4MX900 581 LED50S/840 PSU WB WH	32.2 W
66641699	4MX900 581 LED50S/840 PSU MB WH	32.2 W
66644799	4MX900 491 LED50S/840 PSU WB WH	32.2 W
66645499	4MX900 491 LED50S/840 PSU MB WH	32.2 W
66646199	4MX900 491 LED50S/840 PSU NB WH	32.2 W
66681299	4MX900 LED90S/840 PSD A30 WH L1800	60.1 W
66790199	4MX900 491 LED75S/840 PSU WB WH	50.2 W
66801499	4MX900 491 LED75S/840 PSD MB WH	50.2 W
66379899	4MX900 LED40S/840 PSD WB SI L1200	25.9 W
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	25.9 W
66436899	4MX900 LED60S/840 PSD WB SI L1800	37.3 W
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	37.3 W
66452899	4MX900 LED90S/840 PSD WB SI L1800	60.1 W
66453599	4MX900 LED90S/840 PSD MB SI L1800	60.1 W
66484999	4MX900 491 LED40S/840 PSU WB SI	25.2 W

Maxos LED Performer

Order Code	Full Product Name	Power Consumption
66485699	4MX900 491 LED40S/840 PSU MB SI	25.2 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
66387399	4MX900 LED40S/840 PSD WB WH L1200	Yes
66388099	4MX900 LED40S/840 PSD MB WH L1200	Yes
66389799	4MX900 LED40S/840 PSD NB WH L1200	Yes
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	Yes
66444399	4MX900 LED60S/840 PSD WB WH L1800	Yes
66445099	4MX900 LED60S/840 PSD MB WH L1800	Yes
66446799	4MX900 LED60S/840 PSD NB WH L1800	Yes
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	Yes
66460399	4MX900 LED90S/840 PSD WB WH L1800	Yes
66461099	4MX900 LED90S/840 PSD MB WH L1800	Yes
66462799	4MX900 LED90S/840 PSD NB WH L1800	Yes
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Yes
66476499	4MX900 581 LED40S/840 PSU WB WH	No
66477199	4MX900 581 LED40S/840 PSU MB WH	No
66492499	4MX900 491 LED40S/840 PSU WB WH	No
66493199	4MX900 491 LED40S/840 PSU MB WH	No
66612699	4MX900 LED40S/840 PSU WB WH L1200	No
66624999	4MX900 491 LED40S/840 PSD WB WH	Yes
66625699	4MX900 491 LED40S/840 PSD MB WH	Yes
66626399	4MX900 491 LED40S/840 PSD NB WH	Yes
66628799	4MX900 491 LED50S/840 PSD WB WH	Yes
66629499	4MX900 491 LED50S/840 PSD MB WH	Yes
66630099	4MX900 491 LED50S/840 PSD NB WH	Yes

Order Code	Full Product Name	Dimmable
66631799	4MX900 491 LED50S/840 PSD DA20 WH	Yes
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Yes
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Yes
66636299	4MX900 581 LED40S/840 PSU A30 WH	No
66637999	4MX900 581 LED50S/840 PSU A30 WH	No
66638699	4MX900 491 LED40S/840 PSU A30 WH	No
66640999	4MX900 581 LED50S/840 PSU WB WH	No
66641699	4MX900 581 LED50S/840 PSU MB WH	No
66644799	4MX900 491 LED50S/840 PSU WB WH	No
66645499	4MX900 491 LED50S/840 PSU MB WH	No
66646199	4MX900 491 LED50S/840 PSU NB WH	No
66681299	4MX900 LED90S/840 PSD A30 WH L1800	Yes
66790199	4MX900 491 LED75S/840 PSU WB WH	No
66801499	4MX900 491 LED75S/840 PSD MB WH	Yes
66379899	4MX900 LED40S/840 PSD WB SI L1200	Yes
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	Yes
66436899	4MX900 LED60S/840 PSD WB SI L1800	Yes
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	Yes
66452899	4MX900 LED90S/840 PSD WB SI L1800	Yes
66453599	4MX900 LED90S/840 PSD MB SI L1800	Yes
66484999	4MX900 491 LED40S/840 PSU WB SI	No
66485699	4MX900 491 LED40S/840 PSU MB SI	No

Mechanical and Housing

Order Code	Full Product Name	Housing Color
66387399	4MX900 LED40S/840 PSD WB WH L1200	White
66388099	4MX900 LED40S/840 PSD MB WH L1200	White
66389799	4MX900 LED40S/840 PSD NB WH L1200	White
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	White
66444399	4MX900 LED60S/840 PSD WB WH L1800	White
66445099	4MX900 LED60S/840 PSD MB WH L1800	White
66446799	4MX900 LED60S/840 PSD NB WH L1800	White
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	White
66460399	4MX900 LED90S/840 PSD WB WH L1800	White
66461099	4MX900 LED90S/840 PSD MB WH L1800	White
66462799	4MX900 LED90S/840 PSD NB WH L1800	White
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	White
66476499	4MX900 581 LED40S/840 PSU WB WH	White
66477199	4MX900 581 LED40S/840 PSU MB WH	White
66492499	4MX900 491 LED40S/840 PSU WB WH	White
66493199	4MX900 491 LED40S/840 PSU MB WH	White
66612699	4MX900 LED40S/840 PSU WB WH L1200	White
66624999	4MX900 491 LED40S/840 PSD WB WH	White
66625699	4MX900 491 LED40S/840 PSD MB WH	White

Order Code	Full Product Name	Housing Color
66626399	4MX900 491 LED40S/840 PSD NB WH	White
66628799	4MX900 491 LED50S/840 PSD WB WH	White
66629499	4MX900 491 LED50S/840 PSD MB WH	White
66630099	4MX900 491 LED50S/840 PSD NB WH	White
66631799	4MX900 491 LED50S/840 PSD DA20 WH	White
66633199	4MX900 LED40S/840 PSD A30 WH L1200	White
66635599	4MX900 LED60S/840 PSD A30 WH L1800	White
66636299	4MX900 581 LED40S/840 PSU A30 WH	White
66637999	4MX900 581 LED50S/840 PSU A30 WH	White
66638699	4MX900 491 LED40S/840 PSU A30 WH	White
66640999	4MX900 581 LED50S/840 PSU WB WH	White
66641699	4MX900 581 LED50S/840 PSU MB WH	White
66644799	4MX900 491 LED50S/840 PSU WB WH	White
66645499	4MX900 491 LED50S/840 PSU MB WH	White
66646199	4MX900 491 LED50S/840 PSU NB WH	White
66681299	4MX900 LED90S/840 PSD A30 WH L1800	White
66790199	4MX900 491 LED75S/840 PSU WB WH	White
66801499	4MX900 491 LED75S/840 PSD MB WH	White
66379899	4MX900 LED40S/840 PSD WB SI L1200	Silver

Maxos LED Performer

Order Code	Full Product Name	Housing Color
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	Silver
66436899	4MX900 LED60S/840 PSD WB SI L1800	Silver
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	Silver
66452899	4MX900 LED90S/840 PSD WB SI L1800	Silver

Order Code	Full Product Name	Housing Color
66453599	4MX900 LED90S/840 PSD MB SI L1800	Silver
66484999	4MX900 491 LED40S/840 PSU WB SI	Silver
66485699	4MX900 491 LED40S/840 PSU MB SI	Silver

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
66387399	4MX900 LED40S/840 PSD WB WH L1200	(0.38, 0.38) SDCM <3.5
66388099	4MX900 LED40S/840 PSD MB WH L1200	(0.38, 0.38) SDCM <3.5
66389799	4MX900 LED40S/840 PSD NB WH L1200	(0.38, 0.38) SDCM <3.5
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	(0.38, 0.38) SDCM <3.5
66444399	4MX900 LED60S/840 PSD WB WH L1800	(0.38, 0.38) SDCM <3.5
66445099	4MX900 LED60S/840 PSD MB WH L1800	(0.38, 0.38) SDCM <3.5
66446799	4MX900 LED60S/840 PSD NB WH L1800	(0.38, 0.38) SDCM <3.5
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	(0.38, 0.38) SDCM <3.5
66460399	4MX900 LED90S/840 PSD WB WH L1800	(0.38, 0.38) SDCM <3.5
66461099	4MX900 LED90S/840 PSD MB WH L1800	(0.38, 0.38) SDCM <3.5
66462799	4MX900 LED90S/840 PSD NB WH L1800	(0.38, 0.38) SDCM <3.5
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	(0.38, 0.38) SDCM <3.5
66476499	4MX900 581 LED40S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66477199	4MX900 581 LED40S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66492499	4MX900 491 LED40S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66493199	4MX900 491 LED40S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66612699	4MX900 LED40S/840 PSU WB WH L1200	(0.38, 0.38) SDCM <3.5
66624999	4MX900 491 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66625699	4MX900 491 LED40S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66626399	4MX900 491 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
66628799	4MX900 491 LED50S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66629499	4MX900 491 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66630099	4MX900 491 LED50S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5

Order Code	Full Product Name	Initial chromaticity
66631799	4MX900 491 LED50S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5
66633199	4MX900 LED40S/840 PSD A30 WH L1200	(0.38, 0.38) SDCM <3.5
66635599	4MX900 LED60S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5
66636299	4MX900 581 LED40S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
66637999	4MX900 581 LED50S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
66638699	4MX900 491 LED40S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
66640999	4MX900 581 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66641699	4MX900 581 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66644799	4MX900 491 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66645499	4MX900 491 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66646199	4MX900 491 LED50S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5
66681299	4MX900 LED90S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5
66790199	4MX900 491 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66801499	4MX900 491 LED75S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66379899	4MX900 LED40S/840 PSD WB SI L1200	(0.38, 0.38) SDCM <3.5
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	(0.38, 0.38) SDCM <3.5
66436899	4MX900 LED60S/840 PSD WB SI L1800	(0.38, 0.38) SDCM <3.5
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	(0.38, 0.38) SDCM <3.5
66452899	4MX900 LED90S/840 PSD WB SI L1800	(0.38, 0.38) SDCM <3.5
66453599	4MX900 LED90S/840 PSD MB SI L1800	(0.38, 0.38) SDCM <3.5
66484999	4MX900 491 LED40S/840 PSU WB SI	(0.38, 0.38) SDCM <3.5
66485699	4MX900 491 LED40S/840 PSU MB SI	(0.38, 0.38) SDCM <3

Application Conditions

Order Code	Full Product Name	Maximum dim level
66387399	4MX900 LED40S/840 PSD WB WH L1200	1%
66388099	4MX900 LED40S/840 PSD MB WH L1200	1%
66389799	4MX900 LED40S/840 PSD NB WH L1200	1%
66390399	4MX900 LED40S/840 PSD DA20 WH L1200	1%
66444399	4MX900 LED60S/840 PSD WB WH L1800	1%
66445099	4MX900 LED60S/840 PSD MB WH L1800	1%
66446799	4MX900 LED60S/840 PSD NB WH L1800	1%
66447499	4MX900 LED60S/840 PSD DA20 WH L1800	1%
66460399	4MX900 LED90S/840 PSD WB WH L1800	1%
66461099	4MX900 LED90S/840 PSD MB WH L1800	1%
66462799	4MX900 LED90S/840 PSD NB WH L1800	1%
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	1%
66476499	4MX900 581 LED40S/840 PSU WB WH	Not applicable
66477199	4MX900 581 LED40S/840 PSU MB WH	Not applicable
66492499	4MX900 491 LED40S/840 PSU WB WH	Not applicable
66493199	4MX900 491 LED40S/840 PSU MB WH	Not applicable




Order Code	Full Product Name	Maximum dim level
66612699	4MX900 LED40S/840 PSU WB WH L1200	Not applicable
66624999	4MX900 491 LED40S/840 PSD WB WH	1%
66625699	4MX900 491 LED40S/840 PSD MB WH	1%
66626399	4MX900 491 LED40S/840 PSD NB WH	1%
66628799	4MX900 491 LED50S/840 PSD WB WH	1%
66629499	4MX900 491 LED50S/840 PSD MB WH	1%
66630099	4MX900 491 LED50S/840 PSD NB WH	1%
66631799	4MX900 491 LED50S/840 PSD DA20 WH	1%
66633199	4MX900 LED40S/840 PSD A30 WH L1200	1%
66635599	4MX900 LED60S/840 PSD A30 WH L1800	1%
66636299	4MX900 581 LED40S/840 PSU A30 WH	Not applicable
66637999	4MX900 581 LED50S/840 PSU A30 WH	Not applicable
66638699	4MX900 491 LED40S/840 PSU A30 WH	Not applicable
66640999	4MX900 581 LED50S/840 PSU WB WH	Not applicable
66641699	4MX900 581 LED50S/840 PSU MB WH	Not applicable
66644799	4MX900 491 LED50S/840 PSU WB WH	Not applicable

Maxos LED Performer

Order Code	Full Product Name	Maximum dim level
66645499	4MX900 491 LED50S/840 PSU MB WH	Not applicable
66646199	4MX900 491 LED50S/840 PSU NB WH	Not applicable
66681299	4MX900 LED90S/840 PSD A30 WH L1800	1%
66790199	4MX900 491 LED75S/840 PSU WB WH	Not applicable
66801499	4MX900 491 LED75S/840 PSD MB WH	1%
66379899	4MX900 LED40S/840 PSD WB SI L1200	1%
66382899	4MX900 LED40S/840 PSD DA20 SI L1200	1%

Order Code	Full Product Name	Maximum dim level
66436899	4MX900 LED60S/840 PSD WB SI L1800	1%
66439999	4MX900 LED60S/840 PSD DA20 SI L1800	1%
66452899	4MX900 LED90S/840 PSD WB SI L1800	1%
66453599	4MX900 LED90S/840 PSD MB SI L1800	1%
66484999	4MX900 491 LED40S/840 PSU WB SI	Not applicable
66485699	4MX900 491 LED40S/840 PSU MB SI	Not applicable




Polar Wide Diagrams



**IFPS_4MX900 491 1xLED40S/830 PSD DA20-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSD WB-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED40S/830 PSU MB-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED40S/830 PSU NB-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSD DA20-
Polar Normal (separate)**


**IFPS_4MX900 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED40S/840 PSU A30-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED40S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSU NB-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSD WB-
Polar Normal (separate)**


Polar Wide Diagrams




IFPS_4MX900 491 1xLED50S/840 PSU A30-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/840 PSU NB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED71S/830 PSD MB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED71S/830 PSD NB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED71S/830 PSD WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED71S/830 PSU A30-
Polar Normal (separate)



IFPS_4MX900 491 1xLED75S/840 PSD DA20-
Polar Normal (separate)




IFPS_4MX900 491 1xLED75S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED75S/840 PSU WB-
Polar Normal (separate)


Polar Wide Diagrams




**IFPS_4MX900 581 1xLED40S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**



**IFPS_4MX900 581 1xLED75S/840 PSU A30-
Polar Normal (separate)**






**IFPS_4MX900 L1200 1xLED32S/840 PSU WB-
Polar Normal (separate)**



**IFPS_4MX900 L1200 1xLED40S/830 PSU WB-
Polar Normal (separate)**




Polar Wide Diagrams



IFPS_4MX900 L1200 1xLED40S/840 PSU WB-
Polar Normal (separate)

IFPS_4MX900 L1200 1xLED57S/830 PSD MB-
Polar Normal (separate)




IFPS_4MX900 L1200 1xLED57S/830 PSD NB-
Polar Normal (separate)



IFPS_4MX900 L1200 1xLED57S/830 PSD WB-
Polar Normal (separate)

IFPS_4MX900 L1200 1xLED57S/830 PSU WB-
Polar Normal (separate)

IFPS_4MX900 L1200 1xLED60S/840 PSD
DA20-Polar Normal (separate)




IFPS_4MX900 L1200 1xLED60S/840 PSD NB-
Polar Normal (separate)


IFPS_4MX900 L1200 1xLED60S/840 PSD WB-
Polar Normal (separate)

IFPS_4MX900 L1800 1xLED48S/830 PSD NB-
Polar Normal (separate)


Polar Wide Diagrams




IFPS_4MX900 L1800 1xLED48S/840 PSD
DA20-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED48S/840 PSD NB-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED48S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED60S/830 PSD A30-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED60S/830 PSD MB-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED60S/830 PSD NB-
Polar Normal (separate)



IFPS_4MX900 L1800 1xLED60S/840 PSD
DA20-Polar Normal (separate)






IFPS_4MX900 L1800 1xLED60S/840 PSD MB-
Polar Normal (separate)



IFPS_4MX900 L1800 1xLED60S/840 PSD NB-
Polar Normal (separate)




Polar Wide Diagrams



IFPS_4MX900 L1800 1xLED85S/830 PSD A30-
Polar Normal (separate)

IFPS_4MX900 L1800 1xLED85S/830 PSD MB-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED85S/830 PSD WB-
Polar Normal (separate)



IFPS_4MX900 L1800 1xLED90S/840 PSD
DA20-Polar Normal (separate)

IFPS_4MX900 L1800 1xLED90S/840 PSD NB-
Polar Normal (separate)

IFPS_4MX900 G3 491 1xLED40S/830 PSD
DA20-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/830 PSD MB-
Polar Normal (separate)


IFPS_4MX900 G3 491 1xLED40S/830 PSD NB-
Polar Normal (separate)

IFPS_4MX900 G3 491 1xLED40S/830 PSU A30-
Polar Normal (separate)


Polar Wide Diagrams




IFPS_4MX900 G3 491 1xLED40S/830 PSU NB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/830 PSU WB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/840 PSD
DA20- Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/840 PSD NB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/840 PSU MB-
Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/830 PSD
DA20- Polar Normal (separate)






IFPS_4MX900 G3 491 1xLED50S/830 PSD NB-
Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/830 PSD WB-
Polar Normal (separate)




Polar Wide Diagrams



IFPS_4MX900 G3 491 1xLED50S/830 PSU NB-
Polar Normal (separate)

IFPS_4MX900 G3 491 1xLED50S/830 PSU WB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/840 PSD
DA20- Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/840 PSD MB-
Polar Normal (separate)

IFPS_4MX900 G3 491 1xLED50S/840 PSD NB-
Polar Normal (separate)

IFPS_4MX900 G3 491 1xLED50S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/840 PSU A30-
Polar Normal (separate)


IFPS_4MX900 G3 491 1xLED50S/840 PSU MB-
Polar Normal (separate)

IFPS_4MX900 G3 491 1xLED50S/840 PSU NB-
Polar Normal (separate)


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED50S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED75S/840 PSU MB-
Polar Normal (separate)**






**IFPS_4MX900 G3 491 1xLED75S/840 PSU NB-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED40S/840 PSU A30-
Polar Normal (separate)**




Polar Wide Diagrams



IFPS_4MX900 G3 581 1xLED40S/840 PSU MB-
Polar Normal (separate)

IFPS_4MX900 G3 581 1xLED40S/840 PSU WB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED50S/830 PSU A30-
Polar Normal (separate)



IFPS_4MX900 G3 581 1xLED50S/830 PSU MB-
Polar Normal (separate)

IFPS_4MX900 G3 581 1xLED50S/840 PSU MB-
Polar Normal (separate)

IFPS_4MX900 G3 581 1xLED71S/830 PSU MB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED75S/840 PSU A30-
Polar Normal (separate)


IFPS_4MX900 G3 581 1xLED75S/840 PSU MB-
Polar Normal (separate)

IFPS_4MX900 G3 581 1xLED75S/840 PSU WB-
Polar Normal (separate)


Polar Wide Diagrams




IFPS_4MX900 G3 L1200 1xLED40S/830 PSD
NB-Polar Normal (separate)




IFPS_4MX900 G3 L1200 1xLED40S/840 PSU
WB-Polar Normal (separate)




IFPS_4MX900 G3 L1200 1xLED60S/840 PSU
WB-Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/830 PSD
NB-Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/830 PSD
WB-Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
MB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
NB-Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED85S/830 PSD
WB-Polar Normal (separate)

Maxos LED Performer

Polar Wide Diagrams



IFPS_4MX900 G3 L1800 1xLED90S/840 PSD

NB-Polar Normal (separate)

