



Maxos LED Performer

Maxos LED Performer

La ligne continue gradable ultra puissante. Si vous souhaitez réaliser des économies d'énergie et réduire vos coûts de maintenance tout en améliorant la qualité de votre éclairage, alors Maxos LED Performer est pour vous ! Ce système rail est le plus puissant de sa catégorie et s'adapte à toutes les applications : dans les environnements industriels et logistiques il garantit la sécurité et la productivité, dans les commerces de détail il met en valeur les marchandises et attire les acheteurs. Maxos LED Performer est une solution extrêmement flexible, avec une faible consommation d'énergie et d'excellents faisceaux lumineux, pour un retour sur investissement en moins de 5 ans selon les conditions d'utilisation.

Avantages

- Un retour sur investissement rapide
- Système optique révolutionnaire pour un faisceau précis
- Flexible en termes de solutions de remplacement, d'ajout de projecteurs et de modifications de l'installation au cours du temps

Fonctions


- Faible consommation d'énergie en comparaison avec des tubes fluorescents
- Un modelage parfait du faisceau lumineux pour une réduction maximale des pertes de flux et un éclairage précis sur les plans horizontaux et verticaux
- Fortimo LED Line R
- Possibilité de montage des unités électriques sur un rail Maxos neuf ou existant (rénovation)

Application

- Supermarchés/Hypermarchés
- Entrepôts
- Sites de production

Maxos LED Performer

Schéma dimensionnel




Détails sur le produit

IPDP_4MX900i_0001-Detail photo



IPDP_4MX900i_0003-Detail photo



IPDP_4MX900i_0011-Detail photo



Maxos LED Performer

Détails sur le produit



Informations générales

Marquage CE	Oui
Driver inclus	Oui
Marquage ENEC	Marquage ENEC
Inflammabilité	-
Essai au fil incandescent	Température 650 °C, durée 30 s
Source lumineuse remplaçable	Non
Nombre d'appareillages	1 unité
Code famille de produits	4MX900

Données techniques de l'éclairage

Angle d'ouverture du faisceau de la source lumineuse	120 degré(s)
Température de couleur corrélée (nom.)	4000 K
Indice de rendu de couleur (IRC)	≥80

Fonctionnement et électricité

Fréquence linéaire	50 to 60 Hz
--------------------	-------------

Température

Gamme de températures ambiantes	-20 à +40 °C
---------------------------------	--------------

Approbation et application

Classe de protection CEI	Classe de sécurité I
Protection contre les chocs mécaniques	IK02
Indice de protection	IP40

Performances initiales

Tolérance de flux lumineux	+/-10%
----------------------------	--------

Conditions d'application

Convient pour la commutation aléatoire	Non applicable
--	----------------

Informations générales

Order Code	Full Product Name	Code famille lampe	Commande intégrée
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	-	-
66882399	4MX900 581 LED50S/840 PSD MB WH	LED50S	-
66977699	4MX900 581 LED50S/840 PSD WB WH	LED50S	-
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	LED75S	Flux lumineux constant
66387399	4MX900 LED40S/840 PSD WB WH L1200	LED40S	-
66444399	4MX900 LED60S/840 PSD WB WH L1800	LED60S	-
66445099	4MX900 LED60S/840 PSD MB WH L1800	LED60S	-
66460399	4MX900 LED90S/840 PSD WB WH L1800	LED90S	-
66461099	4MX900 LED90S/840 PSD MB WH L1800	LED90S	-
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	LED90S	-
66476499	4MX900 581 LED40S/840 PSU WB WH	LED40S	-
66477199	4MX900 581 LED40S/840 PSU MB WH	LED40S	-
66492499	4MX900 491 LED40S/840 PSU WB WH	LED40S	-
66493199	4MX900 491 LED40S/840 PSU MB WH	LED40S	-
66624999	4MX900 491 LED40S/840 PSD WB WH	LED40S	-
66625699	4MX900 491 LED40S/840 PSD MB WH	LED40S	-
66626399	4MX900 491 LED40S/840 PSD NB WH	LED40S	-
66628799	4MX900 491 LED50S/840 PSD WB WH	LED50S	-
66629499	4MX900 491 LED50S/840 PSD MB WH	LED50S	-
66633199	4MX900 LED40S/840 PSD A30 WH L1200	LED40S	-
66635599	4MX900 LED60S/840 PSD A30 WH L1800	LED60S	-
66636299	4MX900 581 LED40S/840 PSU A30 WH	LED40S	-
66640999	4MX900 581 LED50S/840 PSU WB WH	LED50S	-
66641699	4MX900 581 LED50S/840 PSU MB WH	LED50S	-
66644799	4MX900 491 LED50S/840 PSU WB WH	LED50S	-
66645499	4MX900 491 LED50S/840 PSU MB WH	LED50S	-
66646199	4MX900 491 LED50S/840 PSU NB WH	LED50S	-
66709399	4MX900 581 LED75S/840 PSU A30 WH	LED75S	-
66790199	4MX900 491 LED75S/840 PSU WB WH	LED75S	-
66795699	4MX900 581 LED75S/840 PSU WB WH	LED75S	-
66796399	4MX900 581 LED75S/840 PSU MB WH	LED75S	-
66797099	4MX900 581 LED75S/840 PSU NB WH	LED75S	-
66800799	4MX900 491 LED75S/840 PSD WB WH	LED75S	-
66801499	4MX900 491 LED75S/840 PSD MB WH	LED75S	-
66802199	4MX900 491 LED75S/840 PSD NB WH	LED75S	-
66805299	4MX900 491 LED75S/840 PSD A30 WH	LED75S	-
66806999	4MX900 581 LED75S/840 PSD WB WH	LED75S	-

Order Code	Full Product Name	Code famille lampe	Commande intégrée
66807699	4MX900 581 LED75S/840 PSD MB WH	LED75S	-
66811399	4MX900 581 LED75S/840 PSD A30 WH	LED75S	-
66379899	4MX900 LED40S/840 PSD WB SI L1200	LED40S	-
66485699	4MX900 491 LED40S/840 PSU MB SI	LED40S	-

Données techniques de l'éclairage

Order Code	Full Product Name	Efficacité		Nombre de sources	
		lumineuse (nominale)	Flux lumineux	lumineuses	Type d'optique
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	149 lm/W	7'500 lm	-	Faisceau extensif
66882399	4MX900 581 LED50S/840 PSD MB WH	155 lm/W	5'000 lm	-	Faisceau semi-intensif
66977699	4MX900 581 LED50S/840 PSD WB WH	155 lm/W	5'000 lm	-	Faisceau extensif
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	149 lm/W	7'500 lm	1	Faisceau semi-intensif
66387399	4MX900 LED40S/840 PSD WB WH L1200	154 lm/W	4'000 lm	1	Faisceau extensif
66444399	4MX900 LED60S/840 PSD WB WH L1800	161 lm/W	6'000 lm	1	Faisceau extensif
66445099	4MX900 LED60S/840 PSD MB WH L1800	161 lm/W	6'000 lm	1	Faisceau semi-intensif
66460399	4MX900 LED90S/840 PSD WB WH L1800	150 lm/W	9'000 lm	1	Faisceau extensif
66461099	4MX900 LED90S/840 PSD MB WH L1800	150 lm/W	9'000 lm	1	Faisceau semi-intensif
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	150 lm/W	9'000 lm	1	Optique asymétrique double 20°
66476499	4MX900 581 LED40S/840 PSU WB WH	159 lm/W	4'000 lm	1	Faisceau extensif

Order Code	Full Product Name	Efficacité		Nombre de sources	
		lumineuse (nominale)	Flux lumineux	lumineuses	Type d'optique
66477199	4MX900 581 LED40S/840 PSU MB WH	159 lm/W	4'000 lm	1	Faisceau semi-intensif
66492499	4MX900 491 LED40S/840 PSU WB WH	159 lm/W	4'000 lm	1	Faisceau extensif
66493199	4MX900 491 LED40S/840 PSU MB WH	159 lm/W	4'000 lm	1	Faisceau semi-intensif
66624999	4MX900 491 LED40S/840 PSD WB WH	159 lm/W	4'000 lm	1	Faisceau extensif
66625699	4MX900 491 LED40S/840 PSD MB WH	159 lm/W	4'000 lm	1	Faisceau semi-intensif
66626399	4MX900 491 LED40S/840 PSD NB WH	159 lm/W	4'000 lm	1	Faisceau intensif
66628799	4MX900 491 LED50S/840 PSD WB WH	155 lm/W	5'000 lm	1	Faisceau extensif
66629499	4MX900 491 LED50S/840 PSD MB WH	155 lm/W	5'000 lm	1	Faisceau semi-intensif
66633199	4MX900 LED40S/840 PSD A30 WH L1200	154 lm/W	4'000 lm	1	Miroir asymétrique, inclinaison de l'axe de 30°
66635599	4MX900 LED60S/840 PSD A30 WH L1800	161 lm/W	6'000 lm	1	Miroir asymétrique, inclinaison de l'axe de 30°
66636299	4MX900 581 LED40S/840 PSU A30 WH	159 lm/W	4'000 lm	1	Miroir asymétrique, inclinaison de l'axe de 30°
66640999	4MX900 581 LED50S/840 PSU WB WH	155 lm/W	5'000 lm	1	Faisceau extensif
66641699	4MX900 581 LED50S/840 PSU MB WH	155 lm/W	5'000 lm	1	Faisceau semi-intensif

Maxos LED Performer

Order Code	Full Product Name	Efficacité		Nombre de sources		Type d'optique
		lumineuse (nominale)	Flux lumineux	lumineuses		
66644799	4MX900 491 LED50S/840 PSU WB WH	155 lm/W	5'000 lm	1		Faisceau extensif
66645499	4MX900 491 LED50S/840 PSU MB WH	155 lm/W	5'000 lm	1		Faisceau semi-intensif
66646199	4MX900 491 LED50S/840 PSU NB WH	155 lm/W	5'000 lm	1		Faisceau intensif
66709399	4MX900 581 LED75S/840 PSU A30 WH	149 lm/W	7'500 lm	1		Miroir asymétrique, inclinaison de l'axe de 30°
66790199	4MX900 491 LED75S/840 PSU WB WH	149 lm/W	7'500 lm	1		Faisceau extensif
66795699	4MX900 581 LED75S/840 PSU WB WH	149 lm/W	7'500 lm	1		Faisceau extensif
66796399	4MX900 581 LED75S/840 PSU MB WH	149 lm/W	7'500 lm	1		Faisceau semi-intensif
66797099	4MX900 581 LED75S/840 PSU NB WH	149 lm/W	7'500 lm	1		Faisceau intensif
66800799	4MX900 491 LED75S/840 PSD WB WH	149 lm/W	7'500 lm	1		Faisceau extensif

Order Code	Full Product Name	Efficacité		Nombre de sources		Type d'optique
		lumineuse (nominale)	Flux lumineux	lumineuses		
66801499	4MX900 491 LED75S/840 PSD MB WH	149 lm/W	7'500 lm	1		Faisceau semi-intensif
66802199	4MX900 491 LED75S/840 PSD NB WH	149 lm/W	7'500 lm	1		Faisceau intensif
66805299	4MX900 491 LED75S/840 PSD A30 WH	149 lm/W	7'500 lm	1		Miroir asymétrique, inclinaison de l'axe de 30°
66806999	4MX900 581 LED75S/840 PSD WB WH	149 lm/W	7'500 lm	1		Faisceau extensif
66807699	4MX900 581 LED75S/840 PSD MB WH	149 lm/W	7'500 lm	1		Faisceau semi-intensif
66811399	4MX900 581 LED75S/840 PSD A30 WH	149 lm/W	7'500 lm	1		Miroir asymétrique, inclinaison de l'axe de 30°
66379899	4MX900 LED40S/840 PSD WB SI L1200	154 lm/W	4'000 lm	1		Faisceau extensif
66485699	4MX900 491 LED40S/840 PSU MB SI	159 lm/W	4'000 lm	1		Faisceau semi-intensif

Fonctionnement et électricité

Order Code	Full Product Name	Consommation	
		Tension d'entrée	électrique
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	220 à 240 V	50.2 W
66882399	4MX900 581 LED50S/840 PSD MB WH	220 à 240 V	32.2 W
66977699	4MX900 581 LED50S/840 PSD WB WH	220-240 V	32.2 W
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	220 à 240 V	50.2 W
66387399	4MX900 LED40S/840 PSD WB WH L1200	220 à 240 V	25.9 W
66444399	4MX900 LED60S/840 PSD WB WH L1800	220 à 240 V	37.3 W
66445099	4MX900 LED60S/840 PSD MB WH L1800	220 à 240 V	37.3 W
66460399	4MX900 LED90S/840 PSD WB WH L1800	220 à 240 V	60.1 W

Order Code	Full Product Name	Consommation	
		Tension d'entrée	électrique
66461099	4MX900 LED90S/840 PSD MB WH L1800	220 à 240 V	60.1 W
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	220 à 240 V	60.1 W
66476499	4MX900 581 LED40S/840 PSU WB WH	220 à 240 V	25.2 W
66477199	4MX900 581 LED40S/840 PSU MB WH	220 à 240 V	25.2 W
66492499	4MX900 491 LED40S/840 PSU WB WH	220 à 240 V	25.2 W
66493199	4MX900 491 LED40S/840 PSU MB WH	220 à 240 V	25.2 W
66624999	4MX900 491 LED40S/840 PSD WB WH	220 à 240 V	25.2 W
66625699	4MX900 491 LED40S/840 PSD MB WH	220 à 240 V	25.2 W

Maxos LED Performer

Order Code	Full Product Name	Tension d'entrée	Consommation électrique
66626399	4MX900 491 LED40S/840 PSD NB WH	220 à 240 V	25.2 W
66628799	4MX900 491 LED50S/840 PSD WB WH	220 à 240 V	32.2 W
66629499	4MX900 491 LED50S/840 PSD MB WH	220 à 240 V	32.2 W
66633199	4MX900 LED40S/840 PSD A30 WH L1200	220 à 240 V	25.9 W
66635599	4MX900 LED60S/840 PSD A30 WH L1800	220 à 240 V	37.3 W
66636299	4MX900 581 LED40S/840 PSU A30 WH	220 à 240 V	25.2 W
66640999	4MX900 581 LED50S/840 PSU WB WH	220 à 240 V	32.2 W
66641699	4MX900 581 LED50S/840 PSU MB WH	220 à 240 V	32.2 W
66644799	4MX900 491 LED50S/840 PSU WB WH	220 à 240 V	32.2 W
66645499	4MX900 491 LED50S/840 PSU MB WH	220 à 240 V	32.2 W
66646199	4MX900 491 LED50S/840 PSU NB WH	220 à 240 V	32.2 W
66709399	4MX900 581 LED75S/840 PSU A30 WH	220 à 240 V	50.2 W
66790199	4MX900 491 LED75S/840 PSU WB WH	220 à 240 V	50.2 W

Order Code	Full Product Name	Tension d'entrée	Consommation électrique
66795699	4MX900 581 LED75S/840 PSU WB WH	220 à 240 V	50.2 W
66796399	4MX900 581 LED75S/840 PSU MB WH	220 à 240 V	50.2 W
66797099	4MX900 581 LED75S/840 PSU NB WH	220 à 240 V	50.2 W
66800799	4MX900 491 LED75S/840 PSD WB WH	220 à 240 V	50.2 W
66801499	4MX900 491 LED75S/840 PSD MB WH	220 à 240 V	50.2 W
66802199	4MX900 491 LED75S/840 PSD NB WH	220 à 240 V	50.2 W
66805299	4MX900 491 LED75S/840 PSD A30 WH	220 à 240 V	50.2 W
66806999	4MX900 581 LED75S/840 PSD WB WH	220 à 240 V	50.2 W
66807699	4MX900 581 LED75S/840 PSD MB WH	220 à 240 V	50.2 W
66811399	4MX900 581 LED75S/840 PSD A30 WH	220 à 240 V	50.2 W
66379899	4MX900 LED40S/840 PSD WB SI L1200	220 à 240 V	25.9 W
66485699	4MX900 491 LED40S/840 PSU MB SI	220 à 240 V	25.2 W

Commandes et gradation

Order Code	Full Product Name	Variation de l'intensité lumineuse
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	Oui
66882399	4MX900 581 LED50S/840 PSD MB WH	Oui
66977699	4MX900 581 LED50S/840 PSD WB WH	Oui
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	Oui
66387399	4MX900 LED40S/840 PSD WB WH L1200	Oui
66444399	4MX900 LED60S/840 PSD WB WH L1800	Oui
66445099	4MX900 LED60S/840 PSD MB WH L1800	Oui
66460399	4MX900 LED90S/840 PSD WB WH L1800	Oui
66461099	4MX900 LED90S/840 PSD MB WH L1800	Oui
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Oui
66476499	4MX900 581 LED40S/840 PSU WB WH	Non
66477199	4MX900 581 LED40S/840 PSU MB WH	Non
66492499	4MX900 491 LED40S/840 PSU WB WH	Non
66493199	4MX900 491 LED40S/840 PSU MB WH	Non
66624999	4MX900 491 LED40S/840 PSD WB WH	Oui
66625699	4MX900 491 LED40S/840 PSD MB WH	Oui
66626399	4MX900 491 LED40S/840 PSD NB WH	Oui
66628799	4MX900 491 LED50S/840 PSD WB WH	Oui
66629499	4MX900 491 LED50S/840 PSD MB WH	Oui
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Oui

Order Code	Full Product Name	Variation de l'intensité lumineuse
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Oui
66636299	4MX900 581 LED40S/840 PSU A30 WH	Non
66640999	4MX900 581 LED50S/840 PSU WB WH	Non
66641699	4MX900 581 LED50S/840 PSU MB WH	Non
66644799	4MX900 491 LED50S/840 PSU WB WH	Non
66645499	4MX900 491 LED50S/840 PSU MB WH	Non
66646199	4MX900 491 LED50S/840 PSU NB WH	Non
66709399	4MX900 581 LED75S/840 PSU A30 WH	Non
66790199	4MX900 491 LED75S/840 PSU WB WH	Non
66795699	4MX900 581 LED75S/840 PSU WB WH	Non
66796399	4MX900 581 LED75S/840 PSU MB WH	Non
66797099	4MX900 581 LED75S/840 PSU NB WH	Non
66800799	4MX900 491 LED75S/840 PSD WB WH	Oui
66801499	4MX900 491 LED75S/840 PSD MB WH	Oui
66802199	4MX900 491 LED75S/840 PSD NB WH	Oui
66805299	4MX900 491 LED75S/840 PSD A30 WH	Oui
66806999	4MX900 581 LED75S/840 PSD WB WH	Oui
66807699	4MX900 581 LED75S/840 PSD MB WH	Oui
66811399	4MX900 581 LED75S/840 PSD A30 WH	Oui
66379899	4MX900 LED40S/840 PSD WB SI L1200	Oui

Maxos LED Performer

Order Code	Full Product Name	Variation de l'intensité lumineuse
66485699	4MX900 491 LED40S/840 PSU MB SI	Non

Mécanique et boîtier

Order Code	Full Product Name	Couleur du corps
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	Blanc
66882399	4MX900 581 LED50S/840 PSD MB WH	Blanc
66977699	4MX900 581 LED50S/840 PSD WB WH	Blanc
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	Blanc
66387399	4MX900 LED40S/840 PSD WB WH L1200	Blanc
66444399	4MX900 LED60S/840 PSD WB WH L1800	Blanc
66445099	4MX900 LED60S/840 PSD MB WH L1800	Blanc
66460399	4MX900 LED90S/840 PSD WB WH L1800	Blanc
66461099	4MX900 LED90S/840 PSD MB WH L1800	Blanc
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Blanc
66476499	4MX900 581 LED40S/840 PSU WB WH	Blanc
66477199	4MX900 581 LED40S/840 PSU MB WH	Blanc
66492499	4MX900 491 LED40S/840 PSU WB WH	Blanc
66493199	4MX900 491 LED40S/840 PSU MB WH	Blanc
66624999	4MX900 491 LED40S/840 PSD WB WH	Blanc
66625699	4MX900 491 LED40S/840 PSD MB WH	Blanc
66626399	4MX900 491 LED40S/840 PSD NB WH	Blanc
66628799	4MX900 491 LED50S/840 PSD WB WH	Blanc
66629499	4MX900 491 LED50S/840 PSD MB WH	Blanc
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Blanc
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Blanc

Order Code	Full Product Name	Couleur du corps
66636299	4MX900 581 LED40S/840 PSU A30 WH	Blanc
66640999	4MX900 581 LED50S/840 PSU WB WH	Blanc
66641699	4MX900 581 LED50S/840 PSU MB WH	Blanc
66644799	4MX900 491 LED50S/840 PSU WB WH	Blanc
66645499	4MX900 491 LED50S/840 PSU MB WH	Blanc
66646199	4MX900 491 LED50S/840 PSU NB WH	Blanc
66709399	4MX900 581 LED75S/840 PSU A30 WH	Blanc
66790199	4MX900 491 LED75S/840 PSU WB WH	Blanc
66795699	4MX900 581 LED75S/840 PSU WB WH	Blanc
66796399	4MX900 581 LED75S/840 PSU MB WH	Blanc
66797099	4MX900 581 LED75S/840 PSU NB WH	Blanc
66800799	4MX900 491 LED75S/840 PSD WB WH	Blanc
66801499	4MX900 491 LED75S/840 PSD MB WH	Blanc
66802199	4MX900 491 LED75S/840 PSD NB WH	Blanc
66805299	4MX900 491 LED75S/840 PSD A30 WH	Blanc
66806999	4MX900 581 LED75S/840 PSD WB WH	Blanc
66807699	4MX900 581 LED75S/840 PSD MB WH	Blanc
66811399	4MX900 581 LED75S/840 PSD A30 WH	Blanc
66379899	4MX900 LED40S/840 PSD WB SI L1200	Argent
66485699	4MX900 491 LED40S/840 PSU MB SI	Argent

Performances initiales

Order Code	Full Product Name	Chromaticité initiale
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	(0.38, 0.38) SDCM <3.5
66882399	4MX900 581 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66977699	4MX900 581 LED50S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	(0.38, 0.38) SDCM <3.5
66387399	4MX900 LED40S/840 PSD WB WH L1200	(0.38, 0.38) SDCM <3.5
66444399	4MX900 LED60S/840 PSD WB WH L1800	(0.38, 0.38) SDCM <3.5
66445099	4MX900 LED60S/840 PSD MB WH L1800	(0.38, 0.38) SDCM <3.5
66460399	4MX900 LED90S/840 PSD WB WH L1800	(0.38, 0.38) SDCM <3.5
66461099	4MX900 LED90S/840 PSD MB WH L1800	(0.38, 0.38) SDCM <3.5
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	(0.38, 0.38) SDCM <3.5
66476499	4MX900 581 LED40S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66477199	4MX900 581 LED40S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66492499	4MX900 491 LED40S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66493199	4MX900 491 LED40S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66624999	4MX900 491 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66625699	4MX900 491 LED40S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66626399	4MX900 491 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
66628799	4MX900 491 LED50S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66629499	4MX900 491 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66633199	4MX900 LED40S/840 PSD A30 WH L1200	(0.38, 0.38) SDCM <3.5
66635599	4MX900 LED60S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5


Order Code	Full Product Name	Chromaticité initiale
66636299	4MX900 581 LED40S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
66640999	4MX900 581 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66641699	4MX900 581 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66644799	4MX900 491 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66645499	4MX900 491 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66646199	4MX900 491 LED50S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5
66709399	4MX900 581 LED75S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
66790199	4MX900 491 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66795699	4MX900 581 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66796399	4MX900 581 LED75S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66797099	4MX900 581 LED75S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5
66800799	4MX900 491 LED75S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66801499	4MX900 491 LED75S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66802199	4MX900 491 LED75S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
66805299	4MX900 491 LED75S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
66806999	4MX900 581 LED75S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66807699	4MX900 581 LED75S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66811399	4MX900 581 LED75S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
66379899	4MX900 LED40S/840 PSD WB SI L1200	(0.38, 0.38) SDCM <3.5
66485699	4MX900 491 LED40S/840 PSU MB SI	(0.38, 0.38) SDCM <3

Conditions d'application


Order Code	Full Product Name	Niveau de gradation maximal
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	1%
66882399	4MX900 581 LED50S/840 PSD MB WH	1%
66977699	4MX900 581 LED50S/840 PSD WB WH	1%
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	1%
66387399	4MX900 LED40S/840 PSD WB WH L1200	1%
66444399	4MX900 LED60S/840 PSD WB WH L1800	1%
66445099	4MX900 LED60S/840 PSD MB WH L1800	1%
66460399	4MX900 LED90S/840 PSD WB WH L1800	1%
66461099	4MX900 LED90S/840 PSD MB WH L1800	1%
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	1%
66476499	4MX900 581 LED40S/840 PSU WB WH	Non applicable
66477199	4MX900 581 LED40S/840 PSU MB WH	Non applicable
66492499	4MX900 491 LED40S/840 PSU WB WH	Non applicable
66493199	4MX900 491 LED40S/840 PSU MB WH	Non applicable
66624999	4MX900 491 LED40S/840 PSD WB WH	1%
66625699	4MX900 491 LED40S/840 PSD MB WH	1%
66626399	4MX900 491 LED40S/840 PSD NB WH	1%
66628799	4MX900 491 LED50S/840 PSD WB WH	1%
66629499	4MX900 491 LED50S/840 PSD MB WH	1%
66633199	4MX900 LED40S/840 PSD A30 WH L1200	1%
66635599	4MX900 LED60S/840 PSD A30 WH L1800	1%

Order Code	Full Product Name	Niveau de gradation maximal
66636299	4MX900 581 LED40S/840 PSU A30 WH	Non applicable
66640999	4MX900 581 LED50S/840 PSU WB WH	Non applicable
66641699	4MX900 581 LED50S/840 PSU MB WH	Non applicable
66644799	4MX900 491 LED50S/840 PSU WB WH	Non applicable
66645499	4MX900 491 LED50S/840 PSU MB WH	Non applicable
66646199	4MX900 491 LED50S/840 PSU NB WH	Non applicable
66709399	4MX900 581 LED75S/840 PSU A30 WH	Non applicable
66790199	4MX900 491 LED75S/840 PSU WB WH	Non applicable
66795699	4MX900 581 LED75S/840 PSU WB WH	Non applicable
66796399	4MX900 581 LED75S/840 PSU MB WH	Non applicable
66797099	4MX900 581 LED75S/840 PSU NB WH	Non applicable
66800799	4MX900 491 LED75S/840 PSD WB WH	1%
66801499	4MX900 491 LED75S/840 PSD MB WH	1%
66802199	4MX900 491 LED75S/840 PSD NB WH	1%
66805299	4MX900 491 LED75S/840 PSD A30 WH	1%
66806999	4MX900 581 LED75S/840 PSD WB WH	1%
66807699	4MX900 581 LED75S/840 PSD MB WH	1%
66811399	4MX900 581 LED75S/840 PSD A30 WH	1%
66379899	4MX900 LED40S/840 PSD WB SI L1200	1%
66485699	4MX900 491 LED40S/840 PSU MB SI	Non applicable


Polar Wide Diagrams



IFPS_4MX900 491 1xLED40S/830 PSD A30-
Polar Normal (separate)






IFPS_4MX900 491 1xLED40S/830 PSD MB-
Polar Normal (separate)



IFPS_4MX900 491 1xLED40S/830 PSD WB-
Polar Normal (separate)

Maxos LED Performer




Polar Wide Diagrams



**IFPS_4MX900 491 1xLED40S/830 PSU MB-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED40S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED40S/840 PSD A30-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED40S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSU WB-
Polar Normal (separate)**

**IFPS_4MX900 491 1xLED50S/830 PSD A30-
Polar Normal (separate)**


**IFPS_4MX900 491 1xLED50S/830 PSD MB-
Polar Normal (separate)**

Maxos LED Performer


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED50S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD A30-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED71S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD WB-
Polar Normal (separate)**

Maxos LED Performer


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU WB-
Polar Normal (separate)**



**IFPS_4MX900 581 1xLED40S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD WB-
Polar Normal (separate)**

Maxos LED Performer


Polar Wide Diagrams




**IFPS_4MX900 581 1xLED40S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/840 PSD A30-
Polar Normal (separate)**



**IFPS_4MX900 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED71S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED71S/830 PSU NB-Polar
Normal (separate)**

Maxos LED Performer


Polar Wide Diagrams




**IFPS_4MX900 581 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED57S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED60S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD
DA20-Polar Normal (separate)**



**IFPS_4MX900 L1800 1xLED48S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/830 PSD MB-
Polar Normal (separate)**

Maxos LED Performer


Polar Wide Diagrams




IFPS_4MX900 L1800 1xLED60S/840 PSD DA20-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED60S/840 PSD MB-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED85S/830 PSD A30-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED85S/830 PSD MB-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED85S/830 PSD WB-Polar Normal (separate)




IFPS_4MX900 L1800 1xLED90S/840 PSD DA20-Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED40S/830 PSD A30-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/830 PSD MB-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED40S/830 PSD NB-Polar Normal (separate)

Maxos LED Performer


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED40S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD
A30-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSU MB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED50S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD WB-
Polar Normal (separate)**

Maxos LED Performer


Polar Wide Diagrams




IFPS_4MX900 G3 491 1xLED50S/830 PSU NB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/830 PSU WB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/840 PSD MB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/840 PSD NB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/840 PSU MB-
Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/840 PSU NB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/840 PSU WB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED71S/830 PSD A30-
Polar Normal (separate)

Maxos LED Performer


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/830 PSD A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD A30-
Polar Normal (separate)**

Maxos LED Performer


Polar Wide Diagrams




**IFPS_4MX900 G3 581 1xLED40S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED50S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/840 PSD MB-
Polar Normal (separate)**

Maxos LED Performer


Polar Wide Diagrams




**IFPS_4MX900 G3 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED71S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED71S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED71S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED71S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED75S/840 PSD A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED75S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED75S/840 PSU MB-
Polar Normal (separate)**

Maxos LED Performer


Polar Wide Diagrams




**IFPS_4MX900 G3 581 1xLED75S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 L1800 1xLED60S/830 PSD
WB-Polar Normal (separate)**



**IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
MB-Polar Normal (separate)**



**IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
WB-Polar Normal (separate)**



**IFPS_4MX900 G3 L1800 1xLED85S/830 PSD
WB-Polar Normal (separate)**

