



Maxos LED Spot Inserts – flexibility and style

Maxos LED Spot Inserts

In specific areas of shops such as fruit and vegetable displays, projectors are often required in addition to LED-based general lighting. Accent lighting is an integral part of the Maxos concept. These dedicated inserts allow light lines to be flexibly equipped with the latest range of projectors as well as general LED lighting. 4MX960 units with projectors for Maxos trunkings with flat ribbon cable (5 x 2.5 mm, 7 x 2.5 mm) are available. These units can be clicked into the trunking sections like a regular electrical unit. Surface-mounted projectors are fixed to the inserts.

Benefits

- Easy to install
- Seamless integration into Maxos rail
- Suitable for latest version of StyliD

Features

- One or two StyliD projectors
- Each projector has 360° directional freedom
- Flexibility in placement on Maxos rail

Application

- Retail

Maxos LED Spot Inserts

Versions



Maxos LED spot inserts 4MX960
trunking system with StyliD ST540C
projector



Maxos LED spot inserts 4MX960
trunking system with StyliD ST540C
projectors



Maxos LED spot inserts 4MX960
trunking system with StyliD ST550C
projector



Maxos LED spot inserts 4MX960
trunking system with StyliD ST550C
projectors

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

Optic type	MB
Product Family Code	4MX960

Initial Performance (IEC Compliant)

Init. Corr. Colour Temperature	3000 K
--------------------------------	--------

Mechanical and Housing

Colour	White
--------	-------

General Information

Order Code	Full Product Name	CE mark	Protection class IEC	Lamp family code	Number of units	Product family code unit A
25545200	4MX960 1 ST540C LED25S/830 PSU MB WH	-	-	LED25S	1 unit	ST540C
25546900	4MX960 2 ST540C LED25S/830 PSU MB WH	CE mark	Safety class I	LED25S	2 units	ST540C
25547600	4MX960 1 ST550C LED39S/830 PSU MB WH	-	-	LED39S	1 unit	ST550C
25548300	4MX960 2 ST550C LED39S/830 PSU MB WH	-	-	LED39S	2 units	ST550C

Initial Performance (IEC Compliant)

Maxos LED Spot Inserts

Order Code	Full Product Name	Initial luminous flux
25545200	4MX960 1 ST540C LED25S/830 PSU MB WH	2700 lm
25546900	4MX960 2 ST540C LED25S/830 PSU MB WH	5400 lm

Order Code	Full Product Name	Initial luminous flux
25547600	4MX960 1 ST550C LED39S/830 PSU MB WH	4300 lm
25548300	4MX960 2 ST550C LED39S/830 PSU MB WH	8600 lm

