



Product Description

MASTER SON-T PIA Eco

High Pressure Sodium lamp with clear tubular outer bulb, high output at reduced power consumption

Benefits

- Superior technology results in a long and reliable lifetime, high lumen maintenance
- High luminous efficacy makes this a easy energy saving HPS lamp

Features

- Clear tubular outer bulb
- Ceramic discharge tube with Philips Integrated Antenna (PIA) for a long and reliable lifetime
- Robust construction with few welding points is highly vibration- and shock-resistant
- ZrCo getter ensures high lumen maintenance and few early failures
- "Eco" concept with high luminous efficacy to saving energy

Application

- Road and residential lighting
- Decorative floodlighting, illumination
- Industrial area lighting
- Recreational sports facilities Outdoor and Indoor


MASTER SON-T PIA Eco

Versions



SON-T PIA 130W E E40

Dimensional drawing



Product	D (max)	L	C (max)
MASTER SON-T PIA Eco 130W E E40 1SL/12	47 mm	132 mm	209 mm

