



Product Description

TL-E 80

Fluorescent lamps with a circular tube having a diameter of 26 mm

优点

- /80 colors have good color rendering and high efficacy compared with standard colors
- Symmetrical, omnidirectional light distribution
- Create atmospheres from warm white to cool daylight

特点

- Available in various color designations

应用

- Suitable for use in a wide range of luminaires for various purposes, including decorative luminaires
- Ideal for 'human' applications such as schools, offices, shops and homes


Versions



LPPR TL-E8 G10q

TL-E 80

二维绘图



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 22W/840 1CT/20	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm
TL-E 22W/865 1CT/20	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm

一般信息	
标称使用寿命	8,000 小时
灯技术	
显色指数 (CRI)	80
操作和电气	
灯具电流 (标称)	0.400 A
电压 (标称)	62 V
控制和调光	
可调光	是
机械和外壳	
灯泡外形	C-T29
审批和申请	
能耗 kWh/1000 h	24 kWh
汞 (Hg) 含量 (标称)	8 mg

Order Code	Full Product Name	底盖
928026284074	TL-E 22W/840 1CT/20	G10Q
928026286574	TL-E 22W/865 1CT/20	G10q

灯技术

Order Code	Full Product Name	颜色名称	相关色温 (标称)	光效 (额定)	光通量
928026284074	TL-E 22W/840 1CT/20	冷白色 (CW)	4000 K	59 lm/W	1,285 lm



TL-E 80

Order Code	Full Product Name	颜色名称	相关色温 (标称)	光效 (额定) (标称)	光通量
928026286574	TL-E 22W/865	冷日光	6500 K	57 lm/W	1,250 lm
	1CT/20				

操作和电气

Order Code	Full Product Name	功耗
928026284074	TL-E 22W/840 1CT/20	22 W

Order Code	Full Product Name	功耗
928026286574	TL-E 22W/865 1CT/20	22.0 W

