



CitySwan Bollard – stylish and discreet

CitySwan Pullert

Being part of the CitySwan family designed by Danish architects Bjarne Schläger and Morten Weeke Borup, the CitySwan Bollard has a stylish, discreet, graceful appearance. The luminaire provides downward functional surface light from high-performance LEDs with incredibly low energy consumption. It is made of dark grey die-cast aluminum, and the housing has a characteristic ellipsoid shape familiar from the CitySwan road luminaire. CitySwan Bollard comes with a choice of three different optical covers: a transparent flat cover for the slickest design, a convex transparent cover for a more elongated light distribution, and a flat, opal cover for optimum uniformity. Nominated for the German design award "Designpreis" in 2009 Danish Design Award 2010/2011 Design: Bjarne Schläger, light + architecture and Morten Weeke Borup, GHB Landskabsarkitekter A/S

Fordeler

- Elegant Danish design
- Energy-efficient

Funksjoner

- Provides functional lighting together with a nice design

Søknad

- Entrances
- Squares
- Sidewalks and bicycle and walking paths

spesifikasjoner

Produktnavn	BGP444
Lyskilde	LUXEON®
Strømsystem	7 W

Korrelert	3000 K (varmhvit)
fargetemperatur	4000 K (nøytral hvit)

Lysytelse	Varmhvit: 380 lm
	Nøytralhvit: 420 lm
Fargegjengivelse	84 (3000 K)
	73 (4000 K)
Lumenedlikehold ved en median levetid* på 100 000 timer	min L80
Feilrate på styringsforkoblinger* ved 100 000 timer	10%
Omgivelsestemperatur og ytelse Tq	+25 °C

Driftstemperatur	–20 til +25 °C
Driver	Innebygd (selvforkoblet LED-modul)
Nettspenning	220–240V / 50–60Hz
Dimming	1–10 V DC (på forespørsel)
Materialer	Mast: ekstrudert aluminium
	Hus: formstøpt aluminium
	Optisk deksel: polykarbonat, gjennomsiktig kule eller flat opal
Farge	Svart 200 Sablé
	Andre RAL-farger på forespørsel
Montering	Undergrunns lengde: 800 mm (må festes i solid grunn)
	Maks SCx: 0,09 m²

Versions



Godkjenning og bruk	
Mek. stöt, beskyttelseskode	IK10
Kontroller og dimming	
Dimmbar	No
Generell informasjon	
CE-merke	CE mark
Fargevalg	Black Noir 200 Sablé
Driver inkludert	Ja
lyskildeserierkode	LED-K2
Lyskilde kan erstattes	No
Produktserierkode	BGP444

Generell informasjon

Order Code	Full Product Name	Optisk deksel-/linsetype
09629200	BGP444 LED/740 230V II PCC BK-200	PCC
09630800	BGP444 LED/740 230V II FG BK-200	FG

